

Data sheet for SINAMICS G120X

Article No.: 6SL3230-2YE32-0UP0

Client order no. : Order no. : Offer no. : Remarks :

	Rated data		
Input			
Number of phases	3 AC		
Line voltage	380 480 V -	+10 % -20 %	
Line frequency	47 63 Hz		
Rated voltage	400V IEC	480V NEC	
Rated current (LO)	42.00 A	37.00 A	
Rated current (HO)	38.00 A	35.00 A	
Output			
Number of phases	3 AC		
Rated voltage	400V IEC	480V NEC 1)	
Rated power (LO)	22.00 kW	30.00 hp	
Rated power (HO)	18.50 kW	25.00 hp	
Rated current (LO)	45.00 A	40.00 A	
Rated current (HO)	38.00 A	34.00 A	
Rated current (IN)	47.00 A		
Max. output current	61.00 A		
Pulse frequency	4 kHz		
Output frequency for vector	control 0 200 Hz		
Output frequency for V/f con	trol 0 550 Hz		
Overload capability			

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

 $150\%\,x$ base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor λ	0.90 0.95	
Offset factor $\cos\phi$	0.99	
Efficiency η	0.97	
Sound pressure level (1m)	70 dB	
Power loss 3)	0.732 kW	
Filter class (integrated)	Unfiltered	
EMC category (with accessories)	without	
Safety function "Safe Torque Off"	without	
_		

_		
Commu	ınıca	tion
COIIIIII	ııııca	LIVII

Communication PROFIBUS DP



Item no. : Consignment no. : Project :

Inputs	outputs	
Standard digital inputs		
Number	6	
Switching level: $0 \rightarrow 1$	11 V	
Switching level: $1 \rightarrow 0$	5 V	
Max. inrush current	15 mA	
Fail-safe digital inputs		
Number	1	
Digital outputs		
Number as relay changeover contact	2	
Output (resistive load)	DC 30 V, 5.0 A	
Number as transistor	0	
Analog / digital inputs		
Number	2 (Differential input)	
Resolution	10 bit	
Switching threshold as digital input		
0 → 1	4 V	
1 → 0	1.6 V	
Analog outputs		
Number	1 (Non-isolated output)	

PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5~^\circ\text{C}$

Closed-loop control techniques		
V/f linear / square-law / parameterizable	Yes	
V/f with flux current control (FCC)	Yes	
V/f ECO linear / square-law	Yes	
Sensorless vector control	Yes	
Vector control, with sensor	No	
Encoderless torque control	No	
Torque control, with encoder	No	



Data sheet for SINAMICS G120X

Article No.: 6SL3230-2YE32-0UP0


Ambient conditions		
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002	
Cooling	Air cooling using an integrated fan	
Cooling air requirement	0.055 m³/s (1.942 ft³/s)	
Installation altitude	1,000 m (3,280.84 ft)	
Ambient temperature		
Operation	-20 45 °C (-4 113 °F)	
Transport	-40 70 °C (-40 158 °F)	
Storage	-25 55 °C (-13 131 °F)	
Relative humidity		
Max. operation	$95~\%$ At $40~^\circ\text{C}$ (104 $^\circ\text{F}$), condensation and icing not permissible	
Conn	ections	
Signal cable		
Conductor cross-section	0.15 1.50 mm ² (AWG 24 AWG 16)	
Line side		
Version	screw-type terminal	
Conductor cross-section	10.00 35.00 mm ² (AWG 8 AWG 2)	
Motor end		
Version	Screw-type terminals	
Conductor cross-section	10.00 35.00 mm ² (AWG 8 AWG 2)	
DC link (for braking resistor)		
PE connection	Screw-type terminals	
Max. motor cable length		
	200 m (656.17 ft)	
Shielded	200 111 (030.17 11)	

	Mechanical data		
D	egree of protection	IP20 / UL open type	
Frame size		FSD	
Net weight		17 kg (37.48 lb)	
Dimensions			
	Width	200 mm (7.87 in)	
	Height	472 mm (18.58 in)	
	Depth	248 mm (9.76 in)	
Standards			
Compliance with standards		UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH	
CE marking		EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC	

Converter losses to IEC61800-9-2*

IE2

47.6 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

Efficiency class

Comparison with the reference converter (90% / 100%)

 $^{^{1)}}$ The output current and HP ratings are valid for the voltage range 440V-480V

³⁾Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.



Data sheet for SINAMICS G120X

Article No.: 6SL3230-2YE32-0UP0

	Operator pane	l: Basic Operator Panel (BOP-2)
	Screen	
Display design	LCD, monochrome	Ambient temperature
	Mechanical data	Operation
Degree of protection	IP55 / UL type 12	Storage
Net weight	0.140 kg (0.31 lb)	Transport
Dimensions		Relative humidity at 25
Width	70.00 mm (2.76 in)	Max. operation
Height	106.85 mm (4.21 in)	
Depth	19.60 mm (0.77 in)	Certificate of suitability

Ambient conditions		
Ambient temperature		
Operation	0 50 °C (32 122 °F)	
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
Relative humidity at 25°C during		
Max. operation	95 %	
Approvals		
Certificate of suitability CE, cULus, EAC, KCC, RCM		