SIEMENS

Data sheet 3RW5215-3TC04



SIRIUS soft starter 200-480 V 25 A, 24 V AC/DC spring-type terminals Thermistor input

product brand name	SIRIUS
product category	Hybrid switching devices
product designation	Soft starter
product type designation	3RW52
manufacturer's article number	
 of standard HMI module usable 	3RW5980-0HS00
 of high feature HMI module usable 	3RW5980-0HF00
 of communication module PROFINET standard usable 	3RW5980-0CS00
 of communication module PROFIBUS usable 	3RW5980-0CP00
 of communication module Modbus TCP usable 	3RW5980-0CT00
 of communication module Modbus RTU usable 	3RW5980-0CR00
 of communication module Ethernet/IP 	3RW5980-0CE00
 of circuit breaker usable at 400 V 	3RV2032-4EA10; Type of coordination 1, Iq = 65 kA, CLASS 10
 of circuit breaker usable at 500 V 	3RV2032-4EA10; Type of coordination 1, Iq = 15 kA, CLASS 10
 of circuit breaker usable at 400 V at inside-delta circuit 	3RV2032-4VA10; Type of coordination 1, Iq = 65 kA, CLASS 10
 of circuit breaker usable at 500 V at inside-delta circuit 	3RV2032-4VA10; Type of coordination 1, Iq = 15 kA, CLASS 10
 of the gG fuse usable up to 690 V 	3NA3822-6; Type of coordination 1, Iq = 65 kA
 of the gG fuse usable at inside-delta circuit up to 500 V 	3NA3822-6; Type of coordination 1, Iq = 65 kA
 of full range R fuse link for semiconductor protection usable up to 690 V 	3NE1817-0: Type of coordination 2, Iq = 65 kA
 of back-up R fuse link for semiconductor protection usable up to 690 V 	3NE8021-1; Type of coordination 2, Iq = 65 kA

General technical data	
starting voltage [%]	30 100 %
stopping voltage [%]	50 %; non-adjustable
start-up ramp time of soft starter	0 20 s
current limiting value [%] adjustable	130 700 %
certificate of suitability	
CE marking	Yes
UL approval	Yes
CSA approval	Yes
product component	
HMI-High Feature	No
 is supported HMI-Standard 	Yes
is supported HMI-High Feature	Yes
product feature integrated bypass contact system	Yes
number of controlled phases	3

	01.400.404.41.5.10.4405.4005
trip class	CLASS 10A (default) / 10E / 20E; acc. to IEC 60947-4-2
buffering time in the event of power failure	
for main current circuit	100 ms
for control circuit	100 ms
insulation voltage rated value	600 V
degree of pollution	3, acc. to IEC 60947-4-2
impulse voltage rated value	6 kV
blocking voltage of the thyristor maximum	1 600 V
service factor	1
surge voltage resistance rated value	6 kV
maximum permissible voltage for safe isolation	
between main and auxiliary circuit	600 V
shock resistance	15 g / 11 ms, from 12 g / 11 ms with potential contact lifting
vibration resistance	15 mm to 6 Hz; 2g to 500 Hz
utilization category according to IEC 60947-4-2	AC 53a
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	02/15/2018
product function	
ramp-up (soft starting)	Yes
ramp-down (soft stop)	Yes
Soft Torque	Yes
adjustable current limitation	Yes
pump ramp down	Yes
intrinsic device protection	Yes
motor overload protection	Yes; Full motor protection (thermistor motor protection and electronic motor overload protection)
 evaluation of thermistor motor protection 	Yes; Type A PTC or Klixon / Thermoclick
• inside-delta circuit	Yes
• auto-RESET	Yes
manual RESET	Yes
• remote reset	Yes; By turning off the control supply voltage
 communication function 	Yes
 operating measured value display 	Yes; Only in conjunction with special accessories
error logbook	Yes; Only in conjunction with special accessories
 via software parameterizable 	No
• via software configurable	Yes
PROFlenergy	Yes; in connection with the PROFINET Standard communication module
firmware update	Yes
 removable terminal for control circuit 	Yes
• torque control	No
analog output	No
Power Electronics	
operational current	
at 40 °C rated value	25 A
at 50 °C rated value	22 A
at 60 °C rated value	20 A
operational current at inside-delta circuit	
• at 40 °C rated value	43.3 A
at 50 °C rated value	39 A
at 60 °C rated value	33.9 A
operating voltage	
• rated value	200 480 V
at inside-delta circuit rated value	200 480 V
relative negative tolerance of the operating voltage	-15 %
relative positive tolerance of the operating voltage	10 %
relative negative tolerance of the operating voltage at inside-delta circuit	-15 %
relative positive tolerance of the operating voltage at inside-delta circuit	10 %
operating power for 3-phase motors	

	E E IAM
at 230 V at 40 °C rated value t 200 V at inside delta signality at 40 °C rated value.	5.5 kW
at 230 V at inside-delta circuit at 40 °C rated value at 400 V at 40 °C rated value	11 kW
at 400 V at 40 °C rated value at 400 V at incide delta circuit at 40 °C rated value.	11 kW 18.5 kW
at 400 V at inside-delta circuit at 40 °C rated value Operating frequency 1 rated value	18.5 KW 50 Hz
Operating frequency 2 rated value	60 Hz
relative negative tolerance of the operating frequency	-10 %
relative positive tolerance of the operating frequency	10 %
adjustable motor current	
at rotary coding switch on switch position 1	11.5 A
 at rotary coding switch on switch position 2 	12.4 A
at rotary coding switch on switch position 3	13.3 A
 at rotary coding switch on switch position 4 	14.2 A
 at rotary coding switch on switch position 5 	15.1 A
 at rotary coding switch on switch position 6 	16 A
 at rotary coding switch on switch position 7 	16.9 A
at rotary coding switch on switch position 8	17.8 A
 at rotary coding switch on switch position 9 	18.7 A
 at rotary coding switch on switch position 10 	19.6 A
at rotary coding switch on switch position 11	20.5 A
at rotary coding switch on switch position 12	21.4 A
at rotary coding switch on switch position 13	22.3 A
at rotary coding switch on switch position 14 at rotary coding switch on switch position 15	23.2 A
at rotary coding switch on switch position 15 at rotary coding switch on switch position 16	24.1 A 25 A
 at rotary coding switch on switch position 16 minimum 	25 A 11.5 A
adjustable motor current	11.07
for inside-delta circuit at rotary coding switch on switch position 1	19.9 A
 for inside-delta circuit at rotary coding switch on switch position 2 	21.5 A
 for inside-delta circuit at rotary coding switch on switch position 3 	23 A
 for inside-delta circuit at rotary coding switch on switch position 4 	24.6 A
 for inside-delta circuit at rotary coding switch on switch position 5 	26.2 A
 for inside-delta circuit at rotary coding switch on switch position 6 	27.7 A
 for inside-delta circuit at rotary coding switch on switch position 7 	29.3 A
for inside-delta circuit at rotary coding switch on switch position 8 for inside delta circuit at rotary coding switch on	30.8 A
 for inside-delta circuit at rotary coding switch on switch position 9 for inside-delta circuit at rotary coding switch on 	32.4 A 33.9 A
switch position 10 for inside-delta circuit at rotary coding switch on	35.5 A
switch position 11 • for inside-delta circuit at rotary coding switch on	37.1 A
switch position 12for inside-delta circuit at rotary coding switch on	38.6 A
switch position 13for inside-delta circuit at rotary coding switch on	40.2 A
switch position 14 • for inside-delta circuit at rotary coding switch on switch position 15	41.7 A
 switch position 15 for inside-delta circuit at rotary coding switch on switch position 16 	43.3 A
at inside-delta circuit minimum	19.9 A
minimum load [%]	15 %; Relative to smallest settable le
power loss [W] for rated value of the current at AC	
at 40 °C after startup	20 W
• at 50 °C after startup	19 W

at 60 °C after startup	18 W
power loss [W] at AC at current limitation 350 %	
 at 40 °C during startup 	376 W
 at 50 °C during startup 	318 W
at 60 °C during startup	278 W
Control circuit/ Control	
type of voltage of the control supply voltage	AC/DC
control supply voltage at AC	
at 50 Hz rated value	24 V
at 60 Hz rated value	24 V
relative negative tolerance of the control supply voltage at AC at 50 Hz	-20 % -
relative positive tolerance of the control supply voltage at AC at 50 Hz	20 %
relative negative tolerance of the control supply voltage at AC at 60 Hz	-20 %
relative positive tolerance of the control supply voltage at AC at 60 Hz	20 %
control supply voltage frequency	50 60 Hz
relative negative tolerance of the control supply voltage frequency	-10 %
relative positive tolerance of the control supply voltage frequency	10 %
control supply voltage	
at DC rated value	24 V
relative negative tolerance of the control supply voltage at DC	-20 %
relative positive tolerance of the control supply voltage at DC	20 %
control supply current in standby mode rated value	160 mA
holding current in bypass operation rated value	360 mA
locked-rotor current at close of bypass contact	0.75 A
maximum inrush current peak at application of control supply voltage maximum	3.3 A
duration of inrush current peak at application of control supply voltage	12.1 ms
design of the overvoltage protection	Varistor
design of short-circuit protection for control circuit	4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply
Inputs/ Outputs	
number of digital inputs	1
number of digital outputs	3
not parameterizable	2
digital output version	2 normally-open contacts (NO) / 1 changeover contact (CO)
number of analog outputs	0
switching capacity current of the relay outputs	
at AC-15 at 250 V rated value	3 A
• at DC-13 at 24 V rated value	1 A
Installation/ mounting/ dimensions	
mounting position	+/- 10° rotation possible and can be tilted forward or backward on vertical mounting surface
fastening method	screw fixing
height	275 mm
width	170 mm
depth	152 mm
required spacing with side-by-side mounting	
• forwards	10 mm
backwards	0 mm
• upwards	100 mm
downwards	75 mm
at the side	5 mm

weight without packaging	2.1 kg
Connections/ Terminals	
type of electrical connection	
for main current circuit	screw-type terminals
for control circuit	spring-loaded terminals
wire length for thermistor connection	
 with conductor cross-section = 0.5 mm² maximum 	50 m
 with conductor cross-section = 1.5 mm² maximum 	150 m
 with conductor cross-section = 2.5 mm² maximum 	250 m
type of connectable conductor cross-sections	
for main contacts	
— solid	2x (1.0 2.5 mm²), 2x (2.5 10 mm²)
 finely stranded with core end processing 	2x (1.0 2.5 mm²), 2x (2.5 6.0 mm²)
at AWG cables for main current circuit solid	2x (16 12), 2x (14 8)
type of connectable conductor cross-sections	
for control circuit solid	2x (0.25 1.5 mm²)
 for control circuit finely stranded with core end 	2x (0.25 1.5 mm²)
processing	
 at AWG cables for control circuit solid 	2x (24 16)
 at AWG cables for control circuit finely stranded with 	2x (24 16)
core end processing	
wire length	000
between soft starter and motor maximum	800 m
at the digital inputs at AC maximum	100 m
at the digital inputs at DC maximum	1 000 m
tightening torque	0.051
for main contacts with screw-type terminals	2 2.5 N·m
 for auxiliary and control contacts with screw-type terminals 	0.8 1.2 N·m
tightening torque [lbf·in]	
for main contacts with screw-type terminals	18 22 lbf·in
for auxiliary and control contacts with screw-type	7 10.3 lbf·in
terminals	1000
Ambient conditions	
installation altitude at height above sea level maximum	5 000 m; Derating as of 1000 m, see catalog
ambient temperature	
 during operation 	-25 +60 °C; Please observe derating at temperatures of 40 °C or
	above
during storage and transport	-40 +80 °C
environmental category	
 during operation according to IEC 60721 	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
 during storage according to IEC 60721 	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must
Garing storage according to IEO 00721	not get inside the devices), 1M4
 during transport according to IEC 60721 	2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)
EMC emitted interference	acc. to IEC 60947-4-2: Class A
Communication/ Protocol	
communication module is supported	
PROFINET standard	Yes
EtherNet/IP	Yes
Modbus RTU	Yes
Modbus TCP	Yes
PROFIBUS	Yes
UL/CSA ratings	
manufacturer's article number	
of circuit breaker	
— usable for Standard Faults at 460/480 V	Siemens type: 3RV2742, max. 70 A or 3VA51, max. 80 A; lq = 5 kA
according to UL	
usable for High Faults at 460/480 V according	Siemens type: 3RV2742, max.40 A or 3VA51, max. 60 A; lq max = 65
to UL — usable for Standard Faults at 460/480 V at	kA Siemens type: 3RV2742, max. 70 A or 3VA51, max. 80 A; lq = 5 kA
inside-delta circuit according to UL	Cicinolis type. Sixv2172, Illax. 10 A of SVAST, Illax. 60 A, Iq - 3 KA
<u> </u>	

- usable for High Faults at 460/480 V at inside-Siemens type: 3VA51, max. 60 A; Iq max = 65 kA delta circuit according to UL - usable for Standard Faults at 575/600 V Siemens type: 3RV2742, max. 70 A or 3VA51, max. 80 A; Iq = 5 kA according to UL - usable for Standard Faults at 575/600 V at Siemens type: 3RV2742, max. 70 A or 3VA51, max. 80 A; Iq = 5 kA inside-delta circuit according to UL • of the fuse - usable for Standard Faults up to 575/600 V Type: Class RK5 / K5, max. 100 A; Iq = 5 kA according to UL - usable for High Faults up to 575/600 V Type: Class J / L, max. 100 A; Iq = 100 kA according to UL - usable for Standard Faults at inside-delta Type: Class RK5 / K5, max. 100 A; Iq = 5 kA circuit up to 575/600 V according to UL — usable for High Faults at inside-delta circuit up Type: Class J / L, max. 100 A; Iq = 100 kA to 575/600 V according to UL operating power [hp] for 3-phase motors • at 200/208 V at 50 °C rated value 5 hp • at 220/230 V at 50 °C rated value 7.5 hp 15 hp • at 460/480 V at 50 °C rated value at 200/208 V at inside-delta circuit at 50 °C rated 10 hp value • at 220/230 V at inside-delta circuit at 50 °C rated 10 hp value • at 460/480 V at inside-delta circuit at 50 °C rated 25 hp contact rating of auxiliary contacts according to UL R300-B300 Safety related data protection class IP on the front according to IEC IP20

Certificates/ approvals

60529

General Product Approval

electromagnetic compatibility

EMC





touch protection on the front according to IEC 60529

Confirmation



in accordance with IEC 60947-4-2

finger-safe, for vertical contact from the front





Declaration of Conformity

Test Certificates

Marine / Shipping





Type Test Certificates/Test Report







Marine / Shipping

other





Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5215-3TC04

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5215-3TC04

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RW5215-3TC04

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RW5215-3TC04&lang=en

Characteristic: Tripping characteristics, I²t, Let-through current https://support.industry.siemens.com/cs/ww/en/ps/3RW5215-3TC04/char

Characteristic: Installation altitude

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RW5215-3TC04&objecttype=14&gridview=view1

Simulation Tool for Soft Starters (STS)

https://support.industry.siemens.com/cs/ww/en/view/101494917

last modified: 4/10/2022 🖸