

ANT-2.4-JJB-ST ✓ ACTIVE

TE Internal #: L9000080-01

Helical Antenna, Single Band, ISM / Zigbee / Bluetooth, Internal / Embedded Mount, Through-Hole/Tab Mount, Solder, Omnidirectional, Single Port

[View on TE.com >](#)



Antennas



Wireless Application: **Bluetooth, ISM, Zigbee**

Mounting Location: **Internal/Embedded**

Mounting Type: **Through-Hole/Tab Mount**

Antenna Termination: **Solder**

Antenna Type: **Helical**

Features

Product Type Features

Antenna Product Type	Antenna
Antenna Termination	Solder

Configuration Features

Antenna Style	Dome
Mounting Location	Internal/Embedded
Antenna Type	Helical
Band Type	Single Band
Port Configuration	Single Port

Electrical Characteristics

VSWR (Max)	<2.1:1
Impedance	50 Ω

Signal Characteristics

Frequency Band	2400 – 2485 MHz
Nominal Frequency Range	2400 – 2500
Peak Gain	< 0 dBi

Body Features

Product Weight	.44 g [.01552 oz]
----------------	-------------------



Mechanical Attachment

Polarization	Linear
Mounting Type	Through-Hole/Tab Mount

Dimensions

Product Width	7 mm[.28 in]
Product Length	17.6 mm[.69 in]
Product Height	0 mm[0 in]

Operation/Application

Directionality	Omnidirectional
----------------	-----------------

Industry Standards

Wireless Application	Bluetooth, ISM, Zigbee
Primary Application	Bluetooth, ISM, Zigbee

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # L9000079-01
Antenna Mini R-Angle 2.4GHz THM



TE Part # L9000099-01
Antenna 1/4 Wave 2.4GHz Coil Screw #10



TE Part # L9000103-01
Antenna uSP PCB RPC 2.4GHz SMT T&R



TE Part # 2445750-1
ANTENNA 2.4GHz HELICAL VERTICAL THM

Customers Also Bought



TE Part #2213748-1
COVER, LIGHT CONTROLLER, 76MM DIA, MEDIUM



TE Part #640457-2
02P MTA100 HDR ASSY SQ R/A F/L



TE Part #7-188275-4
MICRO-MATCH SMD FTE



TE Part #734185-1
WIRE STRIPPER .14-6.0mm2 ASSY



TE Part #1825910-6
FSM4JH=6MM TACT SWITCH, HIGH TEMP




TE Part #1954097-1
Poke In SMT, 2 Position Connect




TE Part #60940-1
.058 PIN REC 24-20 010PTPPHBZ



TE Part #327944
PIDG RECT 22-16COMM 22-18MIL 8



TE Part #1744382-4
04P MTA100 HDR ASSY, SM, SN, LF



TE Part #2232980-2
02P MTA100 HDR ASSY SM W SN

Documents

Product Drawings

[Antenna Mini 2.4GHz THM](#)

English

Datasheets & Catalog Pages

[Sub-6 Cellular LTE-5G NR Frequency Band Guide](#)

English



[ANT-2.4-JJB-xx](#)

English

[Virtual Antenna](#)

English

[Microslatch Ground Plane Optimization](#)

English