
Green Line Laser Module Fan Angle 60° Uniform Line

VLM-520-56-60°Series



The newly developed glass line lens come with various fan angles and they produce high quality uniform laser line in a robust stainless housing, ideal for automation, machine vision, image processing, digital data acquisition, counting, precision 3D scanner and science & medical application. They are available at 10 cm, 20 cm, 40 cm and 90 cm focus length, red & green wavelength, Class 1M and Class 2M laser class to cover within 1 meter range task. For customized focus length, wavelength and laser power output, please contact us.

FEATURES:

- Built with high precision glass line lens and glass laser collimating lens.
- Fan Angle : 60°
- Focus range: 10cm, 20cm, 40cm, 90cm, customized focus length are available by request.
- Customized focus within 1 meter available please direct contact us.
- Two laser power output level: LPO Class 1M laser product

LPT - Class 2M laser product


- Dimensions: Ø10 x 40 mm (Ø0.39" x 1.575")
- Wavelength: 515~530 nm
- 3~6 VDC operation.
- Connection type : Lead wire
- Laser line demonstration: https://www.youtube.com/watch?v=3 gRtxyeP28

APPLICATIONS: ideal for

- Machine vision.
- Automation industry.
- Image processing.
- Medical & Science.
- Scanning.
- Precision 3D scanner.
- Counting.
- Measurement.

VLM-520-56-60°Series

OUTLINE DIMENSIONS (UNITS: mm)



SPECIFICATIONS

Part Number		VLM-520-56 LPO-D60-			VLM-520-56 LPT-D60-				
	r art Number	F10	F20	F40	F90	F10	F20	F40	F90
1	Focus length	10 cm	20 cm	40 cm	90 cm	10 cm	20 cm	40 cm	90 cm
2	Fan angle / Laser line length		60°/L	.ength	of Lase	er Line	as TAI	BLE A	
3	Laser line width				AS TA	BLE B	ı		
4	Recommended working range				AS TA	BLE B	ı		
5	Dimensions		Ø1	10 x 40	mm (Ø	Ø0.39"	x 1.57	5")	
6	6 Weight				17:	±1g			
7	Operating voltage (Vop)				3~6	VDC			
8	Operating current (lop)	Le	ss thar	n 80m/	١	Les	ss than	180m	A
9	Optical power*	Le	ss thar	10mV	V	Le	ss thar	30mV	V
10	Laser power output**	Les	s than	0.39m	W	Le	ess tha	n 1mW	1
11	Laser class	Class 1M Class 2M		2M					
12	12 Wavelength (λp)		515~530nm						
13	Collimating lens / Line generating lens			Asp	herical	glass	lens		
14	Output aperture				8n	nm			
15	Beam shape				Li	ne			
16	Laser line accuracy			4	0"(±1m	m@5N	Л)		
17	Operating temp. range***				-20°C -	~+60°C)		
18	Storage temp. range				·20°C -	~+85°C)		
19	Housing material				Stainle	ss stee	el		
20	Potential of housing				Insu	lated			

VLM-520-56-60°Series

21	Electrostatic discharge (ESD)	30KV				
22	Moisture sensitivity level (MSL)	Level 1 - acc to JEDEC J-STD-020E.				
23	Wire type	2464 2-WIRE CABLE 26 AWG				
24	Cable length	330±30mm				
25	Mean time to failure (MTTF) 25°C	Above 10000 hrs				
26	International Protection Marking	IP67				
27	Application	Precision fine line for Automation, Machine vision and Medical				
28	Suggestion work distance	0~1.2 meters / 0~4 feet				

^{*} Optical power is total power output measured at the aperture of the laser.

- ** According to FDA 1040.10 & IEC 60825-1 regulations, laser power output is measured by 7mm aperture stop from a 10 cm distance of the laser.
- *** Operation temperature means within this temperature range, the laser spot/line will not be affected to change the spot size/line width. It can still work over this range, but the laser spot size or laser line width will be larger.

SAFETY LABEL


LPO:

LPT:

CLASS I LASER PRODUCT



TABLE A: Laser Line Length Table:



Length of laser line:

Distance	10 cm	20 cm	40 cm	100 cm
Fan angle	(4 inch)	(8 inch)	(16 inch)	(40 inch)
5°	0.9 cm	1.75 cm	3.5 cm	7.85 cm
	(0.35")	(0.7")	(1.4")	(3")
10°	1.75cm	3.5 cm	7 cm	17.5 cm
	(0.6")	(1.4")	(2.8")	(6")
15°	2.6 cm	5.2 cm	10.5 cm	26.3 cm
	(1")	(2")	(4")	(10")
20°	3.5 cm	7 cm	14 cm	35 cm
	(1.4")	(2.8")	(5.6")	(14")
30°	5.3 cm	10.7 cm	21 cm	53.5 cm
	(2")	(4")	(8")	(20")
45°	8.28 cm	16.6 cm	33.1 cm	82.85 cm
	(3¼")	(6½")	(13")	(32½")
60°	11.5 cm	23 cm	46 cm	115.5 cm
	(4½")	(9")	(18")	(45")
110°	28.6 cm	57.1 cm	114.2 cm	285.6 cm
	(11¼")	(23")	(46")	(112½")

VLM-520-56-60°Series




TABLE B: Recommended working range:

Focus at 10 cm:

Working range: 0 - 20cm(0-7.9")

Best at: 7 - 14.5cm(2.8"-5.7")

Laser Line Width <1mm

Laser Line Width <2mm

Laser		Recor	mmende	d Work	ing Ran	ge(cm)
Fan Angle		5	10	15	20	25
5°			6.5 -	16	-21	
10°			8 - 1	L5 -	19	
15°		6	- 8 - 1	L5 -	19	
20°		4-	7 - 1	.6	-21.5	
30°		4-	6 - 14.5		-21	
45°	0-		5.5 - 15	5 -	19	
60°	0-		7 - 14	.5	-20	
110°	0-		7 - 1	6.5	-22.5	

Focus at 40 cm:

Working range: 3 - 72cm(1.2"-28.3")

Best at: 20 - 58cm(7.9"-22.8") Laser Line Width <1mm Laser Line Width <2mm Laser Recommended Working Range(cm) Fan Angle 15 30 60 45 75 5° 20.5 - 57 10° 11.5- 22 - 47.5 -61.5 15° 21 - 53 -64 20° 30° 45° 60° 110°

Focus at 20 cm:

Working range: 11 - 32cm(4.3"-12.6")

Best at: 15 - 23.5cm(5.9"-9.3") Laser Line Width <1mm Laser Line Width <2mm

Laser	Recommended Working Range(cm)						
Fan Angle	10	15	20	25	30		
5°	1	12.5- 1	5 - 23	-26			
10°	10-	14	- 22	-26			
15°	10-	14.	5 - 22	-26			
20°	10-	14	.5 - 23	-27			
30°	10-	14	- 22	-26			
45°	9-	13	- 24		-34		
60°	11	- 15	5 - 23.5		-32		
110°	8-	12.5	- 23		-30		

Focus at 90 cm:

Working range: 35 - 145cm(13.8"-57")

Best at: 56 - 116cm(22"-45.7") Laser Line Width <1mm

Laser	Recommended Working Range(cm)							
Fan Angle	40	65	90	115	140			
5°	29-	45 - 9	91 -1	09				
10°	35-		57 - 119		-146			
15°	31-		57 - 119		-140			
20°	31-		59 - 12	2	-142			
30°	42-		50 - 114		-144			
45°	40-		55 - 120		-139			
60°	35-	5	66 - 116		-145			
110°	38-	60) - 106	-1	34			

Laser Line Width <1mm
Laser Line Width <2mm

Headquarter

QUARTON INC.

Tel: 886-2-2648-5656 Fax: 886-2-2648-5522 contact@quarton.com www.quarton.com USA

QUARTON USA INC.

Cell: 210-837-3485 contact@quarton.com www.quarton.com

Optional Accessories

Quarton offers mounts, power supply boards, battery pack and USB cable switch to help you running as quickly as possible. For more information, please visit www.quarton.com, www.guarton.com, www.guarton.com, www.guarton.com, <a href="https://

QLM-1125 - Laser Module Mount/Holder for diameter 6mm to 12.5mm, it's an ideal choose for mounted onto optical tables.

Feature:

- 4 directions adjustable.
- Can be mounted onto the optical table with screws (Screws not included).
- Engraved scale for precision adjustable.



LMPS-MP1 - Multi-function Laser Module Power Supply Board. Four input: USB, micro USB, DC Power Jack(5.5 x 2.1), and terminal block. Two channel output: 7 VDC 500mA and 5 VDC 1A. Three switches-toggle switch, remote switch and TTL signal.




Feature:

- Allow four kinds of power input: USB, micro USB, DC Power Jack(5.5x2.1) and terminal block.
- Two Channel output: 7 VDC 500mA and 5 VDC 1A.
- Built-in three switches: toggle switch, terminal block remote switch and TTL signal switch by on-board connect point.
- 7 VDC output work for all Quarton Laser Modules with 7-12 V operation Voltage (Vop).
- 5 VDC output work for all Quarton Laser Modules with 3-6 V operation Voltage (Vop).
- Three LED indicators: Input power indicator, 7V output indicator and 5V output indicator.

USA

Optional Accessories



LMPS-MP2 - DC converter, In: 9-36V, Out: 5V 1A.



LMPS-mUSB1 - Laser Module Power Supply Board, Input: micro USB, Output: 5 VDC 500mA.

Feature:

- Micro USB connector power input.
- Output 5 VDC 500mA with alligator clips.
- For all Quarton Laser Modules that require 3-6V operation Voltage.



LMPS-DC1 - Laser Module Power Supply Board, Input: DC Power Jack(5.5 x 2.1), Output: 5 VDC 500mA.

Feature:

- DC Power Jack(5.5 x 2.1) power input.
- Output 5 VDC 500mA with alligator clips.
- For all Quarton Laser Modules that require 3-6V operation voltage.

Optional Accessories



CLM-BP4N3 - Battery pack (4* AA batteries)

*** AA Batteries are **NOT** included in package.

Feature:

USB Output Voltage: 5 VDC.

Color: Black.



CLM-USBSW - USB Cable Switch.

Feature:

Length: 28cm.

Color: Black.



CLM-UM3M - USB to micro USB Cable.

Feature:

Length: 3 meters.

· Color: Black.