

#### Description

The IRF7201PBF uses advanced trench technology to provide excellent  $R_{DS(ON)}$ , low gate charge and operation with gate voltages as low as 4.5V. This device is suitable for use as a Battery protection or in other Switching application.

### **General Features**

V<sub>DS</sub> = 30V I<sub>D</sub> =8.5A

 $R_{DS(ON)}$  < 18m $\Omega$  @ V<sub>GS</sub>=10V


### Application

Battery protection

Load switch Uninterruptible power supply



SOP-8



N-Channel MOSFET

### Package Marking and Ordering Information

Product ID	Pack	Brand	Qty(PCS)
IRF7201PBF	SOP-8	HXY MOSFET	3000

# Absolute Maximum Ratings (T\_A = 25 $^\circ C$ unless otherwise noted)

Symbol	Parameter	Rating	Units
Vds	Drain-Source Voltage	30	V
Vgs	Gate-Source Voltage	Gate-Source Voltage ±20	
I <sub>D</sub> @T <sub>A</sub> =25°C	Continuous Drain Current <sup>1</sup>	Continuous Drain Current <sup>1</sup> 8.5	
I <sub>D</sub> @T <sub>A</sub> =70°C	Continuous Drain Current <sup>1</sup>	5.6	А
Ідм	Pulsed Drain Current <sup>2</sup>	35	А
EAS	Single Pulse Avalanche Energy <sup>3</sup>	le Pulse Avalanche Energy <sup>3</sup> 20	
las	Avalanche Current	20	А
P <sub>D</sub> @T <sub>A</sub> =25°C	Total Power Dissipation <sup>4</sup>	pation <sup>4</sup> 1.5	
Тятд	Storage Temperature Range	-55 to 150	°C
TJ	Operating Junction Temperature Range	-55 to 150	°C
R <sub>eja</sub>	Thermal Resistance Junction-ambient¹(t≤10s)	85	°C/W
	Thermal Resistance Junction-ambient <sup>1</sup>	25	°C/W



Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit	
BV <sub>DSS</sub>	Drain-Source Breakdown Voltage	V <sub>GS</sub> =0V , I <sub>D</sub> =250uA	30			V	
$\bigtriangleup BV_{\text{DSS}} / \bigtriangleup T_{\text{J}}$	BVDSS Temperature Coefficient	Reference to 25°C,I₀=1mA		0.034		V/°C	
R <sub>DS(ON)</sub>	Static Drain-Source On-Resistance <sup>2</sup>	V <sub>GS</sub> =10V , I <sub>D</sub> =7A		14	18	mΩ	
	Static Drain-Source On-Resistance	V <sub>GS</sub> =4.5V , I <sub>D</sub> =4A		20	26		
V <sub>GS(th)</sub>	Gate Threshold Voltage		1.2	1.5	2.5	V	
$ riangle V_{GS(th)}$	V <sub>GS(th)</sub> Temperature Coefficient	──V <sub>GS</sub> =V <sub>DS</sub> , I <sub>D</sub> =250uA		-3.84		mV/°C	
1	Drain-Source Leakage Current	V <sub>DS</sub> =24V , V <sub>GS</sub> =0V , T <sub>J</sub> =25°C			1	- uA	
IDSS		V <sub>DS</sub> =24V , V <sub>GS</sub> =0V , T <sub>J</sub> =55°C			5		
lgss	Gate-Source Leakage Current	V <sub>GS</sub> =±20V , V <sub>DS</sub> =0V			±100	nA	
gfs	Forward Transconductance	V <sub>DS</sub> =5V , I <sub>D</sub> =7A		6.2		S	
R <sub>g</sub>	Gate Resistance	V <sub>DS</sub> =0V , V <sub>GS</sub> =0V , f=1MHz		1.04	2.1	Ω	
Qg	Total Gate Charge (4.5V)			6	8.4		
$Q_gs$	Gate-Source Charge	V <sub>DS</sub> =15V , V <sub>GS</sub> =4.5V , I <sub>D</sub> =7A		2.2	3.1	nC	
$Q_{gd}$	Gate-Drain Charge			2	2.8		
T <sub>d(on)</sub>	Turn-On Delay Time			1.2	2.4		
Tr	Rise Time	$V_{DD}$ =15V , $V_{GS}$ =10V , $R_G$ =3.3 $\Omega$		40	72.0	ns	
T <sub>d(off)</sub>	Turn-Off Delay Time	I <sub>D</sub> =7A		18	36.0		
T <sub>f</sub>	Fall Time			7.2	14.4		
Ciss	Input Capacitance			583	816.2		
Coss	Output Capacitance	V <sub>DS</sub> =15V , V <sub>GS</sub> =0V , f=1MHz		77	107.8	pF	
C <sub>rss</sub>	Reverse Transfer Capacitance			59	82.6		
ls	Continuous Source Current <sup>1,5</sup>				7	А	
lsм	Pulsed Source Current <sup>2,5</sup>	──V <sub>G</sub> =V <sub>D</sub> =0V , Force Current			35	А	
$V_{\text{SD}}$	Diode Forward Voltage <sup>2</sup>	V <sub>GS</sub> =0V , I <sub>S</sub> =1A , T <sub>J</sub> =25°C			1.2	V	
t <sub>rr</sub>	Reverse Recovery Time			7.2		nS	
Qrr	Reverse Recovery Charge	I⊧=7A , dI/dt=100A/µs , Tյ=25°C		2.9		nC	

## Electrical Characteristics (TJ=25 °C, unless otherwise noted)

Note :


1. The data tested by surface mounted on a 1 inch<sup>2</sup> FR-4 board with 2OZ copper.

2.The data tested by pulsed , pulse width  $\,\leq\,$  300us , duty cycle  $\,\leq\,$  2%


3. The EAS data shows Max. rating . The test condition is  $V_{DD}$ =25V,  $V_{GS}$ =10V, L=0.1mH, I<sub>AS</sub>=20A

4.The power dissipation is limited by 150°C junction temperature

5. The data is theoretically the same as  $I_D$  and  $I_{DM}$ , in real applications, should be limited by total power dissipation.



### **Typical Characteristics**



**Fig.1 Typical Output Characteristics** 




Fig.3 Forward Characteristics Of Reverse




Fig.5 Normalized  $V_{\text{GS}(\text{th})}$  vs.  $T_{\text{J}}$ 




Fig.2 On-Resistance vs. Gate-Source




Fig.4 Gate-Charge Characteristics




Fig.6 Normalized R<sub>DSON</sub> vs. T<sub>J</sub>






Fig.9 Normalized Maximum Transient Thermal Impedance




Fig.10 Switching Time Waveform







Fig.11 Unclamped Inductive Switching Waveform




# SOP-8 Package Outline Dimensions







Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
Α	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.013	0.020
с	0.170	0.250	0.007	0.010
D	4.800	5.000	0.189	0.197
e	1.270 (BSC)		0.050 (BSC)	
E	5.800	6.200	0.228	0.244
E1	3.800	4.000	0.150	0.157
L	0.400	1.270	0.016	0.050
θ	0 °	8°	0 °	8°



Note: 1.Controlling dimension: in millimeters.

2.General tolerance:± 0.05mm.
 3.The pad layout is for reference purposes only.



### **Attention**

Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.

• HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.

• Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

• HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could

give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

• In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

• No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.

Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production.
HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.