




DEUTSCH

TE Internal #: YCTJ120E02CC015000

Terminal Junction Modules, Bussing Module, 12 Position, Sealable, DIN Rail, -85 – 392 °F [-65 – 200 °C]

[View on TE.com >](#)

Connectors > Terminal Junction Modules & Accessories > Terminal Junction Modules



Terminal Junction System Component Type: **Bussing Module**

Compatible With Contact Size: **20**

Connector System: **Wire-to-Wire**

Number of Positions: **12**

Sealable: **Yes**

Features

Product Type Features

Terminal Junction System Component Type	Bussing Module
Connector System	Wire-to-Wire
Sealable	Yes

Configuration Features

Number of Positions	12
---------------------	----

Contact Features

Contact Base Material	Copper Alloy
Compatible With Contact Size	20
Contact Current Rating (Max)	7.5 A

Mechanical Attachment

Connector Mounting Type	DIN Rail
-------------------------	----------

Usage Conditions

Operating Temperature Range	-65 – 200 °C[-85 – 392 °F]
-----------------------------	----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023 (235)

Candidate List Declared Against: JUNE 2022 (224)

SVHC > Threshold:

Pb (2.5% in Contact Lead Copper Alloy)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability


Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought





Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_YCTJ120E02CC015000_99.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_YCTJ120E02CC015000_99.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_YCTJ120E02CC015000_99.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.