



Inductors for Power Circuits

Wound Metallic Magnetic Material

SPM Series

SPM5012 Type

SPM5012



The products in this catalog will be or have been stopped production

Discontinue Issue Date	Jun. 3, 2022
Last Purchase Order Date	Sep. 30, 2023
Last Shipment Date	Mar. 31, 2024

Please refer to our Web site about replacement information.



REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

	⚠ REMINDERS
or less).	od is less than 12 months. Be sure to follow the storage conditions (Temperature: 5 to 40°C, Humidity: 10 to 75% R riod elapses, the soldering of the terminal electrodes may deteriorate.
Do not use or sto	ore in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
_	, be sure to preheat components. emperature should be set so that the temperature difference between the solder temperature and chip temperature 150°C.
•	tions after mounting should be within the range of the conditions determined in the specifications. short circuit, performance deterioration, or lifespan shortening may occur.
	g a printed circuit board where a chip <mark>is mounted to</mark> a set, b <mark>e sure that residual stress is</mark> not given to the chip due to tion of the printed circuit board an <mark>d partial distortion such as at</mark> screw tightening portions.
Self heating (tem design.	perature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal
• •	the coil for the circuit boar <mark>d design of the non-magnetic shield type.</mark> ay occur due to magne <mark>tic interference.</mark>
Use a wrist band	to discharge static electricity in your body through the grounding wire.
Do not expose th	ne products to magnets or magnetic fields.
Do not use for a	purpose outside of the contents reg <mark>ulated in the delivery specific</mark> ations.
equipment, home equipment, indus The products are	ed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications e appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement strial robots) under a normal operation and use condition. In not designed or warranted to meet the requirements of the applications listed below, whose performance and/or more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment

set forth in the each catalog, please contact us.

- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.

If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions

INDUCTORS &TE

Inductors for Power Circuits

Wound Metallic Magnetic Material

Product compatible with RoHS directive
Halogen-free
Compatible with lead-free solders

Overview of SPM5012 Type

FEATURES

- O Magnetic shield type wound inductor for power circuits using a metallic magnetic material.
- O Low-profile product.
- Ocompared to ferrite wound type inductors, it is possible to achieve large current, low Rdc, and compactness.
- Low inductance variance in high-temperature environments with good DC superimposition characteristics.
- O Metallic magnetic material is used, and the structure has an integrated molded coil, so hum noise is lower than with core adhesive coils.

APPLICATION

Smart phones, tablet terminals, laptop computers, HDDs, servers, VRMs, compact power supply modules, other

■ PART NUMBER CONSTRUCTION



■ OPERATING TEMPERATURE RANGE, PACKAGE QUANTITY, PRODUCT WEIGHT

	Temperat	ure range	Package quantity	Individual weight	
Type Operating temperature*		Storage temperature**			
	(*C)	(°C)	(pieces/reel)	(g)	
SPM5012	-40 to +125	-40 to +125	1000	0.1500	

^{*} Operating temperature range includes self-temperature rise.


ORAMS Directive Compliant Product: See the following for more details related to RoHS Directive compliant products. http://product.tdk.com/en/environment/rohs/Dalagen-free: Indicates that CI content is less than 900ppm, Br content is less than 900ppm, and that the total CI and Br content is less than 1500ppm.

^{**} The Storage temperature range is for after the circuit board is mounted.




SPM5012 Type

■ RECOMMENDED REFLOW PROFILE



Preheati	ng		Soldering		Peak		
Temp.		Time	Temp. T	ime	Temp.	Time	
T1	T2	t1	T3 ta	2	T4	t3	
150°C	180°C	120s	230°C 3	80s	260°C	10s max.	



N D SPM5012 Type ■SHAPE & DIMENSIONS 5.4±0.2 1.2±0.1 Dimensions in mm ■ RECOMMENDED LAND PATTERN Dimensions in mm

Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.



SPM5012 Type

ELECTRICAL CHARACTERISTICS

□ CHARACTERISTICS SPECIFICATION TABLE

L		L measuring frequency	DC resistance Rated current*			Part No.		
(μH)	Tolerance	(kHz)	(mΩ)max.	(m Ω)typ.	ldc1 (A)max.	ldc1 (A)typ.	ldc2 (A)typ	p
1.00	±20%	100	44.0	40.0	5.9	7.9	4.1	SPM5012T-1R0M
2.20	±20%	100	78.8	71.6	4.6	6.1	2.7	SPM5012T-2R2M

* Rated current: smaller value of either ldc1 or ldc2.


Idc1: When based on the inductance change rate (30% below the initial value)

Idc2: When based on the temperature increase (Temperature increase of 40°C by self heating)

 \bigcirc Measurement equipment

Measurement item	Product No.	Manufacturer
L	4284A	Agilent Technologie <mark>s</mark>
DC resistance	AX-111A	ADEX
Rated current Idc1	4284A+42841A+42842C	Agilent Technologies

 $\begin{tabular}{ll} * Equivalent measurement equipment may be used. \end{tabular}$



N D 0 R S SPM5012 Type **ELECTRICAL CHARACTERISTICS** ☐ L FREQUENCY CHARACTERISTICS GRAPH 6.0 Inductance (μH) 4.0 2R2M 1R0M 0.0 0.1 10 100 Frequency (MHz) $\bigcirc \ {\it Measurement equipment}$ Manufacturer 4294A Agilent Technologies * Equivalent measurement equipment may be used.


Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.

INDUCTORS &TDK

SPM5012 Type

ELECTRICAL CHARACTERISTICS

□INDUCTANCE VS. DC BIAS CHARACTERISTICS GRAPH



O Measurement equipment

Product No. Manufacturer
4284A+42841A+42842C Agilent Technologies

Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.


^{*} Equivalent measurement equipment may be used.



SPM5012 Type

■PACKAGING STYLE


□REEL DIMENSIONS



* These values are typical values.

Type A Ø 178

TAPE DIMENSIONS





Dimensions in mm

Type	Α	В	øD0	E	F	P0	P1	P2	W	K	t
SPM5012	5.4	5.7	1.5+0.1/-0	1.75±0.1	5.5±0.1	4.0±0.1	8.0±0.1	2.0±0.1	12.0±0.2	1.5	0.3