## **SIEMENS**

Data sheet 3RM1102-1AA14



Fail-safe direct starter, 3RM1, 500 V, 0.09 - 0.75 kW, 0.4 - 2 A, 110-230 V AC, screw terminals

product brand name	SIRIUS	
product category	Motor starter	
product designation	Fail-safe direct starter	
design of the product	With electronic overload protection and safety-related disconnection	
product type designation	3RM1	
General technical data		
trip class	CLASS 10A	
equipment variant according to IEC 60947-4-2	3	
product function	fail-safe direct starter	
<ul> <li>intrinsic device protection</li> </ul>	Yes	
<ul> <li>for power supply reverse polarity protection</li> </ul>	Yes	
suitability for operation device connector 3ZY12	No	
insulation voltage rated value	500 V	
overvoltage category	III	
surge voltage resistance rated value	6 kV	
maximum permissible voltage for safe isolation		
<ul> <li>between main and auxiliary circuit</li> </ul>	500 V	
<ul> <li>between control and auxiliary circuit</li> </ul>	250 V	
shock resistance	6g / 11 ms	
vibration resistance	1 6 Hz, 15 mm; 20 m/s², 500 Hz	
operating frequency maximum	1 1/s	
mechanical service life (switching cycles) typical	15 000 000	
reference code according to IEC 81346-2	Q	
Substance Prohibitance (Date)	03/01/2017	
product function		
direct start	Yes	
<ul> <li>reverse starting</li> </ul>	No	
product function short circuit protection	No	
Electromagnetic compatibility		
EMC emitted interference according to IEC 60947-1	class A	
EMC immunity according to IEC 60947-1	Class A	
conducted interference		
<ul> <li>due to burst according to IEC 61000-4-4</li> </ul>	3 kV / 5 kHz	
<ul> <li>due to conductor-earth surge according to IEC 61000-4-5</li> </ul>	4 kV signal lines 2 kV	
<ul> <li>due to conductor-conductor surge according to IEC 61000-4-5</li> </ul>	2 kV	
<ul> <li>due to high-frequency radiation according to IEC 61000-4-6</li> </ul>	10 V	
field-based interference according to IEC 61000-4-3	10 V/m	

electrostatic discharge according to IEC 61000-4-2	6 kV contact discharge / 8 kV air discharge	
conducted HF interference emissions according to		
CISPR11	Class B for domestic, business and commercial environments; Class A for industrial environments at 110 V DC	
field-bound HF interference emission according to CISPR11	Class B for domestic, business and commercial environments; Class A for industrial environments at 110 V DC	
Safety related data		
safety device type according to IEC 61508-2	Туре В	
Safety Integrity Level (SIL) according to IEC 61508	3	
SIL Claim Limit (subsystem) according to EN 62061	SILCL 3	
performance level (PL) according to EN ISO 13849-1	e	
category according to EN ISO 13849-1	4	
stop category according to EN 60204-1	0	
Safe failure fraction (SFF)	99.4 %	
average diagnostic coverage level (DCavg)	99 %	
diagnostics test interval by internal test function maximum	600 s	
function test interval maximum	1 y	
failure rate [FIT]		
<ul> <li>at rate of recognizable hazardous failures (λdd)</li> </ul>	1 400 FIT	
<ul> <li>at rate of non-recognizable hazardous failures (λdu)</li> </ul>	16 FIT	
PFHD with high demand rate according to EN 62061	0.00000002 1/h	
PFDavg with low demand rate according to IEC 61508	0.000018	
MTTFd	75 y	
hardware fault tolerance according to IEC 61508	1	
safe state	Load circuit open	
protection class IP on the front according to IEC 60529	IP20	
touch protection on the front according to IEC 60529	finger-safe	
hardware fault tolerance according to IEC 61508 relating to ATEX	0	
PFDavg with low demand rate according to IEC 61508 relating to ATEX	0.0005	
PFHD with high demand rate according to EN 62061 relating to ATEX	0.00000005 1/h	
Safety Integrity Level (SIL) according to IEC 61508 relating to ATEX	SIL2	
T1 value for proof test interval or service life according to IEC 61508 relating to ATEX	3 y	
Main circuit		
number of poles for main current circuit	3	
design of the switching contact	Hybrid	
adjustable current response value current of the	0.4 2 A	
current-dependent overload release	20 % from not rated gurrent	
minimum load [%]	20 %; from set rated current	
type of the motor protection	solid-state 48 500 V	
operating voltage rated value  relative symmetrical tolerance of the operating voltage	10 %	
operating frequency 1 rated value	50 Hz	
operating frequency 2 rated value	60 Hz	
relative symmetrical tolerance of the operating frequency	10 %	
operational current		
at AC at 400 V rated value	2 A	
• at AC-3 at 400 V rated value	2 A	
at AC-53a at 400 V at ambient temperature 40 °C rated value	2 A	
ampacity when starting maximum	16 A	
operating power for 3-phase motors at 400 V at 50 Hz	0.09 0.75 kW	
nputs/ Outputs		
input voltage at digital input		
<ul> <li>at DC rated value</li> </ul>	110 V	

• for signal <1> at DC	79 121
input voltage at digital input	
<ul> <li>at AC rated value</li> </ul>	110 V
<ul><li>with signal &lt;0&gt; at AC</li></ul>	0 40 V
• for signal <1> at AC	93 253 V
input current at digital input	
• for signal <1> at DC	1.5 mA
with signal <0> at DC	0.25 mA
input current at digital input with signal <0> at AC	
• at 110 V	0.2 mA
• at 230 V	0.4 mA
input current at digital input for signal <1> at AC	
• at 110 V	1.1 mA
• at 230 V	2.3 mA
number of CO contacts for auxiliary contacts	1
operational current of auxiliary contacts at AC-15 at	3 A
230 V maximum	
operational current of auxiliary contacts at DC-13 at 24 V maximum	1 A
Control circuit/ Control	
type of voltage of the control supply voltage	AC/DC
control supply voltage at AC	
• at 50 Hz rated value	110 230 V
at 60 Hz rated value	110 230 V
relative negative tolerance of the control supply	15 %
voltage at AC at 60 Hz	
relative positive tolerance of the control supply voltage at AC at 60 Hz	10 %
control supply voltage 1 at AC	
● at 50 Hz	110 230 V
● at 60 Hz	110 230 V
control supply voltage frequency	
• 1 rated value	50 Hz
2 rated value	60 Hz
relative negative tolerance of the control supply voltage at DC	15 %
relative positive tolerance of the control supply voltage at DC	10 %
control supply voltage 1 at DC rated value	110 V
operating range factor control supply voltage rated value at DC	
• initial value	0.85
• full-scale value	1.1
operating range factor control supply voltage rated value at AC at 50 Hz	
• initial value	0.85
• full-scale value	1.1
operating range factor control supply voltage rated value at AC at 60 Hz	
• initial value	0.85
• full-scale value	1.1
control current at AC	
<ul> <li>at 110 V in standby mode of operation</li> </ul>	8 mA
• at 230 V in standby mode of operation	6 mA
at 110 V when switching on	40 mA
at 230 V when switching on	25 mA
at 110 V during operation	25 mA
at 230 V during operation	14 mA
control current at DC	
in standby mode of operation	4 mA
when switching on	13 mA
during operation	30 mA
• during operation	OO HILL

inrush current peak	
• at AC at 110 V	1 200 mA
• at AC at 230 V	2 900 mA
duration of inrush current peak	
• at AC at 110 V	1 ms
• at AC at 230 V	1 ms
power loss [W] in auxiliary and control circuit	
• in switching state OFF	
— with bypass circuit	1.4 W
• in switching state ON	
— with bypass circuit	3.22 W
Response times	
ON-delay time	90 120 ms
OFF-delay time	60 90 ms
	00 90 IIIS
Power Electronics	
operational current	
• at 40 °C rated value	2 A
• at 50 °C rated value	2 A
• at 55 °C rated value	2 A
at 60 °C rated value	2 A
Installation/ mounting/ dimensions	
mounting position	vertical, horizontal, standing (observe derating)
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail
height	100 mm
width	22.5 mm
depth	141.6 mm
required spacing	
with side-by-side mounting	
— forwards	0 mm
— backwards	0 mm
— upwards	50 mm
— downwards	50 mm
— at the side	0 mm
for grounded parts	<b>v</b>
— forwards	0 mm
— backwards	0 mm
— upwards	50 mm
— at the side	3.5 mm
— downwards	50 mm
Ambient conditions	
installation altitude at height above sea level maximum	4 000 m; For derating see manual
ambient temperature	
<ul><li>during operation</li></ul>	-25 +60 °C
<ul><li>during storage</li></ul>	-40 +70 °C
during transport	-40 +70 °C
environmental category during operation according to IEC	3K6 (no ice formation, only occasional condensation), 3C3 (no salt
60721	mist), 3S2 (sand must not get into the devices), 3M6
relative humidity during operation	10 95 %
air pressure according to SN 31205	900 1 060 hPa
Communication/ Protocol	
protocol is supported	
<ul> <li>PROFINET IO protocol</li> </ul>	No
PROFIsafe protocol	No
product function bus communication	No
protocol is supported AS-Interface protocol	No
Connections/ Terminals	
type of electrical connection	screw-type terminals for main circuit, screw-type terminals for control
••	circuit
for main current circuit	screw-type terminals
<ul> <li>for auxiliary and control circuit</li> </ul>	screw-type terminals
-	

wire length for motor unshielded maximum	100 m	
type of connectable conductor cross-sections		
for main contacts		
— solid	1x (0,5 4 mm²), 2x (0,5 2,5 mm²)	
<ul> <li>finely stranded with core end processing</li> </ul>	1x (0,5 4 mm²), 2x (0,5 1,5 mm²)	
<ul> <li>at AWG cables for main contacts</li> </ul>	1x (20 12), 2x (20 14)	
connectable conductor cross-section for main contacts		
<ul> <li>solid or stranded</li> </ul>	0.5 4 mm²	
<ul> <li>finely stranded with core end processing</li> </ul>	0.5 4 mm²	
connectable conductor cross-section for auxiliary contacts		
<ul> <li>solid or stranded</li> </ul>	0.5 2.5 mm²	
<ul> <li>finely stranded with core end processing</li> </ul>	0.5 2.5 mm²	
type of connectable conductor cross-sections		
<ul> <li>for auxiliary contacts</li> </ul>		
— solid	1x (0,5 2,5 mm²), 2x (1,0 1,5 mm²)	
<ul> <li>finely stranded with core end processing</li> </ul>	1x (0.5 2.5 mm²), 2x (0.5 1 mm²)	
<ul> <li>at AWG cables for auxiliary contacts</li> </ul>	1x (20 14), 2x (18 16)	
AWG number as coded connectable conductor cross section		
for main contacts	20 12	
<ul> <li>for auxiliary contacts</li> </ul>	20 14	
JL/CSA ratings		
yielded mechanical performance [hp]		
<ul> <li>for single-phase AC motor</li> </ul>		
— at 230 V rated value	0.125 hp	
<ul> <li>for 3-phase AC motor</li> </ul>		
<ul> <li>at 200/208 V rated value</li> </ul>	0.333 hp	
— at 220/230 V rated value	0.333 hp	
— at 460/480 V rated value	0.75 hp	
operating voltage at AC		
<ul> <li>according to UL rated value</li> </ul>	480 V	
<ul> <li>according to CSA rated value</li> </ul>	400 V	
Certificates/ approvals		
General Product Approval		EMC



Confirmation









**Functional** For use in hazard-**Declaration of** Safety/Safety of **Test Certificates** other Railway ous locations Conformity Machinery



Type Examination Certificate



Type Test Certificates/Test Report

Confirmation

**Special Test Certific-**<u>ate</u>

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RM1102-1AA14


Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RM1102-1AA14

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RM1102-1AA14

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)



last modified: 6/21/2022 🖸