






REV	REVISION RECORD	ECN DRAWN	DATE




- 1.MATERIAL:  
 1.1 INSULATOR: LCP, UL94V-0; COLOR: NATURE.  
 1.2 CONTACT: BRASS, T=0.20mm  
 1.3 SHELL: BRASS, T=0.20mm  
 2.FINISH:  
 2.1 CONTACT: GOLD FLASH PLATED IN CONTACT AREA ; 50u" MIN. TIN PLATED IN SOLDER AREA 30u" MIN. NICKEL UNDERPLATED OVERALL.  
 2.2 SHELL: 50u" MIN. NICKEL PLATED OVERALL.  
 3.ELECTRICAL CHARACTERISTICS  
 3.1 CURRENT RATING: AC/DC 0.5A.  
 3.2 CONTACT RESISTANCE: 20mΩ MAX.  
 3.3 INSULATION RESISTANCE: 100MΩ MIN DC 500V.  
 3.4 DIELECTRIC WITHSTANDING VOLTAGE: AC 500V PER MINUTE.  
 3.5 OPERATING TEMPERATURE: -25°C ~ +85°C.  
 4.NOTES:  
 4.1 THIS COMPONENT AND ITS HOMOGENEOUS SUBCOMPONENTS ARE RoHS2.0 COMPLIANT.  
 4.2 RESISTANCE TO SOLDERING HEAT: IR ReFlow 265±5°C FOR 10 SECONDS.  
 4.3 COPLANARITY IS 0.1MM MAX



RECOMMENDED P.C.B HOLE LAYOUT  
 COMPONENT SIDE VIEW(TOLERANCE: +/-0.05)

CIRCUIT:



TOLERANCES: X.X ±0.3 X.XX ±0.25 X.XXX ±0.15 GENERAL ANGLE: X.X ±2° X.XX ±1°	TITLE: SD CARD NO PUSH SMT LONG TYPE	深圳市金航标电子有限公司	www.kinghelm.com.cn
	DRAWN: <i>No.wan</i>	UNITS: mm	KH-SD2825-B
	CHECKED: <i>YingJianJun</i>	SCALE: 1.8:1	PART NO: 10121-001
	APPROVAL: <i>YingJianJun</i>	REV: A/0	DRAWING NO: C-10121-001
			SHEET NO: 1 OF 1

ÓÉ Foxit PDF Editor ±â¼-  
 °æÈ"ËüÖÐ (c) by Foxit Software Company, 2004  
 ½ö0ÁÖU/EA'A½