SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3230-1YH40-0AB0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Rated data		
Input		
Number of phases	3 AC	
Line voltage	500 690 V +10 %	6 -20 %
Line frequency	47 63 Hz	
Rated voltage	690V IEC	600V NEC
Rated current (LO)	59.00 A	59.00 A
Rated current (HO)	54.40 A	54.40 A
Output		
Number of phases	3 AC	
Rated voltage	690V IEC	600V NEC 1)
Rated power (LO)	55.00 kW	60.00 hp
Rated power (HO)	45.00 kW	50.00 hp
Rated current (LO)	62.00 A	62.00 A
Rated current (HO)	52.00 A	52.00 A
Rated current (IN)	64.00 A	
Max. output current	84.00 A	
Pulse frequency	2 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	
Overlead capability		

Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor λ	0.90 0.95	
Offset factor $\cos \phi$	0.99	
Efficiency η	0.98	
Sound pressure level (1m)	70 dB	
Power loss 3)	1.360 kW	
Filter class (integrated)	RFI suppression filter for Category C2	
EMC category (with accessories)	Category C2	
Safety function "Safe Torque Off"	without SIRIUS device (e.g. via S7- 1500F)	
Communication		

Communication

USS, Modbus RTU, BACnet MS/TP

ltem no. : Consignment no. : Project :

Inputs /	outputs
Standard digital inputs	
Number	6
Switching level: $0 \rightarrow 1$	11 V
Switching level: $1 \rightarrow 0$	5 V
Max. inrush current	15 mA
Fail-safe digital inputs	
Number	1
Digital outputs	
Number as relay changeover contact	2
Output (resistive load)	DC 30 V, 5.0 A
Number as transistor	0
Analog / digital inputs	
Number	2 (Differential input)
Resolution	10 bit
Switching threshold as digital input	
0 → 1	4 V
1 → 0	1.6 V
Analog outputs	
Number	1 (Non-isolated output)
PTC/ KTY interface	
1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5\ ^\circ C$	
Closed-loop co	ntrol techniques

Closed-loop cor	itroi techniques
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No

SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3230-1YH40-0AB0

Ambient conditions		
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002	
Cooling	Air cooling using an integrated fan	
Cooling air requirement	0.083 m³/s (2.931 ft³/s)	
Installation altitude	1,000 m (3,280.84 ft)	
Ambient temperature		
Operation	-20 45 °C (-4 113 °F)	
Transport	-40 70 °C (-40 158 °F)	
Storage	-25 55 °C (-13 131 °F)	
Relative humidity		
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible	
Connections		
Signal cable		
Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 16)	
Line side		
Line side Version	screw-type terminal	
	screw-type terminal 25.00 70.00 mm² (AWG 6 AWG 3/0)	
Version	25.00 70.00 mm ²	
Version Conductor cross-section	25.00 70.00 mm ²	
Version Conductor cross-section Motor end	25.00 70.00 mm² (AWG 6 AWG 3/0)	
Version Conductor cross-section Motor end Version	25.00 70.00 mm ² (AWG 6 AWG 3/0) Screw-type terminals 25.00 70.00 mm ²	
Version Conductor cross-section Motor end Version Conductor cross-section	25.00 70.00 mm ² (AWG 6 AWG 3/0) Screw-type terminals 25.00 70.00 mm ²	
Version Conductor cross-section Motor end Version Conductor cross-section DC link (for braking resistor)	25.00 70.00 mm ² (AWG 6 AWG 3/0) Screw-type terminals 25.00 70.00 mm ² (AWG 6 AWG 3/0)	

Ме	chanical data
Degree of protection	IP20 / UL open type
Frame size	FSE
Net weight	28.7 kg (63.27 lb)
Dimensions	
Width	275 mm (10.83 in)
Height	551 mm (21.69 in)
Depth	248 mm (9.76 in)
	Standards
Compliance with standards	UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH
CE marking	EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC
Converter losses to IEC61800-9-2*	
Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	39.2 %
I ↓ 1,010.0 W (1.4 %)	1,140.0 W (1.5 %) 1,360.0 W (1.8 %)
616.0 W (0.8 %)	660.0 W (0.9 %) 729.0 W (1.0 %)
50% 474.0 W (0.6 %) 25%	492.0 W (0.7 %)
	50% 90% f

The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

¹⁾The output current and HP ratings are valid for the voltage range 550V-600V

³⁾ Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.