SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3230-3YH42-0UF0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Rated data		
Input		
Number of phases	3 AC	
Line voltage	500 690 V +10	% -20 %
Line frequency	47 63 Hz	
Rated voltage	690V IEC	600V NEC
Rated current (LO)	78.00 A	78.00 A
Rated current (HO)	66.40 A	66.40 A
Output		
Number of phases	3 AC	
Rated voltage	690V IEC	600V NEC ¹⁾
Rated power (LO)	75.00 kW	75.00 hp
Rated power (HO)	55.00 kW	60.00 hp
Rated current (LO)	80.00 A	80.00 A
Rated current (HO)	62.00 A	62.00 A
Rated current (IN)	82.00 A	
Max. output current	108.00 A	
Pulse frequency	2 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	
Overland enability		

Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor λ	0.90 0.95	
Offset factor $\cos \phi$	0.99	
Efficiency η	0.98	
Sound pressure level (1m)	72 dB	
Power loss 3)	1.410 kW	
Filter class (integrated)	Unfiltered	
EMC category (with accessories)	without	
Safety function "Safe Torque Off"	without SIRIUS device (e.g. via S7- 1500F)	
Communication		

Communication

PROFINET, EtherNet/IP

ltem no. : Consignment no. : Project :

Inputs / outputs		
Standard digital inputs		
Number	6	
Switching level: $0 \rightarrow 1$	11 V	
Switching level: $1 \rightarrow 0$	5 V	
Max. inrush current	15 mA	
Fail-safe digital inputs		
Number	1	
Digital outputs		
Number as relay changeover contact	2	
Output (resistive load)	DC 30 V, 5.0 A	
Number as transistor	0	
Analog / digital inputs		
Number	2 (Differential input)	
Resolution	10 bit	
Switching threshold as digital input		
0 → 1	4 V	
$1 \rightarrow 0$	1.6 V	
Analog outputs		
Number	1 (Non-isolated output)	
PTC/ KTY interface		
1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5~^\circ\text{C}$		
Closed-loop control techniques		

closed-loop control techniques		
V/f linear / square-law / parameterizable	Yes	
V/f with flux current control (FCC)	Yes	
V/f ECO linear / square-law	Yes	
Sensorless vector control	Yes	
Vector control, with sensor	No	
Encoderless torque control	No	
Torque control, with encoder	No	

SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3230-3YH42-0UF0

Ambient conditions		
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002	
Cooling	Air cooling using an integrated fan	
Cooling air requirement	0.153 m³/s (5.403 ft³/s)	
Installation altitude	1,000 m (3,280.84 ft)	
Ambient temperature		
Operation	-20 45 °C (-4 113 °F)	
Transport	-40 70 °C (-40 158 °F)	
Storage	-25 55 °C (-13 131 °F)	
Relative humidity		
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible	
Co	nnections	
Signal cable		
Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 16)	
Line side		
Version	M10 screw	
Conductor cross-section	35.00 2 x 120.00 mm² (AWG 1 AWG 2 x 4/0)	
Motor end		
Version	M10 screw	
Conductor cross-section	35.00 2 x 120.00 mm ² (AWG 1 AWG 2 x 4/0)	
DC link (for braking resistor)		
PE connection	M10 screw	
Max. motor cable length		
Shielded	300 m (984.25 ft)	
Unshielded	450 m (1,476.38 ft)	

	Mechanical data	
Degree of protection	IP20 / UL o	open type
Frame size	FSF	
Net weight	61 kg (13-	4.48 lb)
Dimensions		
Width	305 mm ((12.01 in)
Height	709 mm ((27.91 in)
Depth	369 mm ((14.53 in)
	Standards	
Compliance with stand	ards UL, cUL, C SEMI F47,	E, C-Tick (RCM), EAC, KCC, REACH
CE marking		ctive 2004/108/EC, Low- irective 2006/95/EC
C	onverter losses to IEC618	300-9-2*
Efficiency class	IE2	
Comparison with the r converter (90% / 100%		
I ▲ 1,120.0 W (1.2 0 100% ●	6) 1,230.0 W (1.3 %	%) 1,410.0 W (1.5 %)
684.0 W (0.7 %)	727.0 W (0.8 %)	788.0 W (0.8 %)
	550.0 W (0.6 %)	

The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

¹⁾The output current and HP ratings are valid for the voltage range 550V-600V

³⁾Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.

SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3230-3YH42-0UF0

	Operator panel:	Intelligent
	Screen	
Display design	LCD color	
Screen resolution	320 x 240 Pixel	
Mechanical data		
Degree of protection	IP55 / UL type 12	
Net weight	0.134 kg (0.30 lb)	
Dimensions		
Width	70.00 mm (2.76 in)	
Height	106.85 mm (4.21 in)	
Depth	19.65 mm (0.77 in)	

Operator Panel (IOP-2)		
Ambient conditions		
Ambient temperature		
Operation	0 50 °C (32 122 °F)	
	55 °C only with door installation kit	
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
Relative humidity at 25°C durin	ıg	
Max. operation	95 %	
Approvals		
Certificate of suitability	CE, cULus, EAC, KCC, RCM	