## **SIEMENS**

Data sheet US2:84FUF95WMJ



Duplex starter w/o alternator, Size 2, Three phase full voltage, Solid-state overload relay, OLR amp range 13-52A, 24VAC 50-60Hz coil, Combination type, Two 50A circuit breakers, Encl NEMA type 4X 304 S-Steel, Water/dust tight noncorrosive

Figure similar

product brand name	Class 84	
design of the product	Duplex controller with two MCPs without alternator	
special product feature	ESP200 overload relay	
General technical data		
weight [lb]	70 lb	
Height x Width x Depth [in]	56 × 29 × 10 in	
touch protection against electrical shock	NA for enclosed products	
installation altitude [ft] at height above sea level maximum	6560 ft	
ambient temperature [°F]		
<ul> <li>during storage</li> </ul>	-22 +149 °F	
during operation	-4 +104 °F	
ambient temperature		
<ul> <li>during storage</li> </ul>	-30 +65 °C	
during operation	-20 +40 °C	
country of origin	USA	
Horsepower ratings		
yielded mechanical performance [hp] for 3-phase AC motor		
• at 200/208 V rated value	10 hp	
• at 220/230 V rated value	15 hp	
• at 460/480 V rated value	25 hp	
<ul><li>at 575/600 V rated value</li></ul>	25 hp	
Contactor		
size of contactor	NEMA controller size 2	
number of NO contacts for main contacts	3	
operating voltage for main current circuit at AC at 60 Hz maximum	600 V	
operational current at AC at 600 V rated value	45 A	
mechanical service life (switching cycles) of the main contacts typical	10000000	
Auxiliary contact		
number of NC contacts at contactor for auxiliary contacts	0	
number of NO contacts at contactor for auxiliary contacts	1	
number of total auxiliary contacts maximum	7	
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)	
Coil		
type of voltage of the control supply voltage	AC	
control supply voltage		

a at DC rated value	0 0 0
<ul> <li>at DC rated value</li> <li>at AC at 50 Hz rated value</li> </ul>	0 0 V
	24 24 V 24 24 V
at AC at 60 Hz rated value  halding power at AC minimum	24 24 V 8.6 W
holding power at AC minimum	218 VA
apparent pick-up power of magnet coil at AC	25 VA
apparent holding power of magnet coil at AC operating range factor control supply voltage rated value	0.85 1.1
of magnet coil	0.65 1.1
percental drop-out voltage of magnet coil related to the input voltage	50 %
ON-delay time	19 29 ms
OFF-delay time	10 24 ms
Overload relay	
product function	
<ul> <li>overload protection</li> </ul>	Yes
<ul> <li>phase failure detection</li> </ul>	Yes
<ul> <li>asymmetry detection</li> </ul>	Yes
<ul> <li>ground fault detection</li> </ul>	Yes
<ul><li>test function</li></ul>	Yes
external reset	Yes
reset function	Manual, automatic and remote
trip class	CLASS 5 / 10 / 20 (factory set) / 30
adjustable current response value current of the current- dependent overload release	13 52 A
tripping time at phase-loss maximum	3 s
relative repeat accuracy	1 %
product feature protective coating on printed-circuit board	Yes
number of NC contacts of auxiliary contacts of overload relay	1
number of NO contacts of auxiliary contacts of overload relay	1
operational current of auxiliary contacts of overload relay	
• at AC at 600 V	5 A
• at DC at 250 V	1 A
contact rating of auxiliary contacts of overload relay according to UL	5A@600VAC (B600), 1A@250VDC (R300)
insulation voltage (Ui)	
<ul> <li>with single-phase operation at AC rated value</li> </ul>	600 V
with multi-phase operation at AC rated value	300 V
Enclosure	
degree of protection NEMA rating of the enclosure	NEMA 4x 304 stainless steel enclosure
design of the housing	dustproof, waterproof & resistant to corrosion
Circuit Breaker	
type of the motor protection	Motor circuit protector (magnetic trip only)
operational current of motor circuit breaker rated value	50 A
adjustable current response value current of instantaneous short-circuit trip unit	180 600 A
Mounting/wiring	
mounting position	Vertical
fastening method	Surface mounting and installation
type of electrical connection for supply voltage line-side	Box lug
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	1x (10 AWG 1/0 AWG)
temperature of the conductor for supply maximum permissible	75 °C
material of the conductor for supply	AL or CU
type of electrical connection for load-side outgoing feeder	Box lug
type of electrical connection for load-side outgoing feeder tightening torque [lbf·in] for load-side outgoing feeder	Box lug 45 45 lbf·in
tightening torque [lbf·in] for load-side outgoing feeder type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi-	45 45 lbf·in

maximum permissible	
material of the conductor for load-side outgoing feeder	AL or CU
type of electrical connection of magnet coil	Screw-type terminals
tightening torque [lbf·in] at magnet coil	5 12 lbf·in
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (16 12 AWG)
temperature of the conductor at magnet coil maximum permissible	75 °C
material of the conductor at magnet coil	CU
type of electrical connection at contactor for auxiliary contacts	Screw-type terminals
tightening torque [lbf·in] at contactor for auxiliary contacts	10 15 lbf·in
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C
material of the conductor at contactor for auxiliary contacts	CU
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 14 AWG)
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C
material of the conductor at overload relay for auxiliary contacts	CU
Short-circuit current rating	
design of the short-circuit trip	Instantaneous trip circuit breaker
breaking capacity maximum short-circuit current (Icu)	
• at 240 V	100 kA
• at 480 V	100 kA
● at 600 V	25 kA
certificate of suitability	NEMA ICS 2; UL 508; CSA 22.2, No.14
From the autoform action	

Industrial Controls - Product Overview (Catalogs, Brochures,...)

www.usa.siemens.com/iccatalog

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:84FUF95WMJ


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/US/en/ps/US2:84FUF95WMJ

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) <a href="http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=US2:84FUF95WMJ&lang=en">http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=US2:84FUF95WMJ&lang=en</a>

Certificates/approvals

https://support.industry.siemens.com/cs/US/en/ps/US2:84FUF95WMJ/certificate



last modified: 1/25/2022 🖸