
# RSL1AB4BD

Harmony, Slim interface plug-in relay, 6 A, 1 CO, standard, 24 V DC



#### Main Range of Product Harmony Electromechanical Relays Series name Slim interface relay **Product or Component** Plug-in relay Type RSL Device short name Contacts type and 1 C/O composition Contact operation Standard [Uc] control circuit 24 V DC voltage 6 A -40...131 °F (-40...55 °C) [Ithe] conventional enclosed thermal

Without

# Control Type Without push-button

current Status LED

#### Complementary

Complementary	
Shape of pin	Flat (PCB type)
Average resistance	3390 Ohm at 73 °F (23 °C) +/- 15 %
Rated operational voltage limits	1833.6 V DC
[Ui] rated insulation voltage	250 V EN/IEC 277 V cUL
[Uimp] rated impulse withstand voltage	6 kV IEC
Contacts material	Silver alloy (AgSnO2)
[le] rated operational current	6 A AC-1/DC-1)IEC/UL
Minimum switching current	10 mA
Maximum switching voltage	277 V
Minimum switching voltage	12 V
Maximum switching capacity	1500 VA 50 W
Minimum switching capacity	120 mW
Operating rate	<= 360 cycles/hour under load <= 18000 cycles/hour no-load
Mechanical durability	10000000 cycles
Electrical durability	60000 cycles, 6 A at 250 V, AC-1 C/O
Operating time	5 ms reset 12 ms
Protection category	RT III
Test levels	Level A
Operating position	Any position
Width	0.20 in (5 mm)
Height	1.10 in (28 mm)
Depth	0.73 in (18.5 mm)
Terminals description ISO n°1	(11-12-14)OC (A1-A2)CO
Net Weight	0.01 lb(US) (0.0054 kg)
Load current	6 A 250 V AC 0.5 mm mounting distance
Average coil consumption	0.17 W
Drop-out voltage threshold	>= 0.05 Uc
Safety reliability data	B10d = 60000


Mounting Support	Socket or PCB
Device presentation	Complete product
Environment	
Dielectric strength	1000 V AC between contacts 4000 V AC between coil and contact
Standards	CSA C22.2 No 14 EN/IEC 61810-1 UL 508
Product Certifications	CSA UL EAC
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)
Vibration resistance	+/- 1 mm 1055 Hz)EN/IEC 60068-2-6
IP degree of protection	IP40 conforming to EN/IEC 60529
Shock resistance	5 gn 11 ms) not operating EN/IEC 60068-2-27 5 gn 11 ms) in operation EN/IEC 60068-2-27
Ambient air temperature for operation	-40131 °F (-4055 °C)
Ordering and shipping details	24427 7ELIO ICE CURE DEL AVO
Category	21127 - ZELIO ICE CUBE RELAYS
Discount Schedule	CP2
GTIN	3606480077975
Nbr. of units in pkg.	1 0.21 67 (6.6)
Package weight(Lbs)	0.21 oz (6 g)
Returnability	Yes CN
Country of origin	CIV
Packing Units	
Unit Type of Package 1	PCE
Package 1 Height	0.59 in (1.5 cm)
Package 1 width	0.20 in (0.5 cm)
Package 1 Length	1.10 in (2.8 cm)
Offer Containability	
Offer Sustainability California proposition 65	WARNING: This product can expose you to chemicals including: Nickel
Odinomia μιοροσιαστί σο	compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EV RoHS  Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	€Yes
China RoHS Regulation	☑ China RoHS Declaration
omma riorro riogalation	
Environmental Disclosure	Product Environmental Profile
	Product Environmental Profile  Find Of Life Information
Environmental Disclosure	
Environmental Disclosure	

# Product data sheet Dimensions Drawings

# RSL1AB4BD

## **Dimensions**

## Relay with Flat Pins (PCB Type)



(1): 5.04 mm / 0.19 in.


# Product data sheet Connections and Schema

# RSL1AB4BD

# Wiring Diagram

# Relay with Flat Pins (PCB Type)


1 C/O contact



#### Curves for Resistive Load

## Maximum Switching Capacity on DC Load


#### Resistive load



X DC Current Y DC Voltage

## **Electrical Durability**

Only tested at 6A/250VAC, projection for the rest 250 Vac Resistive load



X Switching current (A)

Y Cycles

Note: These are typical curves, actual durability depends on load, environment, duty cycle, etc.