## SIEMENS

## Data sheet

## US2:32DUDC92W1VF



2-speed 3-phase motor starter Size 1 Two separate windings Constant or variable torque Solid-state overload relays Low SPD OLR range 3-12A High SPD OLR range 5.5-22A 110V 50HZ / 120V 60HZ coil Combination type 25Amp circuit breaker Encl NEMA type 4X 304 S-steel Water/dust tight noncorrosive

| Figures | similar |
|---------|---------|
|---------|---------|

| product brand name   | Class 32                                      |
|--|---|
| design of the product  | Full-voltage two speed motor starter with MCP |
| special product feature  | ESP200 overload relay                         |
| General technical data   |   |
| weight [lb]  | 51 lb   |
| Height x Width x Depth [in]  | 24 × 20 × 8 in                                |
| touch protection against electrical shock                                  | NA for enclosed products                      |
| installation altitude [ft] at height above sea level maximum               | 6560 ft                                       |
| ambient temperature [°F]   |   |
| <ul> <li>during storage</li> </ul>   | -22 +149 °F                                   |
| during operation   | -4 +104 °F                                    |
| ambient temperature  |   |
| <ul> <li>during storage</li> </ul>   | -30 +65 °C                                    |
| during operation   | -20 +40 °C                                    |
| country of origin  | USA   |
| Horsepower ratings   |   |
| yielded mechanical performance [hp] for 3-phase AC motor                   |   |
| • at 200/208 V rated value   | 3 hp  |
| • at 220/230 V rated value   | 3 hp  |
| <ul> <li>at 460/480 V rated value</li> </ul>                               | 10 hp   |
| <ul> <li>at 575/600 V rated value</li> </ul>                               | 10 hp   |
| Contactor  |   |
| size of contactor  | NEMA controller size 1                        |
| number of NO contacts for main contacts                                    | 6   |
| operating voltage for main current circuit at AC at 60 Hz maximum          | 600 V   |
| operational current at AC at 600 V rated value                             | 27 A  |
| mechanical service life (switching cycles) of the main<br>contacts typical | 1000000                                       |
| Auxiliary contact  |   |
| number of NC contacts at contactor for auxiliary contacts                  | 2   |
| number of NO contacts at contactor for auxiliary contacts                  | 2   |
| number of total auxiliary contacts maximum                                 | 8   |
| contact rating of auxiliary contacts of contactor according to UL          | 10A@600VAC (A600), 5A@600VDC (P600)           |
| Coil   |   |
| type of voltage of the control supply voltage                              | AC  |
| control supply voltage   |   |

| • at AC at 50 Hz rated value  | 110 V  |
|---|--|
| at AC at 60 Hz rated value  | 120 V  |
| holding power at AC minimum   | 8.6 W  |
| apparent pick-up power of magnet coil at AC   | 218 VA   |
| apparent holding power of magnet coil at AC   | 25 VA  |
| operating range factor control supply voltage rated value<br>of magnet coil   | 0.85 1.1                                       |
| percental drop-out voltage of magnet coil related to the<br>input voltage   | 50 %   |
| ON-delay time   | 19 29 ms                                       |
| OFF-delay time  | 10 24 ms                                       |
| Overload relay  |  |
| product function  |  |
| <ul> <li>overload protection</li> </ul>   | Yes  |
| <ul> <li>phase failure detection</li> </ul>   | Yes  |
| <ul> <li>asymmetry detection</li> </ul>   | Yes  |
| <ul> <li>ground fault detection</li> </ul>  | Yes  |
| • test function   | Yes  |
| external reset  | Yes  |
| reset function  | Manual, automatic and remote                   |
| trip class  | CLASS 5 / 10 / 20 (factory set) / 30           |
| adjustable current response value current of overload relay   |  |
| <ul> <li>for low rotational speed</li> </ul>  | 3 12 A   |
| <ul> <li>for high rotational speed</li> </ul>   | 5.5 22 A                                       |
| tripping time at phase-loss maximum   | 3 s  |
| relative repeat accuracy  | 1%   |
| product feature protective coating on printed-circuit board   | Yes  |
| number of NC contacts of auxiliary contacts of overload   | 1  |
| relay<br>number of NO contacts of auxiliary contacts of overload  | 1  |
| relay   |  |
| operational current of auxiliary contacts of overload relay   | 5 A  |
| • at AC at 600 V  | 5 A  |
| at DC at 250 V  |  |
| contact rating of auxiliary contacts of overload relay<br>according to UL   | 5A@600VAC (B600), 1A@250VDC (R300)             |
| insulation voltage (Ui)   |  |
| <ul> <li>with single-phase operation at AC rated value</li> </ul>   | 600 V  |
| <ul> <li>with multi-phase operation at AC rated value</li> </ul>  | 300 V  |
| Enclosure   |  |
| degree of protection NEMA rating  | 4X, 304 stainless steel                        |
| design of the housing   | dustproof, waterproof & resistant to corrosion |
| Circuit Breaker   |  |
| type of the motor protection  | Motor circuit protector (magnetic trip only)   |
| operational current of motor circuit breaker rated value  | 25 A   |
| adjustable current response value current of instantaneous short-circuit trip unit                                    | 55 180 A                                       |
| Mounting/wiring   |  |
| mounting position   | Vertical                                       |
| fastening method  | Surface mounting and installation              |
| type of electrical connection for supply voltage line-side  | Box lug  |
| type of connectable conductor cross-sections at line-side<br>at AWG cables single or multi-stranded                   | 1x (14 AWG 10 AWG) or 1x (12 AWG 10 AWG)       |
| temperature of the conductor for supply maximum permissible   | 75 °C  |
| material of the conductor for supply  | AL or CU                                       |
| type of electrical connection for load-side outgoing feeder   | Screw-type terminals                           |
| tightening torque [lbf·in] for load-side outgoing feeder  | 35 35 lbf·in                                   |
| type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi-<br>stranded | 1x (14 2 AWG)                                  |

| temperature of the conductor for load-side outgoing feeder maximum permissible  | 75 °C                                       |  |
|---|---|--|
| material of the conductor for load-side outgoing feeder   | AL or CU                                    |  |
| type of electrical connection of magnet coil  | Screw-type terminals                        |  |
| tightening torque [lbf·in] at magnet coil   | 5 12 lbf·in                                 |  |
| type of connectable conductor cross-sections of magnet<br>coil at AWG cables single or multi-stranded                               | 2x (16 12 AWG)                              |  |
| temperature of the conductor at magnet coil maximum permissible   | 75 °C                                       |  |
| material of the conductor at magnet coil  | CU  |  |
| type of electrical connection at contactor for auxiliary<br>contacts  | Screw-type terminals                        |  |
| tightening torque [lbf-in] at contactor for auxiliary contacts  | 10 15 lbf·in                                |  |
| type of connectable conductor cross-sections at contactor<br>at AWG cables for auxiliary contacts single or multi-<br>stranded      | 1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG) |  |
| temperature of the conductor at contactor for auxiliary<br>contacts maximum permissible   | 75 °C                                       |  |
| material of the conductor at contactor for auxiliary contacts   | CU  |  |
| type of electrical connection at overload relay for auxiliary contacts  | Screw-type terminals                        |  |
| tightening torque [lbf-in] at overload relay for auxiliary contacts   | 7 10 lbf·in                                 |  |
| type of connectable conductor cross-sections at overload<br>relay at AWG cables for auxiliary contacts single or multi-<br>stranded | 2x (20 14 AWG)                              |  |
| temperature of the conductor at overload relay for auxiliary contacts maximum permissible   | 75 °C                                       |  |
| material of the conductor at overload relay for auxiliary contacts  | CU  |  |
| Short-circuit current rating  |   |  |
| design of the short-circuit trip  | Instantaneous trip circuit breaker          |  |
| breaking capacity maximum short-circuit current (Icu)   |   |  |
| • at 240 V  | 100 A                                       |  |
| • at 480 V  | 100 A                                       |  |
| • at 600 V  | 25 A  |  |
| certificate of suitability  | NEMA ICS 2; UL 508; CSA 22.2, No.14         |  |
| Further information   |   |  |
| Industrial Controls - Product Overview (Catalogs, Brochures,)   |   |  |
| www.usa.siemens.com/iccatalog   |   |  |
| Industry Mall (Online ordering system)  |   |  |


https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:32DUDC92W1VF

Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/US/en/ps/US2:32DUDC92W1VF

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=US2:32DUDC92W1VF&lang=en

Certificates/approvals

https://support.industry.siemens.com/cs/US/en/ps/US2:32DUDC92W1VF/certificate



last modified:

1/25/2022 🖸