



# **OD24-7D5**

# VERTICALLY POLARIZED OMNI ANTENNAS

# 2400-2485 MHZ VERTICALLY POLARIZED OMNI-DIRECTIONAL ANTENNA

The omni-directional antenna systems offered by Laird are constructed of UV-stable fiberglass with all stainless steel brackets standard. They come standard with type N female bulkhead connectors with extra heavy duty nuts for optional standoff type mounting. The 7dBi has a 5 deg electrical downtilt standard which is perfect for close-in wireless systems such as apartment complexes. Because of their unique high performance design which eliminates nulls, they can be used in a wide variety of wireless systems.

## **FEATURES**


- 7 dBi antenna gain
- 5 Deg electrical downtilt
- Type N female integrated bulkhead connector
- · Rugged, lightweight, and waterproof

#### **MARKETS**

- 2.4 GHz ISM band applications
- Base station antennas
- 802.11b and 802.11g wireless systems
- Point-to-multi-point systems
- Wireless broadband systems
- WiFi access points

PARAMETER	
Frequency range	2400-2485 MHz
Input return loss (S11)	-14 dB
VSWR	1.5:1
Impedance	50 ohm
Input power	100W
Pole diameter (OD)	1"- 2" (25-51mm)
Operating temperature	-40 - +70°C
Rated wind velocity	125 mph (56 m/sec)
Gain	7dBi
Vertical 3dB beamwidth	18°
Electrical downtilt	5°
Weight	1.1 LBS (0.5KG)
Length +/- 1.0 in	21 IN (54 CM)
Diameter	1.5 in (38 mm)

## **ANTENNA PATTERN**



#### SYSTEM ORDERING

OD24-7D5 2.4GHz 7dBi omni-directional antenna with 5 deg electrical downtilt



#### TE TECHNICAL SUPPORT CENTER

USA: +1 (800) 522-6752 +1 (905) 475-6222 Canada: Mexico: +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 Germany: +49 (0) 6251-133-1999 +44 (0) 800-267666 UK: +33 (0) 1-3420-8686 France: Netherlands: +31 (0) 73-6246-999 China: +86 (0) 400-820-6015

#### te.com

TE, and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE Connectivity warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE Connectivity will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE Connectivity product is installed. Useful lifetime of the original end product may vary but is not warrantied to exceed one (1) year from the original date of the end product purchase.

©2022 TE Connectivity. All Rights Reserved.

08/22 Original