DATASHEET

UJ4C075023K3S



Part Number	Package	Marking
UJ4C075023K3S	TO-247-3L	UJ4C075023K3S

RoHS COMPLIANT | Pb LEAD FREE | HF HALOGEN FREE

750V-23mΩ SiC FET

Rev. B, July 2021

Description

The UJ4C075023K3S is a 750V, 23mΩ G4 SiC FET. It is based on a unique 'cascode' circuit configuration, in which a normally-on SiC JFET is co-packaged with a Si MOSFET to produce a normally-off SiC FET device. The device's standard gate-drive characteristics allows for a true "drop-in replacement" to Si IGBTs, Si FETs, SiC MOSFETs or Si superjunction devices. Available in the TO-247-3L package, this device exhibits ultra-low gate charge and exceptional reverse recovery characteristics, making it ideal for switching inductive loads and any application requiring standard gate drive.

Features

- On-resistance $R_{DS(on)}$: 23mΩ (typ)
- Operating temperature: 175°C (max)
- Excellent reverse recovery: Q_{rr} = 84nC
- Low body diode V_{FSD}: 1.23V
- Low gate charge: Q_G = 37.8nC
- Threshold voltage $V_{G(th)}$: 4.8V (typ) allowing 0 to 15V drive
- Low intrinsic capacitance
- ESD protected: HBM class 2 and CDM class C3

Typical applications

- EV charging
- PV inverters
- Switch mode power supplies
- Power factor correction modules
- Motor drives
- Induction heating

Maximum Ratings

Parameter	Symbol	Test Conditions	Value	Units
Drain-source voltage	V_{DS}		750	V
Gate-source voltage	V_{GS}	DC	-20 to +20	V
		AC (f > 1Hz)	-25 to +25	V
Continuous drain current [1]	I_D	T_C = 25°C	66	A
		T_C = 100°C	49	A
Pulsed drain current [2]	I_{DM}	T_C = 25°C	196	A
Single pulsed avalanche energy [3]	E_{AS}	L=15mH, I_{AS} =3A	67	mJ
SiC FET dv/dt ruggedness	dv/dt	$V_{DS} \leq 500V$	150	V/ns
Power dissipation	P_{tot}	T_C = 25°C	306	W
Maximum junction temperature	$T_{J,max}$		175	°C
Operating and storage temperature	T_J, T_{STG}		-55 to 175	°C
Max. lead temperature for soldering, 1/8" from case for 5 seconds	T_L		250	°C

1. Limited by $T_{J,max}$
2. Pulse width t_p limited by $T_{J,max}$
3. Starting T_J = 25°C

Thermal Characteristics

Parameter	Symbol	Test Conditions	Value			Units
			Min	Typ	Max	
Thermal resistance, junction-to-case	$R_{\theta JC}$			0.38	0.49	°C/W

Electrical Characteristics (T_J = +25°C unless otherwise specified)

Typical Performance - Static

Parameter	Symbol	Test Conditions	Value			Units
			Min	Typ	Max	
Drain-source breakdown voltage	BV_{DS}	V_{GS}=0V, I_D=1mA	750			V
Total drain leakage current	I_{DSS}	V_{DS}=750V, V_{GS}=0V, T_J=25°C		2	30	µA
		V_{DS}=750V, V_{GS}=0V, T_J=175°C		15		
Total gate leakage current	I_{GSS}	V_{DS}=0V, T_J=25°C, V_{GS}=-20V / +20V		6	±20	µA
Drain-source on-resistance	$R_{DS(on)}$	V_{GS}=12V, I_D=40A, T_J=25°C		23	29	mΩ
		V_{GS}=12V, I_D=40A, T_J=125°C		39		
		V_{GS}=12V, I_D=40A, T_J=175°C		50		
Gate threshold voltage	$V_{G(th)}$	V_{DS}=5V, I_D=10mA	4	4.8	6	V
Gate resistance	R_G	f=1MHz, open drain		4.5		Ω

Typical Performance - Reverse Diode

Parameter	Symbol	Test Conditions	Value			Units
			Min	Typ	Max	
Diode continuous forward current [1]	I_S	T_C = 25°C			66	A
Diode pulse current [2]	$I_{S,pulse}$	T_C = 25°C			196	A
Forward voltage	V_{FSD}	V_{GS}=0V, I_S=20A, T_J=25°C		1.23	1.39	V
		V_{GS}=0V, I_S=20A, T_J=175°C		1.45		
Reverse recovery charge	Q_{rr}	V_R=400V, I_S=40A, V_{GS}=0V, R_{G_EXT}=5Ω di/dt=1500A/µs, T_J=25°C		84		nC
Reverse recovery time	t_{rr}			27		ns
Reverse recovery charge	Q_{rr}	V_R=400V, I_S=40A, V_{GS}=0V, R_{G_EXT}=5Ω di/dt=1500A/µs, T_J=150°C		91		nC
Reverse recovery time	t_{rr}			28		ns

Typical Performance - Dynamic

Parameter	Symbol	Test Conditions	Value			Units
			Min	Typ	Max	
Input capacitance	C_{iss}	V_{DS}=400V, V_{GS}=0V f=100kHz		1400		pF
Output capacitance	C_{oss}			93		
Reverse transfer capacitance	C_{rss}			2.5		
Effective output capacitance, energy related	$C_{oss(er)}$	V_{DS}=0V to 400V, V_{GS}=0V		116		pF
Effective output capacitance, time related	$C_{oss(tr)}$	V_{DS}=0V to 400V, V_{GS}=0V		232		pF
C_{OSS} stored energy	E_{oss}	V_{DS}=400V, V_{GS}=0V		9.3		µJ
Total gate charge	Q_G	V_{DS}=400V, I_D=40A, V_{GS} = 0V to 15V		37.8		nC
Gate-drain charge	Q_{GD}			8		
Gate-source charge	Q_{GS}			11.8		
Turn-on delay time	$t_{d(on)}$	Notes 4 and 5, V_{DS}=400V, I_D=40A, Gate Driver =0V to +15V, Turn-on $R_{G,EXT}$=1Ω, Turn-off $R_{G,EXT}$=5Ω, inductive Load, FWD: same device with V_{GS} = 0V and R_G = 5Ω, RC snubber: R_S=10Ω and C_S=200pF, T_J=25°C		10		ns
Rise time	t_r			49		
Turn-off delay time	$t_{d(off)}$			53		
Fall time	t_f			14		
Turn-on energy including R_S energy	E_{ON}			455		µJ
Turn-off energy including R_S energy	E_{OFF}			140		
Total switching energy	E_{TOTAL}			595		
Snubber R_S energy during turn-on	E_{RS_ON}			4		
Snubber R_S energy during turn-off	E_{RS_OFF}			10		
Turn-on delay time	$t_{d(on)}$	Notes 4 and 5, V_{DS}=400V, I_D=40A, Gate Driver =0V to +15V, Turn-on $R_{G,EXT}$=1Ω, Turn-off $R_{G,EXT}$=5Ω, inductive Load, FWD: same device with V_{GS} = 0V and R_G = 5Ω, RC snubber: R_S=10Ω and C_S=200pF, T_J=150°C		15		ns
Rise time	t_r			47		
Turn-off delay time	$t_{d(off)}$			51		
Fall time	t_f			14		
Turn-on energy including R_S energy	E_{ON}			505		µJ
Turn-off energy including R_S energy	E_{OFF}			157		
Total switching energy	E_{TOTAL}			662		
Snubber R_S energy during turn-on	E_{RS_ON}			4		
Snubber R_S energy during turn-off	E_{RS_OFF}			10		

4. Measured with the switching test circuit in Figure 35.
5. In this datasheet, all the switching energies (turn-on energy, turn-off energy and total energy) presented in the tables and Figures include the device RC snubber energy losses.

Typical Performance - Dynamic (continued)

Parameter	Symbol	Test Conditions	Value			Units
			Min	Typ	Max	
Turn-on delay time	$t_{d(on)}$	Note 6, V_{DS}=400V, I_D=40A, Gate Driver =0V to +15V, Turn-on $R_{G,EXT}$=1Ω, Turn-off $R_{G,EXT}$=5Ω, inductive Load, FWD: UJ3D06520TS, RC snubber: R_S=10Ω and C_S=200pF, T_J=25°C		10		ns
Rise time	t_r			45		
Turn-off delay time	$t_{d(off)}$			50		
Fall time	t_f			11		
Turn-on energy including R_S energy	E_{ON}			366		µJ
Turn-off energy including R_S energy	E_{OFF}			135		
Total switching energy	E_{TOTAL}			501		
Snubber R_S energy during turn-on	E_{RS_ON}			4.4		
Snubber R_S energy during turn-off	E_{RS_OFF}			10		
Turn-on delay time	$t_{d(on)}$	Note 6, V_{DS}=400V, I_D=40A, Gate Driver =0V to +15V, Turn-on $R_{G,EXT}$=1Ω, Turn-off $R_{G,EXT}$=5Ω, inductive Load, FWD: UJ3D06520TS, RC snubber: R_S=10Ω and C_S=200pF, T_J=150°C		10		ns
Rise time	t_r			47		
Turn-off delay time	$t_{d(off)}$			53		
Fall time	t_f			17		
Turn-on energy including R_S energy	E_{ON}			450		µJ
Turn-off energy including R_S energy	E_{OFF}			157		
Total switching energy	E_{TOTAL}			607		
Snubber R_S energy during turn-on	E_{RS_ON}			4.4		
Snubber R_S energy during turn-off	E_{RS_OFF}			10		

6. Measured with the switching test circuit in Figure 36.

Typical Performance Diagrams



Figure 1. Typical output characteristics at T_J = - 55°C, tp < 250µs



Figure 2. Typical output characteristics at T_J = 25°C, tp < 250µs



Figure 3. Typical output characteristics at T_J = 175°C, tp < 250µs



Figure 4. Normalized on-resistance vs. temperature at V_{GS} = 12V



Figure 5. Typical drain-source on-resistances at V_{GS} = 12V



Figure 6. Typical transfer characteristics at V_{DS} = 5V



Figure 7. Threshold voltage vs. junction temperature at V_{DS} = 5V and I_D = 10mA



Figure 8. Typical gate charge at I_D = 40A



Figure 9. 3rd quadrant characteristics at T_J = -55°C



Figure 10. 3rd quadrant characteristics at T_J = 25°C



Figure 11. 3rd quadrant characteristics at T_J = 175°C



Figure 12. Typical stored energy in C_{OSS} at V_{GS} = 0V



Figure 13. Typical capacitances at f = 100kHz and V_{GS} = 0V



Figure 14. DC drain current derating



Figure 15. Total power dissipation



Figure 16. Maximum transient thermal impedance



Figure 17. Safe operation area at T_C = 25°C, D = 0, Parameter t_p



Figure 18. Reverse recovery charge Qrr vs. junction temperature



Figure 19. Clamped inductive switching energy vs. drain current at V_{DS} = 400V and T_J = 25°C



Figure 20. Clamped inductive switching energy vs. drain current at V_{DS} = 500V and T_J = 25°C



Figure 21. RC snubber energy loss vs. drain current at V_{DS} = 400V and T_J = 25°C



Figure 22. RC snubber energy losses vs. drain current at V_{DS} = 500V and T_J = 25°C



Figure 23. Clamped inductive switching energies vs. $R_{G,EXT}$ at V_{DS} = 400V, I_D = 40A, and T_J = 25°C



Figure 24. RC snubber energy losses vs. $R_{G,EXT}$ at V_{DS} = 400V, I_D = 40A, and T_J = 25°C



Figure 25. Clamped inductive switching energies vs. snubber capacitance C_S at V_{DS} = 400V, I_D = 40A, and T_J = 25°C



Figure 26. RC snubber energy losses vs. snubber capacitance C_S at V_{DS} = 400V, I_D = 40A, and T_J = 25°C



Figure 27. Clamped inductive switching energy vs. junction temperature at V_{DS} =400V and I_D = 40A



Figure 28. Clamped inductive switching energy vs. junction temperature at V_{DS} =500V and I_D = 40A



Figure 29. Clamped inductive switching energy vs. drain current at V_{DS} = 400V and T_J = 25°C



Figure 30. Clamped inductive switching energy vs. drain current at V_{DS} = 500V and T_J = 25°C



Figure 31. RC snubber energy losses vs. drain current at V_{DS} = 400V and T_J = 25°C



Figure 32. RC snubber energy losses vs. drain current at V_{DS} = 500V and T_J = 25°C



Figure 33. Clamped inductive switching energy vs. junction temperature at V_{DS} =400V and I_D = 40A



Figure 34. Clamped inductive switching energy vs. junction temperature at V_{DS} =500V and I_D = 40A



Figure 35. Schematic of the half-bridge mode switching test circuit. Note, a bus RC snubber (R_{BS} = 2.5Ω, C_{BS}=100nF) is used to reduce the power loop high frequency oscillations.



Figure 36. Schematic of the chopper mode switching test circuit. Note, a bus RC snubber (R_{BS} = 2.5Ω, C_{BS}=100nF) is used to reduce the power loop high frequency oscillations.

Applications Information

SiC FETs are enhancement-mode power switches formed by a high-voltage SiC depletion-mode JFET and a low-voltage silicon MOSFET connected in series. The silicon MOSFET serves as the control unit while the SiC JFET provides high voltage blocking in the off state. This combination of devices in a single package provides compatibility with standard gate drivers and offers superior performance in terms of low on-resistance ($R_{DS(on)}$), output capacitance (C_{oss}), gate charge (Q_G), and reverse recovery charge (Q_{rr}) leading to low conduction and switching losses. The SiC FETs also provide excellent reverse conduction capability eliminating the need for an external anti-parallel diode.

Like other high performance power switches, proper PCB layout design to minimize circuit parasitics is strongly recommended due to the high dv/dt and di/dt rates. An external gate resistor is recommended when the FET is working in the diode mode in order to achieve the optimum reverse recovery performance. For more information on SiC FET operation, see www.unitedsic.com.

A snubber circuit with a small $R_{(G)}$, or gate resistor, provides better EMI suppression with higher efficiency compared to using a high $R_{(G)}$ value. There is no extra gate delay time when using the snubber circuitry, and a small $R_{(G)}$ will better control both the turn-off $V_{(DS)}$ peak spike and ringing duration, while a high $R_{(G)}$ will damp the peak spike but result in a longer delay time. In addition, the total switching loss when using a snubber circuit is less than using high $R_{(G)}$, while greatly reducing $E_{(OFF)}$ from mid-to-full load range with only a small increase in $E_{(ON)}$. Efficiency will therefore improve with higher load current. For more information on how a snubber circuit will improve overall system performance, visit the UnitedSiC website at www.unitedsic.com

Disclaimer

UnitedSiC reserves the right to change or modify any of the products and their inherent physical and technical specifications without prior notice. UnitedSiC assumes no responsibility or liability for any errors or inaccuracies within.

Information on all products and contained herein is intended for description only. No license, express or implied, to any intellectual property rights is granted within this document.

UnitedSiC assumes no liability whatsoever relating to the choice, selection or use of the UnitedSiC products and services described herein.