

MLFB-Ordering data

6SL3230-1YE30-0UF0



Client order no. : Order no. : Offer no. : Remarks:

Item no.: Consignment no. : Project :

Rated data					
Input					
Number of phases	3 AC				
Line voltage	380 480 V +10 % -20 %				
Line frequency	47 63 Hz				
Rated voltage	400V IEC	480V NEC			
Rated current (LO)	37.00 A	32.00 A			
Rated current (HO)	33.00 A	28.00 A			
Output					
Number of phases	3 AC				
Rated voltage	400V IEC	480V NEC			
Rated power (LO)	18.50 kW	25.00 hp			
Rated power (HO)	15.00 kW	20.00 hp			
Rated current (LO)	38.00 A	34.00 A			
Rated current (HO)	32.00 A	27.00 A			
Rated current (IN)	39.00 A				
Max. output current	51.30 A				
Pulse frequency	4 kHz				
Output frequency for vector control	0 200 Hz				
Output frequency for V/f control	0 550 Hz				

General tech. specifications				
Power factor λ	0.90 0.95			
Offset factor cos φ	0.99			
Efficiency η	0.98			
Sound pressure level (1m)	70 dB			
Power loss	0.500 kW			
Filter class (integrated)	Unfiltered			
EMC category (with accessories)	without			
Ambient conditions				

A					
Ambient conditions					
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002				
Cooling	Air cooling using an integrated fan				
Cooling air requirement	0.055 m³/s (1.942 ft³/s)				
Installation altitude	1000 m (3280.84 ft)				
Ambient temperature					
Operation	-20 45 °C (-4 113 °F)				
Transport	-40 70 °C (-40 158 °F)				
Storage	-25 55 °C (-13 131 °F)				

Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

Relative humidity

Max. operation

95~% At 40 °C (104 °F), condensation and icing not permissible



MLFB-Ordering data

6SL3230-1YE30-0UF0



Fi						

Mechanical	data	Closed-loop cor	Figure similar	
Degree of protection	IP20 / UL open type		•	
Size	FSD	V/f linear / square-law / parameter	izable Yes	
Net weight	17 kg (37.48 lb)	V/f with flux current control (FCC)	Yes	
Width	200 mm (7.87 in)	V/f ECO linear / square-law	Yes	
Height	472 mm (18.58 in)	Sensorless vector control	Yes	
Depth	248 mm (9.76 in)	Vector control, with sensor	No	
Inputs / out		Encoderless torque control	Yes	
Standard digital inputs	Tr	Torque control, with encoder	No	
Number	6			
Switching level: 0→1	11 V	Commu	nication	
Switching level: 1→0	5 V	Communication	PROFINET, EtherNet/IP	
Max. inrush current	15 mA	Connections		
Fail-safe digital inputs	13 IIIA	Signal cable		
Number	1	Conductor cross-section	0.15 1.50 mm ² (AWG 24 AWG 16)	
Digital outputs		Line side		
Number as relay changeover contact	2	Version	screw-type terminal	
Output (resistive load)	DC 30 V, 5.0 A	Conductor cross-section	10.00 35.00 mm² (AWG 8 AWG 2)	
Number as transistor	0	Motor end		
Analog / digital inputs		Version	Screw-type terminals	
Number	2 (Differential input)	Conductor cross-section	10.00 35.00 mm² (AWG 8 AWG 2)	
Resolution	10 bit	DC link (for braking resistor)		
Switching threshold as digital in	out	PE connection	Screw-type terminals	
0→1	4 V	Max. motor cable length	71	
1→0	1.6 V	Shielded	200 m (656.17 ft)	
Analog outputs		Unshielded	300 m (984.25 ft)	
Number	1 (Non-isolated output)	onsineraeu	300 III (304.23 II)	
PTC/ KTY interface				

1 motor temperature sensor input, sensors that can be connected: PTC, KTY and Thermo-Click, accuracy $\pm 5~^{\circ}\text{C}$



MLFB-Ordering data


6SL3230-1YE30-0UF0



Figure similar

Converter losses to EN 50598-2*

Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	-45.20 %



 $The \ percentage \ values \ show \ the \ losses \ in \ relation \ to \ the \ rated \ apparent \ power \ of \ the \ converter.$

The diagram shows the losses for the points (as per standard EN 50598) of the relative torque generating current (I) over the relative motor stator frequency(f). The values are valid for the basic version of the converter without options/components.

Standards

Compliance with standards

UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH

CE marking

EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC

^{*}converted values