SIEMENS

Data sheet

US2:84DUB95WDH



Duplex starter w/o alternator Size 1 Three phase full voltage Solid-state overload relay OLR amp range 0.75-3.4A Combination type Two 30A disconnect switches Encl NEMA type 4X 304 S. Steel Water/dust tight non-corrosive

| Figur | e | si | mi | lar |
|-------|----|----|----|-------|
| rigon | ۷. | 21 | | 1.041 |

| product brand name | Class 84 |
|--|---|
| design of the product | Duplex controller with two non-fusible disconnect switches without alternator |
| special product feature | ESP200 overload relay |
| General technical data | |
| weight [lb] | 70 lb |
| Height x Width x Depth [in] | 34 × 25 × 8 in |
| touch protection against electrical shock | NA for enclosed products |
| installation altitude [ft] at height above sea level maximum | 6560 ft |
| ambient temperature [°F] | |
| during storage | -22 +149 °F |
| during operation | -4 +104 °F |
| ambient temperature | |
| during storage | -30 +65 °C |
| during operation | -20 +40 °C |
| country of origin | USA |
| Horsepower ratings | |
| yielded mechanical performance [hp] for 3-phase AC motor | |
| • at 200/208 V rated value | 0.5 hp |
| at 220/230 V rated value | 0.75 hp |
| at 460/480 V rated value | 1.5 hp |
| at 575/600 V rated value | 2 hp |
| Contactor | |
| size of contactor | NEMA controller size 1 |
| number of NO contacts for main contacts | 3 |
| operating voltage for main current circuit at AC at 60 Hz maximum | 600 V |
| operational current at AC at 600 V rated value | 27 A |
| mechanical service life (switching cycles) of the main contacts typical | 1000000 |
| Auxiliary contact | |
| number of NC contacts at contactor for auxiliary contacts | 0 |
| number of NO contacts at contactor for auxiliary contacts | 1 |
| number of total auxiliary contacts maximum | 8 |
| contact rating of auxiliary contacts of contactor according to UL | 10A@600VAC (A600), 5A@600VDC (P600) |
| Coil | |
| type of voltage of the control supply voltage | AC |
| | |

| control supply voltage | 0.01/ | |
|---|--|--|
| at DC rated value | 00V | |
| at AC at 50 Hz rated value | 380 440 V | |
| • at AC at 60 Hz rated value | 440 480 V | |
| holding power at AC minimum | 8.6 W | |
| apparent pick-up power of magnet coil at AC | 218 VA | |
| apparent holding power of magnet coil at AC | 25 VA | |
| operating range factor control supply voltage rated value of magnet coil | 0.85 1.1 | |
| percental drop-out voltage of magnet coil related to the | 50 % | |
| input voltage | 19 29 ms | |
| ON-delay time | 10 24 ms | |
| OFF-delay time | 10 24 115 | |
| Overload relay | | |
| product function | | |
| overload protection | Yes | |
| phase failure detection | Yes | |
| asymmetry detection | Yes | |
| ground fault detection | Yes | |
| test function | Yes | |
| external reset | Yes | |
| reset function | Manual, automatic and remote | |
| trip class | CLASS 5 / 10 / 20 (factory set) / 30 | |
| adjustable current response value current of the current- dependent overload release | 0.75 3.4 A | |
| tripping time at phase-loss maximum | 3 s | |
| relative repeat accuracy | 1 % | |
| number of NC contacts of auxiliary contacts of overload | 1 | |
| relay number of NO contacts of auxiliary contacts of overload | 1 | |
| relay | | |
| operational current of auxiliary contacts of overload relay | - | |
| • at AC at 600 V | 5 A | |
| • at DC at 250 V | | |
| contact rating of auxiliary contacts of overload relay according to UL | 5A@600VAC (B600), 1A@250VDC (R300) | |
| insulation voltage (Ui) | | |
| with single-phase operation at AC rated value | 600 V | |
| with multi-phase operation at AC rated value | 300 V | |
| Disconnect Switch | | |
| response value of switch disconnector | 30A / 600V | |
| design of fuse holder | non-fusible | |
| operating class of the fuse link | non-fusible | |
| Enclosure | | |
| degree of protection NEMA rating of the enclosure | NEMA 4x 304 stainless steel enclosure | |
| design of the housing | dustproof, waterproof & resistant to corrosion | |
| Mounting/wiring | | |
| mounting position | Vertical | |
| fastening method | Surface mounting and installation | |
| type of electrical connection for supply voltage line-side | Box lug | |
| tightening torque [lbf·in] for supply | 35 35 lbf in | |
| type of connectable conductor cross-sections at line-side | 1x (14 2 AWG) | |
| at AWG cables single or multi-stranded | | |
| temperature of the conductor for supply maximum permissible | 75 °C | |
| material of the conductor for supply | AL or CU | |
| type of electrical connection for load-side outgoing feeder | Screw-type terminals | |
| tightening torque [lbf·in] for load-side outgoing feeder | 20 24 lbf·in | |
| type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded | 2x (14 10 AWG) | |
| temperature of the conductor for load-side outgoing feeder | 75 °C | |
| | | |

| maximum permissible | | |
|--|---|--|
| material of the conductor for load-side outgoing feeder | CU | |
| type of electrical connection of magnet coil | Screw-type terminals | |
| tightening torque [lbf·in] at magnet coil | 5 12 lbf·in | |
| type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded | 2x (16 12 AWG) | |
| temperature of the conductor at magnet coil maximum permissible | 75 °C | |
| material of the conductor at magnet coil | CU | |
| type of electrical connection at contactor for auxiliary contacts | Screw-type terminals | |
| tightening torque [lbf·in] at contactor for auxiliary contacts | 10 15 lbf·in | |
| type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded | 1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG) | |
| temperature of the conductor at contactor for auxiliary contacts maximum permissible | 75 °C | |
| material of the conductor at contactor for auxiliary contacts | CU | |
| type of electrical connection at overload relay for auxiliary contacts | Screw-type terminals | |
| tightening torque [lbf-in] at overload relay for auxiliary contacts | 7 10 lbf·in | |
| type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded | 2x (20 14 AWG) | |
| temperature of the conductor at overload relay for auxiliary contacts maximum permissible | 75 °C | |
| material of the conductor at overload relay for auxiliary contacts | CU | |
| Short-circuit current rating | | |
| design of the fuse link for short-circuit protection of the main circuit required | 10kA@600V (Class H or K); 100kA@600V (Class R or J) | |
| certificate of suitability | NEMA ICS 2; UL 508; CSA 22.2, No.14 | |
| Further information | | |
| Industrial Controls - Product Overview (Catalogs, Broch www.usa.siemens.com/iccatalog Industry Mall (Online ordering system) | ures,) | |

Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:84DUB95WDH


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/US/en/ps/US2:84DUB95WDH

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:84DUB95WDH&lang=en

Certificates/approvals https://support.industry.siemens.com/cs/US/en/ps/US2:84DUB95WDH/certificate



last modified:

1/25/2022 🖸