

### Part Number: XZMDK87W

1.6 x 0.6mm Right Angle SMD Chip LED Lamp


#### Features

- Ideal for indication light on hand held products
- Long life and robust package
- Standard Package: 2,000pcs/ Reel
- MSL (Moisture Sensitivity Level): 3
- Halogen-free
- RoHS compliant





ATTENTION OBSERVE PRECAUTIONS FOR HANDLING ELECTROSTATIC DISCHARGE SENSITIVE DEVICES



1. All dimensions are in millimeters (inches).

2. Tolerance is  $\pm 0.1(0.004")$  unless otherwise noted.

3. Specifications are subject to change without notice.

Absolute Maximum Ratings (T <sub>A</sub> =25°C)		Red (AlGaInP)	Unit	
Reverse Voltage	$V_{\mathrm{R}}$	5	V	
Forward Current	$\mathbf{I}_{\mathbf{F}}$	30	mA	
Forward Current (Peak) 1/10 Duty Cycle 0.1ms Pulse Width	$i_{FS}$	185	mA	
Power Dissipation	$\mathbf{P}_{\mathrm{D}}$	75	mW	
Operating Temperature	TA	-40 ~ +85	°C	
Storage Temperature	Tstg	-40 ~ +85	C	

A Relative Humidity between 40% and 60% is recommended in ESD-protected work areas to reduce static build up during assembly process (Reference JEDEC/JESD625-A and JEDEC/J-STD-033)

Operating Characteristics (T <sub>A</sub> =25°C)	Red (AlGaInP)	Unit	
Forward Voltage (Typ.) (I <sub>F</sub> =20mA)	$V_{\rm F}$	1.95	V
Forward Voltage (Max.) (I <sub>F</sub> =20mA)	$V_{\rm F}$	2.5	v
Reverse Current (Max.) (V <sub>R</sub> =5V)	$I_R$	10	μΑ
Wavelength of Peak Emission CIE127-2007* (Typ.) (I <sub>F</sub> =20mA)	λP	645*	nm
Wavelength of Dominant Emission CIE127-2007* (Typ.) (I <sub>F</sub> =20mA)	λD	630*	nm
Spectral Line Full Width At Half-Maximum (Typ.) (I <sub>F</sub> =20mA)	$ riangle\lambda$	28	nm
Capacitance (Typ.) (V <sub>F</sub> =0V, f=1MHz)	С	35	pF


Part Number	Emitting Color	Emitting Material	Lens-color	Luminous I CIE127- (I <sub>F</sub> =20 mco	2007* mA)	Wavelength CIE127-2007* nm λP	Viewing Angle 20 1/2
				min.	typ.		
XZMDK87W	Red	AlGaInP	Water Clear	120 40*	218 79*	645*	110°

\*Luminous intensity value and wavelength are in accordance with CIE127-2007 standards.


Dec 01,2020

XDSA4981 V15-X Layout: Maggie L.






Relative Intensity Vs. CIE Wavelength




Spatial Distribution





## LED is recommended for reflow soldering and soldering profile is shown below.



measured on the package body surface facing up during reflow. 2. Do not apply any stress to the LED during high temperature conditions. 3. Maximum number of soldering passes: 2



✤ The device has a single mounting surface. The device must be mounted according to the specifications.


#### Recommended Soldering Pattern (Units : mm; Tolerance: ± 0.1)

0.9

1.6


1

0.9






Reel Dimension (Units : mm)



## Tape Specification (Units : mm)



#### Remarks:

If special sorting is required (e.g. binning based on forward voltage, Luminous intensity / luminous flux, or wavelength), the typical accuracy of the sorting process is as follows:


- 1. Wavelength: +/-1nm
- 2. Luminous intensity / luminous flux: +/-15%

3. Forward Voltage: +/-0.1V

Note: Accuracy may depend on the sorting parameters.



# PACKING & LABEL SPECIFICATIONS



(33P) BIN CODE:XXXX

RoHS Compliant Made in China

(9D) D/C:XXXX

#### TERMS OF USE

- 1. Data presented in this document reflect statistical figures and should be treated as technical reference only.
- 2. Contents within this document are subject to improvement and enhancement changes without notice.
- 3. The product(s) in this document are designed to be operated within the electrical and environmental specifications indicated on the datasheet. User accepts full risk and responsibility when operating the product(s) beyond their intended specifications.

(4L) COO:CN

- 4. The product(s) described in this document are intended for electronic applications in which a person's life is not reliant upon the LED. Please consult with a SunLED representative for special applications where the LED may have a direct impact on a person's life.
- 5. The contents within this document may not be altered without prior consent by SunLED.
- 6. Additional technical notes are available at https://www.SunLEDusa.com/TechnicalNotes.asp

Dec 01,2020

XDSA4981 V15-X Layout: Maggie L.