SIEMENS

Data sheet

3RA2215-0DA15-2BB4



Fuseless motor starter Reversing operation 600VAC Size S00 0.22-0.32a 24V DC screw connection For screw mounting Or 35 mm rail-mounting Type of coordination 2 IQ = 150 KA Also full fills type Of coordination 1 1NO+1NC (MSP) 1NC (per contactor)

product brand name	SIRIUS		
product designation	non-fused motor starter 3RA2		
design of the product	reversing starter		
manufacturer's article number			
 of the supplied contactor 	3RT2015-1BB42		
 of the supplied circuit-breakers 	3RV2011-0DA15		
 of the supplied link module 	3RA1921-1DA00		
General technical data			
size of the circuit-breaker	S00		
size of load feeder	S00		
product extension auxiliary switch	Yes		
insulation voltage with degree of pollution 3 at AC rated value	690 V		
degree of pollution	3		
surge voltage resistance rated value	6 kV		
shock resistance according to IEC 60068-2-27	6g / 11 ms		
mechanical service life (switching cycles) of contactor typical	30 000 000		
type of assignment	2		
Ambient conditions			
ambient temperature			
during operation	-20 +60 °C		
during storage	-50 +80 °C		
during transport	-55 +80 °C		
Main circuit			
number of poles for main current circuit	3		
design of the switching contact	electromechanical		
adjustable current response value current of the current-dependent overload release	0.22 0.32 A		
operating voltage			
rated value	690 V		
at AC-3 rated value maximum	690 V		
operating frequency rated value	50 60 Hz		
operational current at AC-3 at 400 V rated value	0.3 A		
operating power at AC-3			
at 400 V rated value	90 W		
at 500 V rated value	90 W		
at 690 V rated value	120 W		
Control circuit/ Control			
control supply voltage at DC			

rated value	24 V			
holding power of magnet coil at DC	4 W			
Auxiliary circuit				
number of NC contacts for auxiliary contacts	2			
number of NO contacts for auxiliary contacts	1			
Protective and monitoring functions				
trip class	CLASS 10			
design of the overload release	thermal (bimetallic)			
response value current of instantaneous short-circuit trip unit	4.16 A			
Short-circuit protection				
product function short circuit protection	Yes			
design of the short-circuit trip	magnetic			
conditional short-circuit current (Iq)				
• at 690 V according to IEC 60947-4-1 rated value	100 000 A			
 at 400 V according to IEC 60947-4-1 rated value 	153 000 A			
 at 500 V according to IEC 60947-4-1 rated value 	100 000 A			
Installation/ mounting/ dimensions				
mounting position	vertical			
fastening method	Snap-mounted to DIN rail or	screw-mounted with ac	Iditional push-in lug	
height	170 mm			
width	90 mm			
depth	97.1 mm			
required spacing				
for grounded parts				
— forwards	0 mm			
— backwards	0 mm			
— upwards	20 mm			
— at the side	9 mm			
— downwards	10 mm			
for live parts				
— forwards	0 mm			
— backwards	0 mm			
— upwards	20 mm			
— downwards	10 mm			
— at the side	9 mm			
Connections/ Terminals				
type of electrical connection for main current circuit	screw-type terminals			
type of connectable conductor cross-sections				
for main contacts stranded	0.5 4 mm², 2x (0.75 2.5	i mm²)		
at AWG cables for main contacts	2x (20 16), only for contactor 2x (18 14), 2x 12			
connectable conductor cross-section for main contacts finely stranded with core end processing	0.5 2.5 mm ²			
Safety related data				
B10 value with high demand rate according to SN 31920	1 000 000			
proportion of dangerous failures with high demand rate according to SN 31920	73 %			
protection class IP on the front according to IEC 60529	IP20			
touch protection on the front according to IEC 60529	finger-safe, for vertical conta	act from the front		
Certificates/ approvals				
		For use in hazard-	Declaration of	
General Product Approval		ous locations	Conformity	



Confirmation









Declaration of Conformity

Test Certificates

Marine / Shipping



Special Test Certific-<u>ate</u>

Type Test Certificates/Test Report







Marine / Shipping

other Railway









Confirmation

Vibration and Shock

Dangerous Good

Transport Informa-<u>tion</u>

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2215-0DA15-2BB4

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2215-0DA15-2BB4

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RA2215-0DA15-2BB4


Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax de.aspx?mlfb=3RA2215-0DA15-2BB4&lang=en


Characteristic: Tripping characteristics, I2t, Let-through current


https://support.industry.siemens.com/cs/ww/en/ps/3RA2215-0DA15-2BB4/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2215-0DA15-2BB4&objecttype=14&gridview=view1







last modified: 12/15/2020 ☑