300 WATTS

CE-300 SERIES AC-DC

• EN 60950-1 ITE Certification

Class B Emissions per EN 55022

FEATURES:

- RoHS Compliant
- Universal 85-264 VAC Input
- Compact 4.9" x 8.5" x 1.95 Size Harmonic Current per EN 61000-3-2
- 2 Year Warranty
- One to Five Tightly Regulated Outputs



FAN/COVER

SAFETY SPECIFICATIONS								
General				Protection Overvoltag Pollution D	Class: e Category: egree:	 2		
CRU Underwriters Laboratories File E137708/E140259				UL 60950-1 CAN/CSA-0	UL 60950-1:2007, 2 nd Edition CAN/CSA-C22.2 No. 60950-1-07, 2 nd Edition			
IECEE SCHEME	CB Rep Nationa	oorts/Certificat al and Group [es (including a Deviations)	^{II} IEC 62368-	EC 62368-1:2014, 2nd Edition			
SUD	TUV SUD America				EN 62368-1:2014, 2nd Edition			
CE	CE Low Voltage Directive RoHS Directive (Recast)				(2014/35/EU of February 2014) (2015/863/EU of March 2015)			
LIK	Electrical Equipment (Safety) Regulations 2016 SI No. 1101							
Restriction of the Use of Certain Hazardous Substances in EEE Regulations 2012 SI No. 3032 + 2019 SI No.492								
			MODEL	LISTING				
MODEL NO) .							
CE-300-500	1 ว	+5V/4UA	+24V/4A	+12V/6A	-5V/1A	-12V/2A		
CE-300-500	2	+5V/40A	+12V/0A	-12V/0A	-3V/1A 15\//1A	+24V/2A +15\//2A		
CE-300-500	3 1	+5V/40A	+120/0A	+24V/3A	-13V/1A 12\//1A	+13V/2A		
CE-300-500	+ 5	+2/1//8A	+24V/4A +12\//8Δ	24V/3A +5\//6Δ	-12V/1A -15\//1A	+12V/2A +15\//2Δ		
CE-300-500	6	+24V/0A +2/1\//8A	21\//Δ	+5\//6Δ	-15V/1A	+15\//2A		
CE-300-501	2	+5V/40A	+28\//3A	+12V/6A	-5V/2A	-12\//2A		
CE-300-501	3	+5V/40A	+3.3V/6A	+24V/4A	-5V/1A	12V/2A		
CE-300-400	1	+5V/40A	+12V/8A	-5V/5A		-12V/2A		
CE-300-400	2	+5V/40A	+24V/4A	+12V/6A		-12V/2A		
CE-300-400	3	+5V/40A	+24V/4A	+15V/4A		-15V/2A		
CE-300-4004	4	+24V/8A	+12V/8A	+5V/6A		-12V/2A		
CE-300-400	5	+5V/40A	-5.2V/12A	+12V/6A		-12V/2A		
CE-300-400	6	+24V/8A	+12V/8A		-12V/1.5A	5V/2A		
CE-300-400	7	+24V/8A	+15V/6A	+5V/6A		-15V/2A		
CE-300-4009	9	+24V/8A	+12V/8A	+5V/10A		-12V/2A		
CE-300-401	1	+5V/40A	+3.3/12A		+12V/2A	-12V/2A		
CE-300-300	1	+5V/40A	+12V/8A	-12V/6A				
CE-300-3002	2	+5V/40A	+12V/8A	+24V/3A				
CE-300-3003	3	+5V/40A	+15V/6A	-15V/4A				
CE-300-3004	4	+12V/16A	-12V/8A	+5V/6A				
CE-300-300	6	+5V/40A	+3.3/12A		+12V/2A			
CE-300-200	1	+5V/40A	+24V/4A					
CE-300-2002	2	+12V/16A	-12V/8A					
CE-300-2003	3	+15V/13A	-15V/6A					
CE-300-2004	4	+24V/8A	-24V/4A					
CE-300-100	1	5V/60A						
CE-300-1002	2	12V/25A						
CE-300-1003	3	15V/20A						
CE-300-1004	4	24V/12A						

CE-300							
OUTPUT SPECIF	ICATIO	NS					
300W							
Outputs 1 – 5:	± 0.5%	(All ou					

C

Total Output Power	300W				
Output Voltage Centering	Outputs 1 – 5:	$\pm 0.5\%$	(All outputs		
			at 50% load)		
Output Voltage Adjust Range	Outputs 1 – 3:	95 - 105%	/6		
Load Regulation	Outputs 1 – 5:	1.0%	(10-100% load change)		
Source Regulation	Outputs 1 – 5:	0.5%			
Cross Regulation	Outputs 2 – 5:	0.5%	(Output 1 load		
			varied 50-100%)		
Output Noise	Outputs 1 - 5:	1.0%	ł		
Turn on Overshoot	None				
Transient Response	Outputs 1 – 5				
Voltage Deviation	5.0%				
Recovery Time	2mS				
Load Change	50% to 100%				
Output Overvoltage Protection	Output 1:	120% to 1	150% Shuts down all		
(Optional)		outputs.	Cycle input to restart.		
Output Overpower Protection	340 W Min.,		•		
	Outputs cycle or	n/off, auto i	recovery		
Output Overcurrent Protection	Outputs 2,3,4 &	5, 110% N	1in		
Hold Up Time	20 mS min., 300W Output, 120V Input				
Start Up Time	3 Seconds				
INPL	JT SPECIFIC	CATION	S		
Source Voltage	85 – 264 Volts A	١C			
Frequency Range	47 – 63 Hz				
Source Current					
True RMS	5.8A at 85V Inpu	ut			
Peak Inrush	20A				
Peak Repetitve	8.2A at 85V Inpu	ut			
Harmonic Distortion	0.05				
Efficiency	.6880(Varies by model)				
Power Factor	0.90 (300 W, 23	0V)			
ENVIRONMEN	FAL SPECIF	ICATIO	NS		
Ambient Operating	0° C to + 50° C				
Temperature Range	Derating: See Power Rating Chart				
Ambient Storage Temp. Range	- 40° C to + 85° C				
Temperature Coefficient	Outputs 1 – 5: 0.02%/°C				
Altitudo	3,000m ASL - O	perating			
Allilude	12,192m ASL –N	on-Operatii	ng		
GENE	RAL SPECIF		DNS		
Dielectric Strength(8)		_			
Reinforced Insulation	4242 VDC, Prim	ary to Sec	ondary, 1 Sec.		
Basic Insulation	2121 VDC, Prim	ary to Gro	und, 1 Sec.		
Operational Insulation	500 VDC, Secor	ndary to Gr	round, 1 Sec.		
Power Fail Signal	Logic low with in	put power	failure 2 mS		
	minimum prior to	o Output 1	dropping 1%		
Remote On/Off (optional)	Contact closure	shuts off a	Il outputs		
Remote Sense(outputs 1 & 2)	250mV compension	sation of o	utput cable losses		
Weight	3.30 Lbs.				
ELECTROMAGNETIC	C COMPATI	BILITY	SPECIFICATIONS		
Electrostatic Discharge	EN 61000-4-2	+/- 8kV C	contact Discharge		
		+/- 8kV A	ir Discharge		
Radiated Electromagnetic Field	EN 61000-4-3	80MHz-2	.5GHz, 10/m, 80% AM		
EFT/Bursts	EN 61000-4-4	+/- 2 kV			
Surges	EN 61000-4-5	+/- 1 kV [Differential Mode		
		+/- 2 kV (Common Mode		
Conducted Immunity	EN 61000-4-6	.15 to 80	MHz, 3V, 80% AM		
Voltage Dips and Interruptions	EN 61000-4-11	30% Red	uction, 500ms		
		95% Red	luction, 10ms		
		60% Red	uction, 1s (Criteria B)		
	EN 55000	95% Red	uctions, 5000ms		
Radiated Emissions	EN 55022	Class B			
	EN 55022	Class B			
Harmonic Current Emissions	EN 55022 EN 61000-3-2	Class B			

Please specify the following optional features when ordering:

RE - Remote Inhibit

OVP - Overvoltage protection

CE-300 SERIES MECHANICAL SPECIFICATIONS







APPLICATIONS INFORMATION

- Semiconductor case temperatures must not exceed 110°C.
 Each output can deliver its rated current but total output power must not exceed 300 watts.
- Internal fan provides airflow to cool internal components. Area around fan and vent
 around fan and vent
- openings must be kept clear to allow unrestricted airflow in and out of these openings.
 This product is intended for use as a professionally installed component within information technology.
- A minimum load of 10% is required on output one to ensure proper regulation of remaining outputs.
- Remote sense terminals may be used to compensate for cable losses up to 250mV. The use of a twisted pair is recommended as well as a decoupling capacitor (0.1 - 10μF) and a capacitor of 100μF/amp connected across the load side.
- Peak to peak output ripple and noise is measured directly at the output terminals of the power supply, without the use of the probe ground lead or retractable tip, 20 MHz bandwidth.
- 8. This product was type tested and safety certified using the dielectric strength test voltages listed in Table 5B of UL 60950-1. In consideration of Clause 5.2.2, care must be taken to insure that the voltage applied to a reinforced insulation does not overstress basic insulation. Secondary to ground capacitors may need to be removed prior to performing a dielectric strength type test on the end product. It is highly recommended that the DC equivalent test voltages be used when performing a production-line dielectric strength test of the assembled end product. Please consult factory before performing an AC dielectric strength test.
- This power supply has been safety approved and final tested using a DC dielectric strength test. Please consult factory before performing an AC dielectric strength test.
- 10. Maximum screw penetration into chassis mounting holes is .188 inches.

MAXIMUM OUTPUT POWER VS. AMBIENT TEMPERATURE



equivalent crimp terminal housing with Molex 6459 or equivalent crimp terminal.

NOTES

Consult factory for alternate output configurations.

Consult factory for positive, negative or floating outputs.

Refer to Applications Information for complete output power ratings.

All specifications are maximum at 25° C, 300W unless otherwise stated, may vary by model and are subject to change without notice.

