SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3220-2YC24-0UB0



Client order no. : Order no. : Offer no. : Remarks :

Rated data		
Input		
Number of phases	3 AC	
Line voltage	200 240 V +10	% -20 %
Line frequency	47 63 Hz	
Rated voltage	200V IEC	240V NEC
Rated current (LO)	26.30 A	26.30 A
Rated current (HO)	20.80 A	20.80 A
Output		
Number of phases	3 AC	
Rated voltage	200V IEC	240V NEC 1)
Rated power (LO)	7.50 kW	10.00 hp
Rated power (HO)	5.50 kW	7.50 hp
Rated current (LO)	28.00 A	28.00 A
Rated current (HO)	22.00 A	22.00 A
Rated current (IN)	29.00 A	
Max. output current	37.80 A	
Pulse frequency	4 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	

Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications	
Power factor λ	0.70 0.85
Offset factor $\cos \phi$	0.96
Efficiency η	0.96
Sound pressure level (1m)	67 dB
Power loss ³⁾	0.365 kW
Filter class (integrated)	Unfiltered
EMC category (with accessories)	without
Safety function "Safe Torque Off"	without
Communication	

Communication

USS, Modbus RTU, BACnet MS/TP

ltem no. : Consignment no. : Project :

Inputs / outputs		
Standard digital inputs		
Number	6	
Switching level: $0 \rightarrow 1$	11 V	
Switching level: $1 \rightarrow 0$	5 V	
Max. inrush current	15 mA	
Fail-safe digital inputs		
Number	1	
Digital outputs		
Number as relay changeover contact	2	
Output (resistive load)	DC 30 V, 5.0 A	
Number as transistor	0	
Analog / digital inputs		
Number	2 (Differential input)	
Resolution	10 bit	
Switching threshold as digital input		
0 → 1	4 V	
1 → 0	1.6 V	
Analog outputs		
Number	1 (Non-isolated output)	
PTC/ KTY interface		
1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5~^\circ\text{C}$		

Closed-loop control techniques	
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No

SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3220-2YC24-0UB0

Ambient conditions	
Standard board coating type	Class 3C2, according to IEC 60721-3-3: 2002
Cooling	Air cooling using an integrated fan
Cooling air requirement	0.018 m³/s (0.653 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
Ambient temperature	
Operation	-20 45 °C (-4 113 °F)
Transport	-40 70 °C (-40 158 °F)
Storage	-25 55 °C (-13 131 °F)
Relative humidity	
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible
Connections	
Signal cable	
Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 16)
Line side	
Version	screw-type terminal
Conductor cross-section	1.50 16.00 mm² (AWG 16 AWG 6)
Motor end	
Version	Screw-type terminals
Conductor cross-section	1.50 16.00 mm² (AWG 16 AWG 6)
DC link (for braking resistor)	
PE connection	On housing with M4 screw
Max. motor cable length	
Shielded	150 m (492.13 ft)
Unshielded	300 m (984.25 ft)

Me	chanical data	
Degree of protection	IP20 / UL open	type
Frame size	FSC	
Net weight	7.1 kg (15.65	lb)
Dimensions		
Width	140 mm (5.51	in)
Height	295 mm (11.6	1 in)
Depth	218 mm (8.58	in)
	Standards	
Compliance with standards	UL, cUL, CE, C- SEMI F47, REA	Tick (RCM), EAC, KCC, CH
CE marking		2004/108/EC, Low- ive 2006/95/EC
Converter lo	osses to IEC61800-	9-2*
Efficiency class	150	
5	IE2	
Comparison with the reference converter (90% / 100%)	1E2 57.8 %	
Comparison with the reference		
Comparison with the reference converter (90% / 100%)	57.8 %	365.0 W (3.1 %)
Comparison with the reference converter (90% / 100%)	57.8 %	365.0 W (3.1 %)
Comparison with the reference converter (90% / 100%)	57.8 %	365.0 W (3.1 %)
Comparison with the reference converter (90% / 100%)	57.8 %	365.0 W (3.1 %)
Comparison with the reference converter (90% / 100%) 247.0 W (2.1 %) 100%	57.8 %	•
Comparison with the reference converter (90% / 100%) 247.0 W (2.1 %)	57.8 % 292.0 W (2.5 %)	365.0 W (3.1 %) ■ 184.0 W (1.6 %)
Comparison with the reference converter (90% / 100%) 247.0 W (2.1 %) 100%	57.8 % 292.0 W (2.5 %)	•

The percentage values show the losses in relation to the rated apparent power of the converter.

90% **f**

50%

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

¹⁾The output current and HP ratings are valid for the voltage range 220V-240V

³⁾Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.

SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3220-2YC24-0UB0

Operator panel: Basic Operator Panel (BOP-2)

Screen	
Display design	LCD, monochrome
Mechanical data	
Degree of protection	IP55 / UL type 12
Net weight	0.140 kg (0.31 lb)
Dimensions	
Width	70.00 mm (2.76 in)
Height	106.85 mm (4.21 in)
Depth	19.60 mm (0.77 in)

Ambient conditions		
Ambient temperature		
Operation	0 50 °C (32 122 °F)	
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
Relative humidity at 25°C during]	
Max. operation	95 %	
	A	
Approvals		
Certificate of suitability	CE, cULus, EAC, KCC, RCM	