

**MLFB-Ordering data** 

6SL3220-3YE50-0CF0

No image available for this configuration.

Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data			General tech. specifications	
Input			Power factor λ	0.90 0.95
Number of phases	3 AC		Offset factor cos φ	0.99
Line voltage	380 480 V	+10 % -20 %	Efficiency η	0.98
Line frequency	47 63 Hz		Sound pressure level (1m)	74 dB
Rated voltage	400V IEC	480V NEC	Power loss	3.670 kW
Rated current (LO)  Rated current (HO)	308.00 A 275.00 A	301.00 A 263.00 A	Filter class (integrated)	RFI suppression filter for Category C3
Output		203.0071	EMC category (with accessories)	Category C3
Number of phases	3 AC		Ambient conditions	
Rated voltage	400V IEC	480V NEC	Ambient	conditions
Rated power (LO)	160.00 kW	250.00 hp	Standard board coating type	Class 3C2, according to IEC 60721-3-3: 2002
Rated power (HO)	132.00 kW	150.00 hp		
Rated current (LO)	302.00 A	302.00 A	Cooling	Air cooling using an integrated fan
Rated current (HO)	250.00 A	240.00 A		
Rated current (IN)	309.00 A		Cooling air requirement	0.210 m <sup>3</sup> /s (7.416 ft <sup>3</sup> /s)
Max. output current	408.00 A		Installation altitude	1000 m (3280.84 ft)
Pulse frequency	2 kHz		Ambient temperature	
Output frequency for vector control	0 200 Hz		Operation	-20 45 °C (-4 113 °F)
			Transport	-40 70 °C (-40 158 °F)
Output frequency for V/f control	0 550 Hz		Storage	-25 55 °C (-13 131 °F)
			Relative humidity	
			Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible

## Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time



**MLFB-Ordering data** 

6SL3220-3YE50-0CF0

No image available for this configuration.

			Figure similar	
Mechanical data		Closed-loop control techniques		
Degree of protection	IP20 / UL open type			
Size	<b>V/f linear / square-law / param</b> FSG		e <b>rizable</b> Yes	
Net weight	105 kg (231.49 lb)	V/f with flux current control (FCC)	Yes	
Width	305 mm (12.01 in)	V/f ECO linear / square-law	Yes	
Height	999 mm (39.33 in)	Sensorless vector control	Yes	
Depth	369 mm (14.53 in)	Vector control, with sensor	No	
- -		Encoderless torque control	Yes	
Inputs / out	tputs			
Standard digital inputs		Torque control, with encoder	No	
Number	6	Communication		
Switching level: 0→1	11 V	Communication PROFINET, EtherNet/IP		
Switching level: 1→0	5 V			
Max. inrush current	15 mA	Connections		
Fail-safe digital inputs		Signal cable		
Number	1	Conductor cross-section	0.15 1.50 mm <sup>2</sup> (AWG 24 AWG 16)	
Digital outputs		Line side		
Number as relay changeover contact	2	Version	M10 screw	
Output (resistive load)	DC 30 V, 5.0 A	Conductor cross-section	35.00 185.00 mm <sup>2</sup> (AWG 1 MCM 2 x 350)	
Number as transistor	0	Motor end		
Analog / digital inputs		Version	M10 screw	
Number	2 (Differential input)	Conductor cross-section	35.00 185.00 mm <sup>2</sup> (AWG 1 MCM 2 x 350)	
Resolution	10 bit	DC link (for braking resistor)	,	
Switching threshold as digital in	put	PE connection	M10 screw	
0→1	4 V		IVI I O SCIEW	
1→0	1.6 V	Max. motor cable length	200 (656 47 %)	
Analog outputs		Shielded	200 m (656.17 ft)	
Number	1 (Non-isolated output)			

1 motor temperature sensor input, sensors that can be connected: PTC, KTY and Thermo-Click, accuracy  $\pm 5~^{\circ}\text{C}$ 

PTC/ KTY interface



MLFB-Ordering data

6SL3220-3YE50-0CF0

90%

No image available for this configuration.

Figure similar

## Converter losses to EN 50598-2\* **Standards** Efficiency class IE2 UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI Compliance with standards F47, REACH Comparison with the reference converter (90% / -43.00 % 100%) EMC Directive 2004/108/EC, Low-Voltage **CE** marking Directive 2006/95/EC 3661.0 W (1.75 %) 2274.9 W (1.09 %) 2777.5 W (1.33 %) 1667.3 W (0.80 %) 1211.6 W (0.58 %) 1390.7 W (0.66 %) 50% 856.1 W (0.41 %) 931 W (0.44 %) 25%

 $The \ percentage \ values \ show \ the \ losses \ in \ relation \ to \ the \ rated \ apparent \ power \ of \ the \ converter.$ 

50%

The diagram shows the losses for the points (as per standard EN 50598) of the relative torque generating current (I) over the relative motor stator frequency(f). The values are valid for the basic version of the converter without options/components.

## Operator panel: Intelligent Operator Panel (IOP-2)

Screen		Ambie	Ambient conditions	
Display design	LCD colors	Ambient temperature during		
		Operation	0 50 °C (32 122 °F)	
Screen resolution	320 x 240 Pixel		55 °C only with door mounting kit	
Mechanical data		Storage	-40 70 °C (-40 158 °F)	
Degree of protection	IP55 / UL type 12	Transport	-40 70 °C (-40 158 °F)	
Net weight	0.13 kg (0.30 lb)	Relative humidity at 25°C di	uring	
Width	70.0 mm (2.76 in)	Max. operation	95 %	
Height	106.85 mm (4.21 in)			
Depth	19.65 mm (0.77 in)	P	Approvals	
T.	(2 7.1)	Certificate of suitability	CE, cULus, EAC, KCC, RCM	

<sup>\*</sup>converted values