

# ST-REL3-KG 24/21/SO46 - Relay connectors



2826091

<https://www.phoenixcontact.com/us/products/2826091>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in relay interface for protection against interference on the control side, with soldered-in miniature switching relay, contacts (AgNi): medium to large loads, 1 changeover contact, input voltage 24 V AC/DC

## Your advantages

- Use of AC output cards, resulting in residual AC currents
- Resistant to interference currents
- Applications with long control lines
- High relay release voltage

## Commercial data

Item number	2826091
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	CK6122
Catalog page	Page 446 (C-5-2019)
GTIN	4017918077839
Weight per piece (including packing)	41.17 g
Weight per piece (excluding packing)	38.9 g
Customs tariff number	85364190
Country of origin	DE

# ST-REL3-KG 24/21/SO46 - Relay connectors



2826091

<https://www.phoenixcontact.com/us/products/2826091>

## Technical data

### Product properties

Product type	Single relay
Mechanical service life	approx. $2 \times 10^7$ cycles

### Insulation characteristics

Insulation	Basic insulation
------------	------------------

### Insulation characteristics

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

### Electrical properties

Maximum power dissipation for nominal condition	0.62 W
Test voltage (Winding/contact)	2.5 kV AC (50 Hz, 1 min., winding/contact)

### Input data

#### Coil side

Nominal input voltage $U_N$	24 V AC
Input voltage range	21.6 V AC ... 26.4 V AC (20 °C)
Drive and function	monostable
Drive (polarity)	polarized
Typical input current at $U_N$	26 mA
Typical response time	8 ms
Typical release time	10 ms
Protective circuit	Bridge rectifier; Bridge rectifier Surge protection; Varistor RC element; RC element
Operating voltage display	Yellow LED

### Output data

#### Switching

Contact switching type	1 changeover contact
Type of switch contact	Single contact
Contact material	AgNi
Maximum switching voltage	250 V AC/DC
Limiting continuous current	6 A
Maximum inrush current	8 A
Interrupting rating (ohmic load) max.	140 W (at 24 V DC) 60 W (at 48 V DC) 45 W (at 60 V DC)

# ST-REL3-KG 24/21/SO46 - Relay connectors



2826091

<https://www.phoenixcontact.com/us/products/2826091>

	35 W (at 110 V DC)
	55 W (at 220 V DC)
	1500 VA (for 250 V AC)

## Dimensions

Width	20.8 mm
Height	42.5 mm
Depth	112 mm

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

## Standards and regulations

Standards/regulations	IEC 60664
	EN 50178

## Mounting

Mounting type	Plug-in mounting
Mounting position	any


# ST-REL3-KG 24/21/SO46 - Relay connectors

2826091

<https://www.phoenixcontact.com/us/products/2826091>

## Drawings

Circuit diagram



# ST-REL3-KG 24/21/SO46 - Relay connectors



2826091

<https://www.phoenixcontact.com/us/products/2826091>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2826091>



**EAC**

Approval ID: TR\_TS\_D\_00573\_c

# ST-REL3-KG 24/21/SO46 - Relay connectors



2826091

<https://www.phoenixcontact.com/us/products/2826091>

## Classifications

### ECLASS

ECLASS-11.0	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601

### ETIM

ETIM 9.0	EC001437
----------	----------

### UNSPSC

UNSPSC 21.0	39122300
-------------	----------

# ST-REL3-KG 24/21/SO46 - Relay connectors



2826091

<https://www.phoenixcontact.com/us/products/2826091>

## Environmental product compliance

REACH SVHC	Lead 7439-92-1
	Hexahydromethylphthalic anhydride
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)