

2356607-2 ✓ ACTIVE

AMP | Superseal Pro


TE Internal #: 2356607-2

Housing for Female Terminals, Wire-to-Wire, 4 Position, .197 in [5 mm] Centerline, Sealable, Black, Wire & Cable, Signal, Superseal Pro

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings



Connector System: **Wire-to-Wire**

Number of Positions: **4**

Connector & Housing Type: **Housing for Female Terminals**

Centerline (Pitch): **5 mm [ .197 in ]**

Sealable: **Yes**

## Features

### Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

### Configuration Features

Number of Positions	4
Number of Rows	2

### Electrical Characteristics

Operating Voltage	12 VDC
Nominal Voltage Architecture	12 V

### Body Features



Primary Product Color	Black
-----------------------	-------

Connector & Keying Code	B
-------------------------	---

### Contact Features

Contact Size	1.2mm
--------------	-------

Contact Type	Receptacle
--------------	------------

Mating Tab Width	1.2 mm[.047 in]
------------------	-----------------

### Mechanical Attachment

Mating Alignment Type	Keyed
-----------------------	-------

Mating Alignment	With
------------------	------

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

### Housing Features

Centerline (Pitch)	5 mm[.197 in]
--------------------	---------------

### Dimensions

Row-to-Row Spacing	5.5 mm[.216 in]
--------------------	-----------------

### Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
-----------------------------	----------------

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------

### Operation/Application

Circuit Application	Signal
---------------------	--------

### Other

Connector Position Assurance Capable	No
--------------------------------------	----

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
--	---

Halogen Content	Not Low Halogen - contains Br or Cl > 900
-----------------	---



ppm.

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts




TE Part # 963143-1  
MQS BLINDSTOPFEN



TE Part # CAT-M4595-T273  
MCON Receptacle and Tab




TE Part # 2356631-2  
4POS,MCON 1.2,TAB HSG ASSY,SLD, COD B




TE Part # 1010-066-0406  
SEAL, INTF, 4P, RED-ORG, SL RET, DT


### Also in the Series | Superseal Pro




Automotive Housings(87)



Connector Backshells(14)



Connector Caps & Covers(1)



Other Automotive Connector Accessories(1)

### Customers Also Bought



TE Part #788189-2  
CPC 17-3 RCPT ASY,REV SEX



TE Part #2-330648-1  
PIDG 22-16 22-18 MIL R 4; TAPE



TE Part #2177090-3  
STEEL,OUTER FERRULE,8MM HV, 25SQMM



TE Part #1-1633961-2  
CRIMPER, INSULATION F PREMIUM



## Documents

### Product Drawings

4POS,MCON 1.2,REC HSG ASSY,SLD,COD B

English

4POS,MCON 1.2,REC HSG ASSY,SLD,COD B

English

### CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2356607-2\_C.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2356607-2\_C.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2356607-2\_C.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

Superseal Pro Connector series-Applications

English

Product Specification

English

Product Specification

English

2356607-2

Housing for Female Terminals, Wire-to-Wire, 4 Position, .197 in [5 mm] Centerline,  
Sealable, Black, Wire & Cable, Signal, Superseal Pro

