

Description: 1608 2.4-2.5GHz Balun

PART NUMBER: BLN1608LL01R2400A

Features:

- Compact size: 1.6x0.8x0.65mm
- RoHS compliant

Applications:

- WLAN, 802.11a/b/g/n
- Bluetooth
- ISM Band

ELECTRICAL SPECIFICATIONS

DESCRIPTION	Value
Pass Band	2400~2500 MHz
Unbalanced Impedance	50Ω
balanced Impedance	100Ω
Insertion Loss	1.1 dB (Max.) at 25°C 1.4 dB (Max.) at -25 ~ 85°C
V.S.W.R / Return Loss	2.0(Max) / 10 dB (Min.)
Phase Difference	180 ±10 degree
Amplitude Difference	2 dB (Max)

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION



This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:



Description: 1608 2.4-2.5GHz Balun


PART NUMBER: BLN1608LL01R2400A

MECHANICAL DIMENSION

Outline

Termination


Mechanical



	Terminal name	function
	P1	Unbal.
V	P2	GND
	P3	Balanced
	P4	Balanced
	P5	GND
	P6	Not Connect

	Dimension
L (mm)	1.60 ±0.15
W (mm)	0.80 ±0.15
T (mm)	0.65 ±0.15
P1 (mm)	0.30 ±0.15
P2 (mm)	0.30 ± 0.15
P3 (mm)	0.30 ± 0.15
P4 (mm)	0.30 ± 0.15
P5 (mm)	0.30 ± 0.15
P6 (mm)	0.30 ± 0.15
D1 (mm)	0.10 ±0.05
D2 (mm)	0.55 ±0.15
D3 (mm)	0.25 ±0.15
D4 (mm)	0.20 ±0.15

Reference design of EVB




Line width should be designed to match 50Ω characteristic impedance, depending on PCB material and thickness.



Description: 1608 2.4-2.5GHz Balun

PART NUMBER: BLN1608LL01R2400A

ELECTRICAL PERFORMANCES



- Unbalanced port return loss (Sss11)
- Balanced port return loss (Sdd22)
- Insertion loss (Sds21, differential port to single-ended port)
- Imbalance (S21/S31 amplitude and phase difference)
- Measured on Agilent E5071C Network Analyzer

Frequency Characteristics



Description: 1608 2.4-2.5GHz Balun

PART NUMBER: BLN1608LL01R2400A

REVISION HISTORY

Revision	Date	Description	
Version 1	Oct 06 2020	- New issue	