SIEMENS

Data sheet

3RA6400-2EB42



SIRIUS Compact load feeder DOL starter for IO-Link 690 V 24 V DC 8...32 A IP20 Connection main circuit: Spring-type terminal Connection control circuit: Spring-type terminal


product brand name	SIRIUS		
product designation	Compact starter for IO-Link		
design of the product	direct starter		
product type designation	3RA64		
General technical data			
product function control circuit interface to parallel wiring	No		
product extension auxiliary switch	Yes		
power loss [W] for rated value of the current at AC in hot operating state	5.4 W		
• per pole	1.8 W		
power loss [W] for rated value of the current without load current share typical	3.4 W		
insulation voltage rated value	690 V		
degree of pollution	3		
surge voltage resistance rated value	6 000 V		
degree of protection NEMA rating	other		
shock resistance	a=60 m/s2 (6g) with 10 ms per 3 shocks in all axes		
vibration resistance	f= 4 5.8 Hz, d= 15 mm; f= 5.8 500 Hz, a= 20 m/s ² ; 10 cycles		
mechanical service life (switching cycles)			
 of the main contacts typical 	10 000 000		
 of auxiliary contacts typical 	10 000 000		
 of the signaling contacts typical 	10 000 000		
electrical endurance (switching cycles) of auxiliary contacts			
 at DC-13 at 6 A at 24 V typical 	30 000		
 at AC-15 at 6 A at 230 V typical 	200 000		
type of assignment	continous operation according to IEC 60947-6-2		
reference code acc. to IEC 81346-2	Q		
Substance Prohibitance (Date)	01.05.2012 00:00:00		
Ambient conditions			
installation altitude at height above sea level maximum	2 000 m		
 ambient temperature during operation 	-20 +60 °C		
 ambient temperature during storage 	-55 +80 °C		
 ambient temperature during transport 	-55 +80 °C		
relative humidity during operation	10 90 %		
Main circuit			
number of poles for main current circuit	3		
adjustable current response value current of the	8 32 A		
-			


current-dependent overload release	-
formula for making capacity limit current	12 x le
formula for breaking capacity limit current	10 x le
yielded mechanical performance for 4-pole AC motor	
 at 400 V rated value 	15 kW
• at 500 V rated value	11 kW
• at 690 V rated value	11 kW
 operating voltage at AC-3 rated value maximum 	400 V
operational current	
 at AC at 400 V rated value 	32 A
• at AC-43	
— at 400 V rated value	29 A
— at 500 V rated value	17.6 A
— at 690 V rated value	12.8 A
operating power	
 at AC-3 at 400 V rated value 	15 kW
• at AC-43	
— at 400 V rated value	15 000 W
— at 500 V rated value	11 000 W
— at 690 V rated value	11 000 W
no-load switching frequency	3 600 1/h
operating frequency	
 at AC-41 acc. to IEC 60947-6-2 maximum 	750 1/h
 at AC-43 acc. to IEC 60947-6-2 maximum 	250 1/h
Control circuit/ Control	
type of voltage	DC
holding power	
• at DC maximum	3.4 W
Auxiliary circuit	
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
number of NO contacts of instantaneous short-circuit trip	0
unit for signaling contact	
number of CO contacts of the current-dependent overload release for signaling contact	0
operational current of auxiliary contacts at AC-12 maximum	10 A
operational current of auxiliary contacts at DC-13 at 250 V	0.27 A
Protective and monitoring functions	0.21 A
trip class	CLASS 10 and 20 adjustable
 breaking capacity operating short-circuit current (Ics) at 400 V 	53 44
 at 400 V at 500 V rated value 	53 kA 1 kA
 at 500 V rated value at 690 V rated value 	1 KA 1 kA
UL/CSA ratings	
full-load current (FLA) for 3-phase AC motor	20.4
at 480 V rated value	32 A
yielded mechanical performance [hp] for 3-phase AC motor	
• at 200/208 V rated value	7.5 hp
• at 220/230 V rated value	10 hp
 at 460/480 V rated value 	20 hp
Short-circuit protection	·
	Yes
Short-circuit protection product function short circuit protection design of short-circuit protection	
Short-circuit protection product function short circuit protection	Yes
Short-circuit protection product function short circuit protection design of short-circuit protection	Yes


Installation/ mounting/ dimensions			
mounting position	any		
recommended	vertical, on horizontal standard mounting rail		
fastening method	screw and snap-on mounting		
height	191 mm		
width	- 45 mm		
depth	165 mm		
Connections/ Terminals			
product function			
 removable terminal for main circuit 	Yes		
 removable terminal for auxiliary and control circuit 	Yes		
type of electrical connection			
for main current circuit	spring-loaded terminals		
 for auxiliary and control circuit 	spring-loaded terminals		
type of connectable conductor cross-sections			
for main contacts			
— solid	2x (2.5 6 mm²), 1x 10 mm²		
 finely stranded with core end processing 	2x (2.5 6 mm ²)		
 — finely stranded without core end processing 	2x (2.5 6 mm ²)		
 at AWG cables for main contacts 	2x (14 10), 1x 8		
type of connectable conductor cross-sections			
for auxiliary contacts			
— solid	2x (0.25 1.5 mm²)		
 finely stranded with core end processing 	2x (0.25 1.5 mm ²)		
 — finely stranded without core end processing 	2x (0.25 1.5 mm ²)		
 at AWG cables for auxiliary contacts 	2x (24 16)		
Safety related data			
B10 value with high demand rate acc. to SN 31920	2 000 000		
proportion of dangerous failures			
with high demand rate acc. to SN 31920	50 %		
Communication/ Protocol			
product function bus communication	Yes		
protocol is supported			
IO-Link protocol	Yes		
product function control circuit interface with IO link	Yes		
IO-Link transfer rate	COM2 (38,4 kBaud)		
point-to-point cycle time between master and IO-Link	2.5 ms		
device minimum			
type of voltage supply via input/output link master	No		
data volume			
 of the address range of the inputs with cyclical transfer total 	2 byte		
 of the address range of the outputs with cyclical transfer total 	2 byte		
Electromagnetic compatibility			
conducted interference			
• due to burst acc. to IEC 61000-4-4	4 kV main circuits, 2 kV auxiliary circuits, 2 kV IO-Link, 2 kV limit switches, 2 kV line hand-held device		
• due to conductor-earth surge acc. to IEC 61000-4-5	4 kV main circuits, 0.5 kV auxiliary voltage with upstream overvoltage protection		
 due to conductor-conductor surge acc. to IEC 61000-4-5 	2 kV main circuits, 0.5 kV auxiliary voltage with upstream overvoltage protection		
 due to high-frequency radiation acc. to IEC 61000- 4-6 	0.15-80Mhz at 10V		
field-based interference acc. to IEC 61000-4-3	80 3000 MHz at 10V/m		
electrostatic discharge acc. to IEC 61000-4-2	8 kV		
conducted HF interference emissions acc. to CISPR11	150 kHz 30 MHz Class A		
field-bound HF interference emission acc. to CISPR11	30 1000 MHz Class A		
Supply voltage			

Supply voltage required Auxiliary voltage		Yes			
Display					
number of LEDs			3		
display version as status display of the input/output link device		green/red dual LED			
Certificates/ approval	S				
General Product Ap	proval			EMC	Functional Safety/Safety of Machinery
(SP)		(UL)	EHC	RCM	
Declaration of Conf	ormity	Test Certificat	es Marine / Shippin	g	
CE EG-Konf.	<u>Miscellaneous</u>	<u>Type Test</u> <u>Certificates/Te</u> <u>Report</u>	est as	B U REAU VERITAS	Lloyd's Register uts
Marine / Shipping			other		
PRS	RINA	KMRS RMRS	<u>Confirmation</u>		
Cax online generato http://support.automat Service&Support (M https://support.industr Image database (pro	com/ic10 e ordering system) emens.com/mall/en/er r tion.siemens.com/WW anuals, Certificates, y.siemens.com/cs/ww oduct images, 2D dim	/Catalog/product? /CAXorder/default Characteristics, I /en/ps/3RA6400-2 ension drawings	mlfb=3RA6400-2EB42 .aspx?lang=en&mlfb=3RA	uit diagrams, EPLAN r	nacros,)
Characteristic: Tripp https://support.industr		/en/ps/3RA6400-2	EB42/char		

Further characteristics (e.g. electrical endurance, switching frequency) http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA6400-2EB42&objecttype=14&gridview=view1







last modified:

1/18/2021 🖸