

Feb. 1. 2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

△	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	△	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△						△					
△						△					

APPLICATION STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C	STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C
	VOLTAGE	AC 50 V	OPERATING HUMIDITY RANGE	RELATIVE HUMIDITY : 95 % MAX (NO DEW CONDENSATION IS PERMITTED)
	CURRENT	0.3 A		

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENT	QT	AT
------	-------------	-------------	----	----

CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING	X	X
MARKING	CONFIRMED VISUALLY.		X	X

ELECTRICAL CHARACTERISTICS				
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz).	60 mΩ MAX.	X	X
INSULATION RESISTANCE	100 V DC.	100 MΩ MIN.	X	-
VOLTAGE PROOF	150 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	X

MECHANICAL CHARACTERISTICS				
INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR.	INSERTION FORCE: 55.2 N MAX. WITHDRAWAL FORCE: 2.3 N MIN.	X	-
MECHANICAL OPERATION	50 TIMES INSERTION AND EXTRACTIONS.	1) CONTACT RESISTANCE: 70 mΩ MAX. 2) NO DAMAGE, CRACK AND LOOSENESS OF PART.	X	-
VIBRATION	FREQUENCY: 10 TO 55 Hz, SINGLE AMPLITUDE: 0.75 mm, - m/s ² AT 10 CYCLES FOR 3 DIRECTIONS.	1) NO ELECTRICAL DISCONTINUITY OF 1 μs MIN. 2) NO DAMAGE, CRACK AND LOOSENESS OF PART.	X	-
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		X	-

ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, 90~95 %, 96 h.	1) CONTACT RESISTANCE: 70 mΩ MAX. 2) INSULATION RESISTANCE: 100 MΩ MIN.	X	-
RAPID CHAGE OF TEMPERTURE	TEMPERTURE -55→15~35→ 85→15~35°C TIME 30→ 2~ 3→ 30→ 2~ 3 min. UNDER 5 CYCLES.	3) NO DAMAGE, CRACK AND LOOSENESS OF PART.	X	-
DRY HEAT	EXPOSED AT 85 °C, 96 h.	1) CONTACT RESISTANCE: 70 mΩ MAX.	X	-
COLD	EXPOSED AT -55 °C, 96 h.	2) NO DAMAGE, CRACK AND LOOSENESS OF PART.	X	-
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	NO HEAVY CORROSION.	X	-
SULPHUR DIOXIDE	EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD: JIS C 0090)	1) CONTACT RESISTANCE: 70 mΩ MAX. 2) NO HEAVY CORROSION.	X	-
RESISTANCE TO SOLDERING HEAT	REFLOW RECOMMENDED TEMPERATURE PROFILE TO BE TESTED UNDER THE ABOVE CONDITIONS.	NO MELTING OF RESIN WHICH AFFECTS THE PERFORMANCE OF COMPONENT.	X	-
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 235 °C FOR IMMERSION DURATION, 2 s.	NO PINHOLE OR DEWETTING ON SOLDERED SURFACE.	X	-

REMARKS	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	<i>Mitsukawa</i>	<i>Mitsukawa</i>	<i>M. Sakaki</i>	<i>T. Yoshimura</i>	
UNLESS OTERWISE SPECIFIED, REFER TO JIS C 5402.	99.10.25	99.10.25	99.10.26	99.10.26	
NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST X: APPLICABLE TEST					

HRS HIROSE ELECTRIC CO., LTD.	SPECIFICATION SHEET		PART NO.
			FX11LB -92 S - SV (21)
CODE NO.(OLD)	DRAWING NO.	CODE NO.	1
CL	ELC4 - 152121 - 01	CL 573 - 0153 - 2 - 21	1

TO
PCK