

	39	101.19 [3.984]	40	4-87232-0	
	38	98.65 [3.884]	39	3-87232-9	
	37	96.11 [3.784]	38	3-87232-8	
	36	93.57 [3.684]	37	3-87232-7	-
	35	91.03 [3.584]	36	3-87232-6	
	34	88.49 [3.484]	35	3-87232-5	-
	33	85.95 [3.384]	34	3-87232-4	
	32	83.41 [3.284]	33	3-87232-3	
	31	80.87 [3.184]	32	3-87232-2	
	30	78.33 [3.084]	31	3-87232-1	
	29	75.79 [2.984]	30	3-87232-0	С
	28	73.25 [2.884]	29	2-87232-9	
	27	70.71 [2.784]	28	2-87232-8	
	26	68.17 [2.684]	27	2-87232-7	
4.00	25	65.63 [2.584]	26	2-87232-6	
1.02	24	63.09 [2.484]	25	2-87232-5	
└── [.040] REF.	23	60.55 [2.384]	24	2-87232-4	
	22	58.01 [2.284]	23	2-87232-3	
	21	55.47 [2.184]	22	2-87232-2	
	20	52.93 [2.084]	21	2-87232-1	
1.75	19	50.39 [1.984]	20	2-87232-0	
[.069]	18	47.85 [1.884]	19	1-87232-9	
	17	45.31 [1.784]	18	1-87232-8	
\square	16	42.77 [1.684]	17	1-87232-7	
	15	40.23 [1.584]	16	1-87232-6	
	14	37.69 [1.484]	15	1-87232-5	232
	13	35.15 [1.384]	14	1-87232-4	87
	12	32.61 [1.284]	13	1-87232-3	В
3.99	1 1	30.07 [1.184]	12	1-87232-2	
[.157]	10	27.53 [1.084]	11	1-87232-1	
	9	24.99 [0.984]	10	1-87232-0	
	8	22.45 [0.884]	9	87232-9	
	7	19.91 [0.784]	8	87232-8	
→ 0.63±0.05 [.025±.002] TYP.	6	17.37 [0.684]	7	87232-7	
	5	14.83 [0.584]	6	87232-6	
	4	12.29 [0.484]	5	87232-5	
	3	9.75 [0.384]	4	87232-4	
	2	7.21 [0.284]	3	87232-3	
	1	4.67 [0.184]	2	87232-2	
	0	2.13 [0.084]	1	87232-1	
		Λ	NO OF	PART	
		A	POSN	NUMBER	
THIS DRAWING IS A CONTROLLED DOCU	MENT DWN	31-MAR-97			
	CHK	NDBERG 31-MAR-97	-E TE	TE Connectivity	А
DIMENSIONS: TOLERANCES UNL OTHERWISE SPEC	IFIED: APVD	31-MAR-97 NAME			
mm [INCHES] 0 PLC ± -	S. SHU PRODUCT SI			SSEMBLY, MOD II,	
$1 \text{ PLC} \pm -2 \text{ PLC} \pm 0.13[$	[.005]			CL, RIGHT ANGLE, RE POST, SINGLE ROW	
4 PLC ± - ANGLES ±			CODE DRAWING NO	RESTRICTED TO	
MATERIAL FINISH	WEIGHT	A2 00	779 C- 8723	2 -	
$\boxed{3}$ $\boxed{4}$	CUSTON	/ · · · · /	SCA		

D