


# FSP150-P24 C Series

### FEATURES

- Class-I design
- IEC 62368-1 safety standard
- Low profile 2 x 4 x 1.2 inches
- Input power less than 0.5W @ 0.2W load
- EN 55032 Class B radiated emission
- High altitude 5000 meters operation
- Fan driver 12V



### SAFETY STANDARD APPROVAL



### DESCRIPTION

This AC-DC switching power supplies in a package of 2 x 4 inches is a Class-I PSU. This PSU is capable of delivering 150 watts continuous power at 7 CFM forced air cooling or 100 watts continuous power at convection cooling and 50°C operation temperature. Product is suitable for audio & video, display, information, networking & PoE application.

### INPUT SPECIFICATIONS

Input voltage:	90-264 VAC
Input frequency:	47-63 Hz
Input current:	1.7 A (rms) for 115 VAC 0.8 A (rms) for 230 VAC
Input power consumption	< 0.5W @ 0.2W load
Touch current:	0.75 mA max. @ 264 VAC, 63 Hz

### OUTPUT SPECIFICATIONS

Output voltage/current:	See rating chart.
Fan driver (CN201):	Non-regulated 12V @ 500 mA max.
Total output power:	150W
Protection:	
Over voltage:	Latch off
Short circuit:	Auto recovery
Over current:	Auto recovery
Over temperature:	Latch off
Temperature coefficient:	All outputs ±0.04% /°C maximum
Transient response:	Maximum excursion of 4% or better on all models, recovering to 1% of final value within 500 us after a 25% step load change


### ENVIRONMENTAL SPECIFICATIONS

Operating temperature:	-20°C~+70°C
Storage temperature:	-40°C~+85°C
Relative humidity:	5% to 95% non-condensing
Derating:	Derate from 100% at +50°C linearly to 50% at +70°C, applicable to both convection and forced-air cooling conditions


### GENERAL SPECIFICATIONS

Power factor:	0.9 minimum
Efficiency:	See rating chart.
Hold-up time:	10 ms minimum at 120 VAC
Line regulation:	±0.5% maximum at full load
Inrush current:	80 A @ 115 VAC, at 25°C cold start 160 A @ 230 VAC, at 25°C cold start
Operating altitude:	5000 meters above sea level
Withstand voltage:	3000 VAC from input to output, 1500 VAC from input to ground, 1500 VAC from output to ground
Isolation Resistance:	Input to output 100M ohm @ 500Vdc, 25°C
MTBF:	400,000 hours at full load at 25°C ambient, calculated per TELCORDIA SR-332
EMC Performance	
EN55032	Class B conducted, class B radiated
FCC:	Class B conducted, class B radiated
VCCI:	Class B conducted, class B radiated
EN61000-3-2:	Harmonic distortion, class D
EN61000-3-3:	Line flicker
EN61000-4-2:	ESD, ±8 KV air and ±4 KV contact
EN61000-4-3:	Radiated immunity, 3 V/m
EN61000-4-4:	Fast transient/burst, ±1 KV
EN61000-4-5:	Surge, ±1 KV diff., ±2 KV com
EN61000-4-6:	Conducted immunity, 3 Vrms
EN61000-4-8:	Magnetic field immunity, 1 A/m
EN61000-4-11:	Voltage dip immunity, 30% reduction for 500 ms, criteria A >95% reduction for 10 ms, criteria A >95% reduction for 5000 mS, criteria B

**INPUT VOLTAGE DERATING CURVE**



**OUTPUT POWER DERATING CURVE**




**OUTPUT VOLTAGE/CURRENT RATING CHART**

Model	Output							Efficiency Max. Power 115/230 Vac (typical)
	Voltage	Min. Load	Max. Current convection	Max. Current 7 CFM	Tolerance	Ripple & Noise	Max. Power	
FSP150-P24-C12	12 V	0 A	8.35 A	12.50 A	±3%	120 mV	100 W / 150 W	89 / 91%
FSP150-P24-C54	54 V	0 A	1.85 A	2.78 A	±3%	500 mV	100 W / 150 W	88 / 90%

NOTES:

- Ripple and noise is maximum peak to peak voltage value measured at output within 20 MHz bandwidth, at rated line voltage and output load ranges, and with a 47  $\mu$ F electrical capacitor in parallel with a 0.1  $\mu$ F ceramic capacitor across the output.
- The first value of maximum current is at convection cooling. The second value is with 7 CFM forced air provided by user.

### MECHANICAL SPECIFICATIONS



Pin assignment:

1. Input connector (CN1):

Pin No.	Function	Wafer
1	Line	J.S.T B2P3-VH or equivalent
2	Neutral	
3	Neutral	

Matting connector:

J.S.T housing VHR-3N,  
Crimp PIN SVH-21T-P1.1

Output connector (CN200):

Pin No.	Function	Wafer
1, 2, 3	V+	J.S.T B6P-VH or equivalent
4, 5, 6	GND	

Matting connector:

J.S.T housing VHR-6N,  
Crimp PIN SVH-41T-P1.1

Output connector (CN201):

Pin No.	Function	Wafer
1	+12V	MOLEX 22-27-2021 or equivalent
2	GND	

Matting connector:

MOLEX housing 22-01-2026,  
Crimp PIN 08-50-0113

NOTES:

- Dimensions shown in mm
- Tolerance 0.5 maximum
- To ensure compliance with level B emissions, connect the three "\*" marked mounting holes with metallic standoffs to the chassis.
- Ground tab is 6.35 x 0.8 mm (0.25" x 0.032") fast-on connector.
- Weight: 156 grams (0.344 lbs.) approx.