## Features

- Switching capacity up to 10A
- Small size and light weight
- Low coil power consumption
- High contact load

# Contact Data\*

Contact Arrangement		1A = SPST N.O.				
		1C = SPDT				
Contact Rating	N.O.	10A @ 120VAC, Resistive, 10K cycles, 85°C ambient				
		10A @ 277VAC, Resistive, 10K cycles, 40°C ambient				
		5A @ 240VAC, Resistive, 10K cycles, 85°C ambient				
		5A @ 277VAC, General Purpose, 100K cycles, 105°C				
		3A @ 30VDC, Resistive, 10K cycles, 85°C ambient				
		TV-5 @ 120VAC, 25K cycles, 40°C ambient				
		1/4 hp @ 120/240/277VAC, 6K cycles, 40°C ambient				
N.C.		10A @ 120VAC, Resistive, 10K cycles, 85°C ambient				
		5A @ 240VAC, Resistive, 10K cycles, 85°C ambient				
		3A @ 30VDC, Resistive, 6K cycles, 40°C ambient				
		1/4 hp @ 120/240/277VAC, 6K cycles, 40°C ambient				

Contact Resistance	< 50 milliohms initial
Contact Material	AgSnO <sub>2</sub>
Maximum Switching Power	2770VA
Maximum Switching Voltage	277VAC
Maximum Switching Current	10A

# Coil Data\*

Coil Voltage Coil VDC Resistance Ω +/- 10%		Pick Up Voltage VDC (max) 75% of rated voltage	Release Voltage VDC (min) 10% of rated voltage	Coil Power W	Operate Time ms	Release Time ms		
Rated	Max	.20W	.45W	-				
3	3.9	45	20	2.25	0.3		10	10
5	6.5	125	55	3.75	0.5	.20 or .45		
6	7.8	180	80	4.50	0.6			
9	11.7	405	180	6.75	0.9			
12	15.6	720	320	9.00	1.2			
18	22.8	1620	720	13.50	1.8			
24	31.2	2880	1280	18.00	2.4			
48	62.4	n/a	5120	36.00	4.8			











#### **General Data\***

Electrical Life @ rated load	100K cycles, average		
Mechanical Life	10M cycles, average		
Insulation Resistance	1000M Ω min. @ 500VDC, initial		
Dielectric Strength Coil to Contact	4000V rms min. @ sea level, initial		
Contact to Contact	1000V rms min. @ sea level, initial		
Shock Resistance	100m/s <sup>2</sup> for 11 ms		
Vibration Resistance	1.50mm double amplitude 10~55Hz		
Operating Temperature	-55°C to +125°C		
Storage Temperature	-55°C to +125°C		
Solderability	260°C for 5 s		
Weight	7g		

\* Values can change due to the switching frequency, desired reliability levels, environmental conditions and in-rush load levels. It is recommended to test actual load conditions for the application. It is the user's responsibility to determine the performance suitability for their specific application. The use of any coil voltage less than the rated coil voltage may compromise the operation of the relay.


#### **Ordering Information**


1. Series	J105D	1A	S	12VDC	.45
J105D					
<ul> <li>2. Contact Arrangement</li> <li>1A = SPST N.O.</li> <li>1C = SPDT **only available with .45W coil power</li> </ul>					
3. Sealing Option S = Sealed, Standard					
4. Coil Voltage 3VDC 5VDC 6VDC 9VDC 12VDC 18VDC 24VDC 48VDC **only available with .45W coil power					
5. Coil Power .20 = .20W .45 = .45W					



#### Dimensions

Units = mm





## Schematics & PC Layouts

**Bottom Views** 

