SIEMENS

Data sheet

3RA2110-0FH15-1AP0



Load feeder fuseless, Direct-on-line starting 400 V AC, Size S00 0.35...0.50 A 230 V AC Spring-type terminal for 60 mm busbar systems (also fulfills type of coordination 1) Type of coordination 2, Iq = 150 kA 1 NO (contactor)

product brand name	SIRIUS
product designation	Direct (on-line) starter
design of the product	for 60 mm busbars
product type designation	3RA21
manufacturer's article number	
 of the supplied contactor 	<u>3RT2015-2AP01</u>
 of the supplied circuit-breakers 	<u>3RV2011-0FA20</u>
 of the supplied busbar adapter 	<u>8US1251-5DT11</u>
 of the supplied link module 	<u>3RA2911-2AA00</u>
General technical data	
size of the circuit-breaker	S00
size of load feeder	S00
insulation voltage with degree of pollution 3 at AC rated value	690 V
surge voltage resistance rated value	6 kV
degree of protection NEMA rating	other
shock resistance according to IEC 60068-2-27	6g / 11 ms
mechanical service life (switching cycles) of contactor typical	30 000 000
type of assignment	2
type of protection according to ATEX directive 2014/34/EU	Ex II (2) GD
certificate of suitability according to ATEX directive 2014/34/EU	DMT 02 ATEX F 001
Substance Prohibitance (Date)	10/01/2009
Ambient conditions	
ambient temperature	
 during operation 	-20 +60 °C
 during storage 	-50 +80 °C
during transport	-50 +80 °C
temperature compensation	-20 +60 °C
relative humidity during operation	10 95 %
Main circuit	
number of poles for main current circuit	3
design of the switching contact	electromechanical
adjustable current response value current of the current-dependent overload release	0.35 0.5 A
operating voltage	
 rated value 	690 V
 at AC-3 rated value maximum 	690 V

operating frequency rated value	50 60 Hz		
operating frequency rated value operational current at AC-3 at 400 V rated value			
•	0.44 A		
operating power at AC-3	120 W		
• at 400 V rated value	120 W		
Control circuit/ Control			
type of voltage of the control supply voltage	AC		
control supply voltage at AC			
• at 50 Hz rated value	230 V		
• at 50 Hz rated value	230 230 V		
at 60 Hz rated value	230 V		
at 60 Hz rated value	230 230 V		
apparent holding power of magnet coil at AC	4.2 VA		
Auxiliary circuit			
product extension auxiliary switch	Yes		
Protective and monitoring functions			
trip class	CLASS 10		
design of the overload release	thermal (bimetallic)		
UL/CSA ratings			
full-load current (FLA) for 3-phase AC motor			
• at 480 V rated value	0.5 A		
Short-circuit protection			
product function short circuit protection	Yes		
design of the short-circuit trip	magnetic		
conditional short-circuit current (Iq)			
 at 400 V according to IEC 60947-4-1 rated value 	150 000 A		
Installation/ mounting/ dimensions			
mounting position	vertical		
fastening method	for snapping onto 60 mm busbar systems		
height	260 mm		
width	45 mm		
depth	155 mm		
required spacing			
• for grounded parts			
— forwards	20 mm		
— backwards	0 mm		
— upwards	50 mm		
— at the side	20 mm		
douvourordo			
— downwards	10 mm		
	10 mm		
 for live parts forwards 	10 mm 20 mm		
for live parts			
 for live parts forwards 	20 mm		
 for live parts forwards backwards 	20 mm 0 mm		
 for live parts forwards backwards upwards 	20 mm 0 mm 50 mm		
 for live parts forwards backwards upwards downwards 	20 mm 0 mm 50 mm 10 mm		
 for live parts forwards backwards upwards downwards at the side 	20 mm 0 mm 50 mm 10 mm		
 for live parts forwards backwards upwards downwards at the side Connections/ Terminals 	20 mm 0 mm 50 mm 10 mm 20 mm		
 for live parts forwards backwards upwards downwards at the side Connections/ Terminals type of electrical connection 	20 mm 0 mm 50 mm 10 mm		
 for live parts forwards backwards upwards downwards at the side Connections/ Terminals type of electrical connection for main current circuit for auxiliary and control circuit 	20 mm 0 mm 50 mm 10 mm 20 mm		
 for live parts forwards backwards upwards downwards at the side Connections/ Terminals type of electrical connection for main current circuit for auxiliary and control circuit Safety related data 	20 mm 0 mm 50 mm 10 mm 20 mm		
 for live parts forwards backwards upwards downwards at the side Connections/ Terminals type of electrical connection for main current circuit for auxiliary and control circuit Safety related data B10 value with high demand rate according to SN 31920 	20 mm 0 mm 50 mm 10 mm 20 mm spring-loaded terminals spring-loaded terminals		
 for live parts forwards backwards upwards downwards at the side Connections/ Terminals type of electrical connection for main current circuit for auxiliary and control circuit Safety related data B10 value with high demand rate according to SN 31920 proportion of dangerous failures 	20 mm 0 mm 50 mm 10 mm 20 mm spring-loaded terminals spring-loaded terminals		
 for live parts forwards backwards upwards downwards at the side Connections/ Terminals type of electrical connection for main current circuit for auxiliary and control circuit Safety related data B10 value with high demand rate according to SN 31920 proportion of dangerous failures with high demand rate according to SN 31920 	20 mm 0 mm 50 mm 10 mm 20 mm spring-loaded terminals spring-loaded terminals 1 000 000 73 %		
 for live parts forwards backwards upwards downwards at the side Connections/ Terminals type of electrical connection for main current circuit for auxiliary and control circuit Safety related data B10 value with high demand rate according to SN 31920 proportion of dangerous failures with high demand rate according to IEC 60529 	20 mm 0 mm 50 mm 10 mm 20 mm spring-loaded terminals spring-loaded terminals 1 000 000		
 for live parts forwards backwards upwards downwards at the side Connections/ Terminals type of electrical connection for main current circuit for auxiliary and control circuit Safety related data B10 value with high demand rate according to SN 31920 proportion of dangerous failures with high demand rate according to IEC 60529 Communication/ Protocol 	20 mm 0 mm 50 mm 10 mm 20 mm spring-loaded terminals spring-loaded terminals 1 000 000 73 %		
 for live parts forwards backwards upwards downwards at the side Connections/ Terminals type of electrical connection for main current circuit for auxiliary and control circuit Safety related data B10 value with high demand rate according to SN 31920 proportion of dangerous failures with high demand rate according to SN 31920 touch protection on the front according to IEC 60529 Communication/ Protocol protocol is supported 	20 mm 0 mm 50 mm 10 mm 20 mm spring-loaded terminals spring-loaded terminals 1 000 000 73 % finger-safe, for vertical contact from the front		
 for live parts forwards backwards upwards downwards at the side Connections/ Terminals type of electrical connection for main current circuit for auxiliary and control circuit Safety related data B10 value with high demand rate according to SN 31920 proportion of dangerous failures with high demand rate according to IEC 60529 touch protection on the front according to IEC 60529 Communication/ Protocol protocol is supported PROFINET IO protocol 	20 mm 0 mm 50 mm 10 mm 20 mm spring-loaded terminals spring-loaded terminals 1 000 000 73 % finger-safe, for vertical contact from the front No		
 for live parts forwards backwards upwards downwards at the side Connections/ Terminals type of electrical connection for main current circuit for auxiliary and control circuit Safety related data B10 value with high demand rate according to SN 31920 proportion of dangerous failures with high demand rate according to IEC 60529 Communication/ Protocol PROFINET IO protocol PROFINET IO protocol PROFISafe protocol 	20 mm 0 mm 50 mm 10 mm 20 mm spring-loaded terminals spring-loaded terminals 1 000 000 73 % finger-safe, for vertical contact from the front No No		
 for live parts forwards backwards upwards downwards at the side Connections/ Terminals type of electrical connection for main current circuit for auxiliary and control circuit Safety related data B10 value with high demand rate according to SN 31920 proportion of dangerous failures with high demand rate according to IEC 60529 touch protection on the front according to IEC 60529 Communication/ Protocol protocol is supported PROFINET IO protocol 	20 mm 0 mm 50 mm 10 mm 20 mm spring-loaded terminals spring-loaded terminals 1 000 000 73 % finger-safe, for vertical contact from the front No		

General Product Ap	proval			For use in hazard- ous locations	Declaration of Conformity	
(SP) CM	<u>Confirmation</u>		EHC	K ATEX	UK CA	
Declaration of Conformity	Test Certificates		Marine / Shipping			
CE EG-Konf.	<u>Type Test Certific-</u> ates/Test Report	Special Test Certific- ate	ABS	BUREAU VERITAS	Lloyd's Register uts	
Marine / Shipping				other	Railway	
PRS	RINA	KMRS	DNV-GL DNV-GL	<u>Confirmation</u>	Vibration and Shock	
Further information Information- and Downloadcenter (Catalogs, Brochures,) https://www.siemens.com/ic10 Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2110-0FH15-1AP0 Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2110-0FH15-1AP0 Service&Support (Manuals, Certificates, Characteristics, FAQs,) https://support.industry.siemens.com/cs/ww/en/ps/3RA2110-0FH15-1AP0 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2110-0FH15-1AP0⟨=en Characteristic: Tripping characteristics, I ² t, Let-through current https://support.industry.siemens.com/cs/ww/en/ps/3RA2110-0FH15-1AP0/char Further characteristics (e.g. electrical endurance, switching frequency) http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2110-0FH15-1AP0&objecttype=14&gridview=view1						

last modified:

2/16/2022 🖸