


MATING SIDE OF CONNECTOR



TINI QG
PANEL MOUNT

NUMBER OF CONTACTS
3, 4, 5, 6, 7 OR 8

MALE

HOUSING FINISH
BLANK = NICKEL PLATED (STANDARD)
B = BLACK CHROME

CONTACT FINISH
BLANK = SILVER PLATED (STANDARD)
AU = GOLD PLATED

NOTES:

1. MATERIALS:
HOUSING - COPPER ALLOY, NICKEL OR BLACK CHROME PLATED
CONTACT PINS - COPPER ALLOY, SILVER OR GOLD PLATED
INSULATOR - THERMOPLASTIC, DARK BROWN
HEX NUT & WASHER - COPPER ALLOY, NICKEL PLATED
2. 0.250 MAXIMUM PANEL THICKNESS.
3. SOLDER TERMINALS MAY BE SOLDERED TO PC BOARD.
4. WASHER & HEX NUT SHIPPED UNASSEMBLED.
5. THIS PRODUCT IS RoHS COMPLIANT.


REV	ECO NUMBER	DATE	BY	APVD
S	REDRAWN 26984	07-11-12	JEB	TJK
REVISIONS				

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES
- TWO PLACE DECIMALS ±0.02
- THREE PLACE DECIMALS ±0.005

DO NOT SCALE DRAWING

RECOMMENDED PC LAYOUTS
COMPONENT SIDE
SEE NOTE 4



CUSTOMER DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.

SIZE	WIDTH	MULT	LBS/M	TEMPER
FINISH SPEC No.			MATERIAL SPEC No.	
FIRST USED ON		SCALE 2:1		
DATE DRAWN	BY	CHKD CD	APVD PN	
06-04-79	JZG	09-10-79	05-22-80	
NAME TINI Q-G MALE PANEL MOUNT RECEPTACLE, RoHS			PART No.	REV
			TB_M SERIES	S