

- Compact metal package
- Wide 2:1 input voltage ranges 16.5–36, 33–75 VDC
- Very high efficiency up to 93%
- No minimum load
- Soft start
- Adjustable output voltage +10/-20%
- Sense line
- Remote On/Off input
- Reverse input voltage protection
- Over temperature protection
- 3-year product warranty



The TEP 160 Series is a family of isolated high performance DC/DC converter modules with wide 2:1 input voltage ranges which come in a rugged, sealed industry standard half brick package.

A very high efficiency allows full power operation without forced air cooling at 25°C This temperature can be increased to 40°C with optional mounted heatsink or up to 60°C when mounted on an iron base plate. The very wide input voltage range and reverse input voltage protection make these converters interesting solution for battery operated systems. Typical applications are in telecom/datacom, industry control and railway systems for on board power distribution. These series is available in many optional designs on demand --> see options.

Models				
Order Code	Input Voltage Range	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TEP 160-2412	16.5 - 36 VDC (24 VDC nom.)	12 VDC (9.6 - 13.2 VDC)	13'000 mA	92 %
TEP 160-2413		15 VDC (12.0 - 16.5 VDC)	10'000 mA	92 %
TEP 160-2415		24 VDC (19.2 - 26.4 VDC)	6'500 mA	93 %
TEP 160-2416		28 VDC (22.4 - 30.8 VDC)	5'500 mA	93 %
TEP 160-2418		48 VDC (38.4 - 52.8 VDC)	3'300 mA	92 %
TEP 160-4812	33 - 75 VDC (48 VDC nom.)	12 VDC (9.6 - 13.2 VDC)	16'000 mA	92 %
TEP 160-4813		15 VDC (12.0 - 16.5 VDC)	13'000 mA	93 %
TEP 160-4815		24 VDC (19.2 - 26.4 VDC)	8'000 mA	92 %
TEP 160-4816		28 VDC (22.4 - 30.8 VDC)	7'000 mA	92 %
TEP 160-4818		48 VDC (38.4 - 52.8 VDC)	4'000 mA	92 %
TEP 160-48153		53 VDC (42.4 - 58.3 VDC)	3'700 mA	92 %

Options	
Suffix -CM	- Chassis mount models w/o filter: www.tracopower.com/products/tep160cm.pdf
Suffix -CMF	- Chassis mount models w/ filter to meet EN 55032 class A: www.tracopower.com/products/tep160cmf.pdf
TEP-HS1	- Optional Heat Sink: www.tracopower.com/products/tep-hs1.pdf
on demand (backorder with MOQ non stocking item)	- Optional model with 3.3 VDC / 40'000 mA Output and 16.5 - 36 VDC Input - Optional model with 5 VDC / 30'000 mA Output and 16.5 - 36 VDC Input - Optional model with 3.3 VDC / 45'000 mA Output and 33 - 75 VDC Input - Optional model with 5 VDC / 34'000 mA Output and 33 - 75 VDC Input - Optional models with Sync pin to synchronize switching frequency of up to 3 units (EMC reason)

Input Specifications		
Input Current	- At no load	24 Vin models: 35 mA typ. 48 Vin models: 25 mA typ.
Surge Voltage		24 Vin models: 50 VDC max. (1 s max.) 48 Vin models: 100 VDC max. (1 s max.)
Under Voltage Lockout		24 Vin models: 15.5 VDC min. / 16 VDC typ. / 16.3 VDC max. 48 Vin models: 31.6 VDC min. / 32 VDC typ. / 32.5 VDC max.
Recommended Input Fuse		24 Vin models: 15'000 mA (fast acting) 48 Vin models: 10'000 mA (fast acting) (The need of an external fuse has to be assessed in the final application.)
Input Filter		Internal Pi-Type

Output Specifications		
Output Voltage Adjustment		-20% to +10% (By external trim resistor) See application note: www.tracopower.com/overview/tep160 Output power must not exceed rated power!
Voltage Set Accuracy		±1% max.
Regulation	- Input Variation (Vmin - Vmax) - Load Variation (0 - 100%)	0.1% max. 0.1% max.
Ripple and Noise (20 MHz Bandwidth)		3.3 Vout models: 75 mVp-p max. (w/ 1 µF X7R 22 µF poscap) 5 Vout models: 75 mVp-p max. (w/ 1 µF X7R 22 µF poscap) 12 Vout models: 100 mVp-p max. (w/ 1 µF X7R 22 µF poscap) 15 Vout models: 100 mVp-p max. (w/ 1 µF X7R 22 µF poscap) 24 Vout models: 200 mVp-p max. (w/ 4.7 µF X7R) 28 Vout models: 200 mVp-p max. (w/ 4.7 µF X7R) 48 Vout models: 300 mVp-p max. (w/ 2.2 µF X7R) 53 Vout models: 300 mVp-p max. (w/ 2.2 µF X7R)
Capacitive Load	- 24 Vin input	53 Vout models: 690 µF max. 3.3 Vout models: 121'000 µF max. 5 Vout models: 60'000 µF max. 12 Vout models: 10'800 µF max. 15 Vout models: 6'600 µF max. 24 Vout models: 2'700 µF max. 28 Vout models: 1'900 µF max. 48 Vout models: 680 µF max.
	- 48 Vin input	3.3 Vout models: 136'000 µF max. 5 Vout models: 68'000 µF max. 12 Vout models: 13'300 µF max. 15 Vout models: 8'600 µF max. 24 Vout models: 3'300 µF max. 28 Vout models: 2'500 µF max. 48 Vout models: 830 µF max.
Minimum Load		Not required

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Temperature Coefficient	±0.02 %/K max.
Start-up Time	75 ms typ.
Short Circuit Protection	Continuous, Automatic recovery
Output Current Limitation	120 - 150% of I _{out} max.
Overvoltage Protection	115 - 130% of V _{out} nom.
Transient Response	- Response Time 200 µs typ. / 250 µs max. (25% Load Step)

Safety Specifications

Standards	- IT / Multimedia Equipment	EN 60950-1 EN 62368-1 IEC 60950-1 IEC 62368-1 UL 60950-1 UL 62368-1
	- Certification Documents	www.tracopower.com/overview/tep160
Pollution Degree		PD 2
Over Voltage Category		OVC II

EMC Specifications

EMI Emissions	- Conducted Emissions	EN 55032 class A (with external filter) EN 55032 class B (with external filter)
	- Radiated Emissions	EN 55032 class A (with external filter) EN 55032 class B (with external filter)
		External filter proposal: www.tracopower.com/overview/tep160
EMS Immunity		EN 55024 (IT Equipment) EN 55035 (Multimedia)
	- Electrostatic Discharge	Air: EN 61000-4-2, ±8 kV, perf. criteria A Contact: EN 61000-4-2, ±6 kV, perf. criteria A
	- RF Electromagnetic Field	EN 61000-4-3, 20 V/m, perf. criteria A
	- EFT (Burst) / Surge	EN 61000-4-4, ±2 kV, perf. criteria A EN 61000-4-5, ±2 kV, perf. criteria A
	- Conducted RF Disturbances	Ext. input component: 2x KY 200 µF EN 61000-4-6, 10 V _{rms} , perf. criteria A
	- PF Magnetic Field	Continuous: EN 61000-4-8, 100 A/m, perf. criteria A 1 s: EN 61000-4-8, 1000 A/m, perf. criteria A

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature - Case Temperature - Storage Temperature	-40°C to +75°C +115°C max. -55°C to +125°C
Power Derating	- High Temperature	Depending on model See application note: www.tracopower.com/overview/tep160
Over Temperature Protection Switch Off	- Protection Mode - Measurement Point	120°C typ. (Automatic recovery at 105°C typ.) Case
Cooling System		Natural convection (20 LFM)
Sense Function		10% max. of V _{out} nom. (if sense function is not used, sense pins must be connected to corresponding polarity output pins.)
Remote Control	- Voltage Controlled Remote (passive = on) - Off Idle Input Current - Remote Pin Input Current	On: 3.0 to 12 VDC or open circuit Off: 0 to 1.2 VDC or short circuit Refers to 'Remote' and '-Vin' Pin 3 mA typ. -0.5 to 1.0 mA
Altitude During Operation		5'000 m max. (for basic insulation) 2'000 m max. (for reinforced insulation)

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Regulator Topology	Forward Converter
Switching Frequency	225 - 275 kHz (PWM) 250 kHz typ. (PWM)
Insulation System	Reinforced Insulation
Working Voltage (rated)	145 VAC (3.3 and 5 Vout models) 185 VAC (4.8 and 5.3 Vout models) 172 VAC (other output models)
Isolation Test Voltage	- Input to Output, 60 s - Input to Case, 60 s - Output to Case, 60 s
	3'000 VAC 1'600 VAC 1'600 VAC
Isolation Resistance	- Input to Output, 500 VDC
Isolation Capacitance	- Input to Output, 100 kHz, 1 V
Reliability	- Calculated MTBF
Washing Process	380'000 h (MIL-HDBK-217F, ground benign)
Environment	- Vibration - Thermal Shock
	According to Cleaning Guideline www.tracopower.com/info/cleaning.pdf
Housing Material	MIL-STD-810F MIL-STD-810F
Base Material	Metal
Potting Material	Non-conductive FR4 (UL 94 V-0 rated)
Pin Material	Silicone (UL 94 V-0 rated)
Pin Foundation Plating	Copper
Pin Surface Plating	Nickel (2 - 3 µm)
Housing Type	Tin (3 - 5 µm), matte
Mounting Type	Metal Case
Connection Type	PCB Mount
Footprint Type	THD (Through-Hole Device)
Soldering Profile	Half-Brick
Weight	Lead-Free Wave Soldering 260°C / 6 s max.
Thermal Impedance	105 g
Environmental Compliance	- Case to Ambient
	6.1 K/W typ. 4.6 K/W typ. (with Heat Sink)
	- REACH Declaration
	www.tracopower.com/info/reach-declaration.pdf REACH SVHC list compliant REACH Annex XVII compliant
	- RoHS Declaration
	www.tracopower.com/info/rohs-declaration.pdf Exemptions: 7a, 7c-I (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule))
	- SCIP Reference Number
	931b6944-928b-4cea-8bfa-21644d000430


Supporting Documents

Overview Link (for additional Documents)

www.tracopower.com/overview/tep160

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Outline Dimensions



Pinout		
Pin	Single	Pin Diameter
1	-Vin (GND)	1.0 mm (0.04 inch)
2	Case	1.0 mm (0.04 inch)
3	Remote On/Off	1.0 mm (0.04 inch)
4	+Vin (Vcc)	1.0 mm (0.04 inch)
5	-Vout	2.0 mm (0.08 inch)
6	-Sense	1.0 mm (0.04 inch)
7	Trim	1.0 mm (0.04 inch)
8	+Sense	1.0 mm (0.04 inch)
9	+Vout	2.0 mm (0.08 inch)
10	Sync (on demand)	1.0 mm (0.04 inch)