



# **Barracuda VFH69383B23JW**

**6-Port Vehicular MIMO Antenna** 698-960/1690-3800 MHz and 2400-2500/4900-6000 MHz

The Barracuda VFH69383B23JW multiport/multiband antenna provides an excellent solution for Public Safety, Transportation and Aftermarket Fleet applications. Configured for 2-port MIMO operation over the 3G/4G/ISM/CBRS bands and 3-port MIMO operation over the low//high frequency Wi-Fi bands. An additional 6th port provides an active antenna for enabling GNSS global navigation services.

#### **FEATURES AND BENEFITS**

- One single-hole mount/fixing- reduces vehicle damage Attractive IP67 low profile aerodynamic housing and the cost of installation

  - Multiband/MIMO operation with GNSS navigation

#### **APPLICATIONS**

- FirstNet/Public Safety
- Transportation
- Aftermarket fleet

- 5G ready
- Rugged LTE Gateways
- Others

ELECTRICAL SPECIFICATION	NS						
Antenna Model		VFH69383B23JW-518J					
Number of Ports		6					
Port Configuration		2x- 3G/4G/ISM/CBRS 3x- Wi-Fi					
Operating Frequency (MHz)	698-806	824-894	880-960	1690-3800	2400-2500	4900-6000	
Peak Gain - Avg (dBi)	1.0	-0.1	0.2	3.6	2.7	5.1	
Peak Gain* - Max (dBi)	2.5	2.5	2.5	7.4	4.0	6.4	
VSWR - Avg	<1.5:1	<1.5:1	<1.5:1	<1.3:1	<1.3:1	<1.2:1	
VSWR - Max		<2.5:1			<2.0:1		
Isolation LTE1 to LTE2 (dB)	-17	-17	-17	-22	-30	-42	
Isolation LTE1 to WIFI 1 (dB)	-36	-36	-38	-21	-21	-42	
Isolation LTE1 to WIFI 2 (dB)	-40	-44	-45	-22	-22	-42	
Isolation LTE1 to WIFI 3 (dB)	-19	-21	-24	-30	-36	-47	
Isolation LTE2 to WFI 1 (dB)	-37	-42	-43	-21	-21	-42	
Isolation LTE2 to WIFI 2 (dB)	-35	-35	-37	-21	-21	-41	
Isolation LTE2 to WIFI 3 (dB)	-16	-18	-19	-26	-36	-47	

ELECTRICAL SPECIFICATIONS	S					
Isolation WIFI 1 to WIFI 2 (dB)	-58	-59	-58	-37	-38	-46
Isolation WIFI 1 to WIFI 3 (dB)	-41	-44	-47	-38	-38	-46
Isolation WIFI 2 to WIFI 3 (dB)	-40	-42	-42	-35	-36	-45
Isolation GNSS to LTE 1 (dB)	-41	-50	-51	-41	-52	-52
Isolation GNSS to LTE 2 (dB)	-42	-42	-41	-49	-53	-54
Isolation GNSS to WIFI 1 (dB)	-69	-71	-66	-52	-54	-49
Isolation GNSS to WIFI 2 (dB)	-67	-69	-69	-51	-52	-54
Isolation GNSS to WIFI 3 (dB)	-40	-45	-44	-48	-56	-61
Azimuth Plane 3 dB Beamwidth	360°, Omnidirectional					
Nominal Impedance (Ohms)	50					
Polarization	Linear Vertical					
Max Power - Ambient 25°C (W)	10					

MECHANICAL SPECIFICATIONS				
Dimensions - L x W x H - mm (inches)	179 x 63 x 48 (7.04 x 2.48 x 1.69)			
Weight - kg (lbs.)	0.72 (1.6)			
Cable Type	LMR 100, Black			
Mounting	P-Mount			
Radome Material	PC, UL94-V0			
Baseplate Material	Aluminum			

ENVIRONMENTAL SPECIFICATIONS	
Operating Environment	Outdoor Vehicle
Operating Temperature - °C (°F)	-30 to +70°C (-22 to +158°F)
Storage Temperature - °C (°F)	-40 to +85°C (-40 to +185°F)
Ingress Protection Rating	IP67
Material Substance Compliance	RoHS

GNSS ANTENNA SPECIFICATIONS					
Frequency of Operation (MHz)	1559 - 1606				
Band	BEIDOU	GPS	GLONASS		
Frequency Band (MHz)	1559.052 - 1563.144	1574.42 - 1576.42	1598.0625 - 1605.89		
Absolute Gain (dBi)	3	3	3		
LNA Gain, Typ. @ room temp. (dBi)	26	27	26		
Noise Figure @ room temp., Max (dB)	3.0	2.5	2.8		
Max VSWR @ room temp.	2:1	2:1	2:1		
Polarization	RHCP				
Nominal Impedance (Ohms)	50				
DC Voltage (Vdc)	3.3				


GNSS ANTENNA SPECIFICATIONS					
Operating Supply Voltage (Vdc)	2.5 - 7.0				
Current Consumption, Max @ room temp mA)	20				
Out-of-band Signal Rejection Min @ room temp (dBc)	60 (@1-1525 MHz) 60 (@1675-2000 MHz) 50 (@20		50 (@2000-3000 MHz)		
Input Max Power (dBm)	-30				
Cable Type	RG174				


# **CONFIGURATION**


PART NUMBER	CABLE LENGTH	CONNECTOR - LTE PORTS	CONNECTOR - WI-FI PORTS	CONNECTOR - GNSS PORT
VFH69383B23JW-518J	5.18 m (17.0 ft.)	SMA- male	SMA- male	SMA- male

# **PACKAGING INFORMATION**

PACKAGED DIMENSIONS	CARTON	MASTER CARTON	AIR PALLET	OCEAN PALLET
Number of Antennas	1	8	192	240
Height - mm (in.)	135 (5.31)	295 (11.6)	1350 (53.15)	1650 (64.96)
Length - mm (in.)	245 (9.65)	520 (20.5)	1200 (47.24)	1200 (47.24)
Width - mm (in.)	120 (47.2)	260 (10.2)	800 (31.5)	800 (31.5)
Shipping Weight - kg (lb.)	0.85 (1.9)	7.5 (16)	198 (436)	245 (540)









The Barracuda antenna can create an IP67 water-tight seal when installed on vehicles. Certain vehicles such as a Ford Explorer Interceptor have more narrow roof ridges that are tightly spaced together. For this type, vehicle special adapters are available.


See parts BKIT-VFX69383-001 (between ridges installation) and BKIT-VFX69383-003 (atop ridge installation) for product details.


#### **RADIATION PATTERNS - LTE ANTENNAS**




## 960 MHz











## 1690 MHz


















## 2170 MHz











## 2700 MHz

















## **RADIATION PATTERNS - WI-FI ANTENNAS**


## 2400 MHz











## 2500 MHz

















#### 5900 MHz







#### TE TECHNICAL SUPPORT CENTER

USA: +1 (800) 522-6752 +1 (905) 475-6222 Canada: Mexico: +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 Germany: +49 (0) 6251-133-1999 +44 (0) 800-267666 UK: France: +33 (0) 1-3420-8686 Netherlands: +31(0)73-6246-999 China: +86 (0) 400-820-6015

#### te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE product is installed. Useful lifetime of the original end product may vary but is not to exceed five (5) years from the original date of the end product purchase.

©2021 TE Connectivity. All Rights Reserved.

11/21 Original

