

### ● General Description

The AGM215MNE combines advanced trench MOSFET technology with a low resistance package to provide extremely low  $R_{DS(ON)}$ . This device is ideal for load switch and battery protection applications.

### ● Features

- Advance high cell density Trench technology
- Low  $R_{DS(ON)}$  to minimize conductive loss
- Low Gate Charge for fast switching
- Low Thermal resistance
- 100% Avalanche tested
- 100% DVDS tested
- with ESD


### ● Application

- MB/VGA Vcore
- SMPS 2<sup>nd</sup> Synchronous Rectifier
- POL application
- BLDC Motor driver

### Product Summary

BVDSS	RDSON	ID
19.5V	11mΩ	7.0A

### SOT23-6L Pin Configuration



### Package Marking and Ordering Information

Device Marking	Device	Device Package	Reel Size	Tape width	Quantity
AGM215MNE	AGM215MNE	SOT23-6L	178mm	8mm	3000

**Table 1. Absolute Maximum Ratings ( $T_A=25^\circ\text{C}$ )**

Symbol	Parameter	Value	Unit
$V_{DS}$	Drain-Source Voltage ( $V_{GS}=0V$ )	19.5	V
$V_{GS}$	Gate-Source Voltage ( $V_{DS}=0V$ )	$\pm 10$	V
$I_D$	Drain Current-Continuous( $T_A=25^\circ\text{C}$ ) (Note 1)	7	A
	Drain Current-Continuous( $T_A=100^\circ\text{C}$ )	4.3	A
IDM (pluse)	Drain Current-Pulsed (Note 2)	28	A
$P_D$	Total Power Dissipation( $T_A=25^\circ\text{C}$ )	1.2	W
	Total Power Dissipation( $T_A=100^\circ\text{C}$ )	0.48	W
EAS	Avalanche energy (Note 3)	25	mJ
$T_J, T_{STG}$	Operating Junction and Storage Temperature Range	-55 To 150	$^\circ\text{C}$

**Table 2. Thermal Characteristic**

Symbol	Parameter	Typ	Max	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient (Steady State) <sup>1</sup>	---	105	$^\circ\text{C/W}$

**Table 3. N- Channel Electrical Characteristics (T<sub>J</sub>=25°C unless otherwise noted)**




Symbol	Parameter	Conditions	Min	Typ	Max	Unit
<b>On/Off States</b>						
BVDSS	Drain-Source Breakdown Voltage	VGS=0V ID=250μA	19.5	--	--	V
IDSS	Zero Gate Voltage Drain Current	VDS=18V,VGS=0V	--	--	1	μA
IGSS	Gate-Body Leakage Current	VGS=±10V,VDS=0V	--	--	±10	uA
VGS(th)	Gate Threshold Voltage	VDS=VGS,ID=250μA	0.5	0.7	1.0	V
gFS	Forward Transconductance	VDS=5V,ID=4A	--	13.6	--	S
RDS(on)	Drain-Source On-State Resistance	VGS=4.5V, ID=5A	--	11	15	mΩ
		VGS=2.5V, ID=4A	--	14	19	mΩ
<b>Dynamic Characteristics</b>						
Ciss	Input Capacitance	VDS=10V,VGS=0V, F=1MHZ	--	854	--	pF
Coss	Output Capacitance		--	150	--	pF
Crss	Reverse Transfer Capacitance		--	90	--	pF
Rg	Gate resistance	VGS=0V, VDS=0V,f=1.0MHz	--	--	--	Ω
<b>Switching Times</b>						
td(on)	Turn-on Delay Time	VGS=4.5V,VDS=10V RL=2Ω,RGEN=6Ω	--	11	--	nS
tr	Turn-on Rise Time		--	34	--	nS
td(off)	Turn-Off Delay Time		--	55	--	nS
tf	Turn-Off Fall Time		--	51	--	nS
Qg	Total Gate Charge	VGS=4.5V, VDS=10V, ID=5A	--	9.1	--	nC
Qgs	Gate-Source Charge		--	1.6	--	nC
Qgd	Gate-Drain Charge		--	2.0	--	nC
<b>Source-Drain Diode Characteristics</b>						
ISD	Source-Drain Current(Body Diode)		--	--	7.0	A
VSD	Forward on Voltage	VGS=0V,IS=5A	--	--	1.2	V
trr	Reverse Recovery Time	IF=5A , dl/dt=100A/μs ,	--	--	--	ns
Qrr	Reverse Recovery Charge	TJ=25°C	--	--	--	nc

Notes 1.The maximum current rating is package limited.


Notes 2.Repetitive Rating: Pulse width limited by maximum junction temperature


Notes 3.EAS condition: T<sub>J</sub>=25°C

### Typical Electrical And Thermal Characteristics (Curves)



### Typical Electrical And Thermal Characteristics (Curves)



**Package Mechanical Data-SOT23-6L**


Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
$\theta$	0°	8°	0°	8°


Disclaimer:

The information provided in this document is believed to be accurate and reliable. however, Shenzhen Core Control Electronics Technology Co., Ltd. does not assume any responsibility for the following consequences. Do not consider the use of such information or use beyond its scope.

The information mentioned in this document may be changed at any time without notice.

The products and information provided in this document do not infringe patents. Shenzhen Core Control Electronics Technology Co., Ltd. assumes no responsibility for any infringement of any other rights of third parties. The result of using such products and information.

This document is the first version issued on Sep. 10th, 2023. This document replaces all previously provided information.

 It is a registered trademark of Shenzhen Core Control Electronics Technology Co., Ltd.

Copyright © 2017 Shenzhen Core Control Electronics Technology Co., Ltd. all rights reserved.