SIEMENS

Data sheet

US2:84JUH950MF



Duplex starter w/o alternator, Size 4, Three phase full voltage, Solid-state overload relay, OLR amp range 50-200A, 110V 50Hz / 120V 60Hz coil, Combination type, Two 150A circuit breakers, Enclosure NEMA type 12, Dust/drip proof for indoors

Fi	aur	es	imi	lar
	90.	0.5		I CAI

product brand name	Class 84
design of the product	Duplex controller with two MCPs without alternator
special product feature	ESP200 overload relay
General technical data	
weight [lb]	106 lb
Height x Width x Depth [in]	56 × 29 × 10 in
touch protection against electrical shock	NA for enclosed products
installation altitude [ft] at height above sea level maximum	6560 ft
ambient temperature [°F]	
 during storage 	-22 +149 °F
 during operation 	-4 +104 °F
ambient temperature	
 during storage 	-30 +65 °C
during operation	-20 +40 °C
country of origin	USA
Horsepower ratings	
yielded mechanical performance [hp] for 3-phase AC motor	
 at 200/208 V rated value 	40 hp
 at 220/230 V rated value 	50 hp
 at 460/480 V rated value 	100 hp
 at 575/600 V rated value 	100 hp
Contactor	
size of contactor	NEMA controller size 4
number of NO contacts for main contacts	3
operating voltage for main current circuit at AC at 60 Hz maximum	600 V
operational current at AC at 600 V rated value	135 A
mechanical service life (switching cycles) of the main contacts typical	500000
Auxiliary contact	
number of NC contacts at contactor for auxiliary contacts	0
number of NO contacts at contactor for auxiliary contacts	1
number of total auxiliary contacts maximum	7
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)
Coil	
type of voltage of the control supply voltage	AC
control supply voltage	

 at DC rated value 	0 0 V	
 at AC at 50 Hz rated value 	110 110 V	
at AC at 60 Hz rated value	120 120 V	
holding power at AC minimum	22 W	
apparent pick-up power of magnet coil at AC	510 VA	
apparent holding power of magnet coil at AC	51 VA	
operating range factor control supply voltage rated value of magnet coil	0.85 1.1	
percental drop-out voltage of magnet coil related to the input voltage	50 %	
ON-delay time	18 34 ms	
OFF-delay time	10 12 ms	
Overload relay		
product function		
 overload protection 	Yes	
 phase failure detection 	Yes	
 asymmetry detection 	Yes	
 ground fault detection 	Yes	
test function	Yes	
external reset	Yes	
reset function	Manual, automatic and remote	
trip class	CLASS 5 / 10 / 20 (factory set) / 30	
adjustable current response value current of the current- dependent overload release	50 200 A	
tripping time at phase-loss maximum	3 s	
relative repeat accuracy	1 %	
product feature protective coating on printed-circuit board	Yes	
number of NC contacts of auxiliary contacts of overload relay	1	
number of NO contacts of auxiliary contacts of overload relay	1	
operational current of auxiliary contacts of overload relay		
• at AC at 600 V	5 A	
• at DC at 250 V	1 A	
contact rating of auxiliary contacts of overload relay according to UL	5A@600VAC (B600), 1A@250VDC (R300)	
insulation voltage (Ui)		
 with single-phase operation at AC rated value 	600 V	
 with multi-phase operation at AC rated value 	300 V	
Enclosure		
degree of protection NEMA rating of the enclosure	NEMA Type 12	
design of the housing	dustproof and drip-proof for indoor use	
Circuit Breaker		
type of the motor protection	Motor circuit protector (magnetic trip only)	
operational current of motor circuit breaker rated value	150 A	
adjustable current response value current of instantaneous short-circuit trip unit	800 1500 A	
Mounting/wiring		
mounting position	Vertical	
fastening method	Surface mounting and installation	
type of electrical connection for supply voltage line-side	Box lug	
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	1x (6 AWG 350 Kcmil) or 1x (4 AWG 350 Kcmil)	
temperature of the conductor for supply maximum permissible	75 °C	
material of the conductor for supply	AL or CU	
type of electrical connection for load-side outgoing feeder	Box lug	
tightening torque [lbf·in] for load-side outgoing feeder	200 200 lbf·in	
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded	1x (6 AWG 250 MCM)	
temperature of the conductor for load-side outgoing feeder	75 °C	
,		

maximum permissible				
material of the conductor for load-side outgoing feeder	CU			
type of electrical connection of magnet coil	Screw-type terminals			
tightening torque [lbf·in] at magnet coil	5 12 lbf·in			
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (16 12 AWG)			
temperature of the conductor at magnet coil maximum permissible	75 °C			
material of the conductor at magnet coil	CU			
type of electrical connection at contactor for auxiliary contacts	Screw-type terminals			
tightening torque [lbf-in] at contactor for auxiliary contacts	10 15 lbf·in			
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)			
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C			
material of the conductor at contactor for auxiliary contacts	CU			
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals			
tightening torque [lbf-in] at overload relay for auxiliary contacts	7 10 lbf·in			
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 14 AWG)			
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C			
material of the conductor at overload relay for auxiliary contacts	CU			
Short-circuit current rating				
design of the short-circuit trip	Instantaneous trip circuit breaker			
breaking capacity maximum short-circuit current (Icu)				
• at 240 V	100 kA			
• at 480 V	100 kA			
• at 600 V	25 kA			
certificate of suitability	NEMA ICS 2; UL 508; CSA 22.2, No.14			
Further information				
Industrial Controls - Product Overview (Catalogs, Brochures,) www.usa.siemens.com/iccatalog Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:84JUH950MF				

Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/US/en/ps/US2:84JUH950MF

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:84JUH950MF&lang=en

Certificates/approvals

https://support.industry.siemens.com/cs/US/en/ps/US2:84JUH950MF/certificate

last modified:

1/25/2022 🖸