
Red Line Laser Module with TTL Function Fan Angle 60° Uniform Line

VLM-635-57-60°Series



The newly developed glass line lens come with various fan angles and they produce high quality uniform laser line in a robust stainless housing, ideal for automation, machine vision, image processing, digital data acquisition, counting, precision 3D scanner and science & medical application. They are all come with TTL function to allow up to 10K Hz modulation frequency. They are available at 10 cm, 20 cm, 40 cm and 90 cm focus length, red & green wavelength, Class 1M and Class 2M laser class to cover within 1 meter range task. For customized focus length, wavelength and laser power output, please contact us.

FEATURES:

- Built with high precision glass line lens and glass laser collimating lens.
- Fan Angle: 60°
- Focus range: 10cm, 20cm, 40cm, 90cm, customized focus length are available by request.
- CW to 10K HZ stable power output for demanding power and speed are of important.
- Customized focus within 1 meter available please direct contact us.
- Two laser power output level: LPO Class 1M laser product

LPT - Class 2M laser product


- Dimensions: Ø10 x 40 mm (Ø0.39" x 1.575")
- Wavelength: 630~645 nm
- 3~6 VDC operation.
- Connection type : Lead wire
- Laser line demonstration: https://www.youtube.com/watch?v=3_gRtxyeP28

APPLICATIONS: ideal for

- Machine vision.
- Automation industry.
- Image processing.
- Medical & Science.
- Scanning.
- Precision 3D scanner.
- Counting.
- Measurement.

VLM-635-57-60°Series

OUTLINE DIMENSIONS (UNITS: mm)



SPECIFICATIONS

	Part Number	VLM-635-57 LPO-D60-				VLM	-635-5	7 LPT-	D60-
	Fait Number	F10	F20	F40	F90	F10	F20	F40	F90
1	Focus length	10 cm	20 cm	40 cm	90 cm	10 cm	20 cm	40 cm	90 cm
2	Fan angle / Laser line length		60°/L	ength.	of Lase	er Line	as TA l	BLE A	
3	Laser line width				AS TA	BLE B	ı		
4	Recommended working range				AS TA	BLE B	ı		
5	TTL modulation frequency			Hig	gh ON,	0-10K	Hz		
6	Dimensions		Ø′	10 x 40	mm (Ø	ð0.39"	x 1.57	5")	
7	Weight				17:	±1g			
8	Operating voltage (Vop)				3~6	VDC			
9	Operating current (lop)	L	ess tha	ın 50m	Α	Le	ess tha	n 100m	nΑ
10	Optical power*	L	ess tha	an 5mV	٧	Le	ess tha	ın 10m'	W
11	Laser power output**	Le	ss thar	0.39m	ηW	L	ess tha	an 1mV	٧
12	Laser class		Clas	s 1M			Clas	s 2M	
13	Wavelength (λp)				630~6	345nm			
14	Collimating lens / Line generating lens			Asp	herical	glass	lens		
15	Output aperture				8n	nm			
16	Beam shape				Liı	ne			
17	Laser line accuracy			4	0"(±1m	m@5N	1)		
18	Operating temp. range***				-20°C -	-+60°C			
19	Storage temp. range				-20°C -	~+85°C)		
20	Housing material / color	Stainless steel / Silver							

VLM-635-57-60°Series

21	Potential of housing	Insulated
22	Electrostatic discharge (ESD)	30KV
23	Moisture sensitivity level (MSL)	Level 1 - acc to JEDEC J-STD-020E.
24	Wire type	2464 3-WIRE CABLE 26 AWG
25	Cable length	330±30mm
26	Mean time to failure (MTTF) 25°C	Above 10000 hrs
27	International Protection Marking	IP67
20	Application	Precision fine line for Automation, Machine vision and
20	Application	Medical with modulation function
29	Suggestion work distance	0~1.2 meters / 0~4 feet

^{*} Optical power is total power output measured at the aperture of the laser.

SAFETY LABEL


LPO:

LPT:

CAUTION
LASER RADIATION
DO NOT STARE
INTO BEAM
LASER DIODE
Wavelength: 630-680nm
CLASS II LASER PRODUCT
Manufacturer: QUARTON Inc
9F, 19S, Sec.1, Ta-Tung Rd,
Halchib District, New Taple City,
Ta I w a n , R . O . C .

TABLE A: Laser Line Length Table:

CLASS I LASER PRODUCT



Length of laser line:

Distance	10 cm	20 cm	40 cm	100 cm	
Fan angle	(4 inch)	(8 inch)	(16 inch)	(40 inch)	
5°	0.9 cm	1.75 cm	3.5 cm	7.85 cm	
	(0.35")	(0.7")	(1.4")	(3")	
10°	1.75cm	3.5 cm	7 cm	17.5 cm	
	(0.6")	(1.4")	(2.8")	(6")	
15°	2.6 cm	5.2 cm	10.5 cm	26.3 cm	
	(1")	(2")	(4")	(10")	
20°	3.5 cm	7 cm	14 cm	35 cm	
	(1.4")	(2.8")	(5.6")	(14")	
30°	5.3 cm	10.7 cm	21 cm	53.5 cm	
	(2")	(4")	(8")	(20")	
45°	8.28 cm	16.6 cm	33.1 cm	82.85 cm	
	(3¼")	(6½")	(13")	(32½")	
60°	11.5 cm	23 cm	46 cm	115.5 cm	
	(4½")	(9")	(18")	(45")	
110°	28.6 cm	57.1 cm	114.2 cm	285.6 cm	
	(11¼")	(23")	(46")	(112½")	

^{**} According to FDA 1040.10 & IEC 60825-1 regulations, laser power output is measured by 7mm aperture stop from a 10 cm distance of the laser.

^{***} Operation temperature means within this temperature range, the laser spot/line will not be affected to change the spot size/line width. It can still work over this range, but the laser spot size or laser line width will be larger.

VLM-635-57-60°Series



TABLE B: Recommended working range:

Focus at 10 cm:

Working range: 0 - 20cm(0-7.9")

Laser Line Width <2mm Recommended Working Range(cm) Laser Fan Angle 10 15

Best at: 7 - 14.5cm(2.8"-5.7") Laser Line Width <1mm

•		ī				
5°			6.5 -	16	-21	
10°			8 -	15	-19	
15°		I	6- 8 -	15	-19	
20°		4-	7 -	16	-21.5	
30°		4-	6 - 14	.5	-21	
45°	0-		5.5 -	15	-19	
60°	0-		7 - 1	.4.5	-20	
110°	0-		7 -	16.5	-22.5	

Focus at 40 cm:

Working range: 3 - 72cm(1.2"-28.3")

Laser Line Width <2mm Laser Recommended Working Range(cm) Fan Angle 45 60 30 5° 11- 20.5 - 57 10° 11.5- 22 - 47.5 -61.5 15° 7- 21 - 53 -64 20° 21 - 54 -68 30° 45° 60° 110°

Best at: 20 - 58cm(7.9"-22.8") Laser Line Width <1mm

Focus at 20 cm:

Working range: 11 - 32cm(4.3"-12.6")

Best at: 15 - 23.5cm(5.9"-9.3") Laser Line Width <1mm Laser Line Width <2mm

Laser	Recom	mende	ed Worki	ng Ran	ge(cm)
Fan Angle	10	15	20	25	30
5°		12.5- 1	5 - 23	-26	
10°	10-	14	- 22	-26	
15°	10-	14.	5 - 22	-26	
20°	10-	14	.5 - 23	-27	
30°	10-	14	- 22	-26	
45°	9-	13	- 24		-34
60°	11	- 1	5 - 23.5		-32
110°	8-	12.5	- 23		-30

Focus at 90 cm:

Working range: 35 - 145cm(13.8"-57")

Best at: 56 - 116cm(22"-45.7") Laser Line Width <1mm

			100	Laser Li	ne Width <		
Laser	Recommended Working Range(cm)						
Fan Angle	40	65	90	115	140		
5°	29-	45 - 9	1 -1	09			
10°	35-		57 - 119		-146		
15°	31-		57 - 119		-140		
20°	31-		59 - 12	2	-142		
30°	42-	e e	60 - 114		-144		
45°	40-		55 - 120		-139		
60°	35-	5	6 - 116		-145		
110°	38-	60	- 106	-1	34		

Laser Line Width <1mm Laser Line Width <2mm

Headquarter QUARTON INC.

Tel: 886-2-2648-5656 Fax: 886-2-2648-5522 contact@quarton.com www.quarton.com

QUARTON USA INC.

Cell: 210-837-3485 contact@quarton.com www.quarton.com

Optional Accessories

Quarton offers mounts, power supply boards, battery pack and USB cable switch to help you running as quickly as possible. For more information, please visit www.quarton.com, www.guarton.com, www.guarton.com, www.guarton.com, <a href="https://


QLM-1125 - Laser Module Mount/Holder for diameter 6mm to 12.5mm, it's an ideal choose for mounted onto optical tables.

Feature:

- 4 directions adjustable.
- Can be mounted onto the optical table with screws (Screws not included).
- Engraved scale for precision adjustable.




LMPS-MP1 - Multi-function Laser Module Power Supply Board. Four input: USB, micro USB, DC Power Jack(5.5 x 2.1), and terminal block. Two channel output: 7 VDC 500mA and 5 VDC 1A. Three switches-toggle switch, remote switch and TTL signal.



Feature:

- Allow four kinds of power input: USB, micro USB, DC Power Jack(5.5x2.1) and terminal block.
- Two Channel output: 7 VDC 500mA and 5 VDC 1A.
- Built-in three switches: toggle switch, terminal block remote switch and TTL signal switch by on-board connect point.
- 7 VDC output work for all Quarton Laser Modules with 7-12 V operation Voltage (Vop).
- 5 VDC output work for all Quarton Laser Modules with 3-6 V operation Voltage (Vop).
- Three LED indicators: Input power indicator, 7V output indicator and 5V output indicator.

Optional Accessories



LMPS-MP2 - DC converter, In: 9-36V, Out: 5V 1A.



LMPS-mUSB1 - Laser Module Power Supply Board, Input: micro USB, Output: 5 VDC 500mA.

Feature:

- Micro USB connector power input.
- Output 5 VDC 500mA with alligator clips.
- For all Quarton Laser Modules that require 3-6V operation Voltage.



LMPS-DC1 - Laser Module Power Supply Board, Input: DC Power Jack(5.5 x 2.1), Output: 5 VDC 500mA.

Feature:

- DC Power Jack(5.5 x 2.1) power input.
- Output 5 VDC 500mA with alligator clips.
- For all Quarton Laser Modules that require 3-6V operation voltage.

Optional Accessories



CLM-BP4N3 - Battery pack (4* AA batteries)

*** AA Batteries are **NOT** included in package.

Feature:

USB Output Voltage: 5 VDC.

Color: Black.



CLM-USBSW - USB Cable Switch.

Feature:

Length: 28cm.

Color: Black.



CLM-UM3M - USB to micro USB Cable.

Feature:

Length: 3 meters.

· Color: Black.