

Description

The VN10LFTA uses advanced trench technology

to provide excellent $R_{\text{DS}(\text{ON})},$ low gate charge and

operation with gate voltages as low as 4.5V. This

device is suitable for use as a

Battery protection or in other Switching application.

General Features

V_{DS} = 60V I_D =0.3A

 $R_{DS(ON)} < 2\Omega @ V_{GS}=10V$

ESD Rating: HBM≥2000V

Application

Battery protection

Load switch

Uninterruptible power supply


Package Marking and Ordering Information

Product ID	Pack	Brand	Qty(PCS)
VN10LFTA	SOT-23	HXY MOSFET	3000

Absolute Maximum Ratings (Tc=25°Cunless otherwise noted)

Symbol	Parameter	Limit	Unit	
Vds	Drain-Source Voltage		60	V
Vgs	Gate-Source Voltage		±20	V
	Continuous Drain Current (TJ =150℃)	T _A =25℃	0.3	
I _D		T _A =100 °C	0.19	A
Ідм	Drain Current-Pulsed (Note 1)		0.8	А
PD	Maximum Power Dissipation		0.35	W
Тј,Тѕтб	Operating Junction and Storage Temperature Range		-55 To 150	°C
Reja	Thermal Resistance, Junction-to-Ambient (Note 2)		350	°C W





N-Channel MOSFET



Electrical Characteristics (T_A=25[°]Cunless otherwise noted)

Parameter	Symbol	Condition	Min	Тур	Max	Unit
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V I _D =250µA	60	68	-	V
Zero Gate Voltage Drain Current	ldss	V _{DS} =60V,V _{GS} =0V	-	-	1	μA
Gate-Body Leakage Current	lGSS	V _{GS} =±10V,V _{DS} =0V V _{GS} =±20V,V _{DS} =0V	-	±100 ±4	±500 ±10	nA uA
Gate Threshold Voltage	VGS(th)	$V_{DS}=V_{GS}$,I _D =250µA	0.7	1.2	1.9	V
		V _{GS} =5V, I _D =0.1A	-	1.3	3	Ω
Drain-Source On-State Resistance	Rds(on)	V _{GS} =10V, I _D =0.1A	-	1	2	Ω
Forward Transconductance	gfs	V _{DS} =10V,I _D =0.2A	0.1	-	-	S
Input Capacitance	C _{lss}		-	21	50	PF
Output Capacitance	Coss	V _{DS} =25V,V _{GS} =0V, F=1.0MHz	-	11	25	PF
Reverse Transfer Capacitance	Crss		-	4.2	5	PF
Turn-on Delay Time	td(on)		-	10	-	nS
Turn-on Rise Time	tr	VDD=30V,ID=0.2A	-	50	-	nS
Turn-Off Delay Time	td(off)	V_{GS} =10V,R _{GEN} =10Ω	-	17	-	nS
Turn-Off Fall Time	t _f		-	10	-	nS
Total Gate Charge	Qg	V _{DS} =10V,I _D =0.3A, V _{GS} =4.5V	-	1.7	3	nC
Diode Forward Voltage (Note 3)	Vsd	V _{GS} =0V,I _S =0.2A	-	-	1.2	V
Diode Forward Current (Note 2)	Is		-	-	0.3	A

Notes:

1. Repetitive Rating: Pulse width limited by maximum junction temperature.

2. Surface Mounted on FR4 Board, $t \le 10$ sec.

3. Pulse Test: Pulse Width \leq 300µs, Duty Cycle \leq 2%.

4. Guaranteed by design, not subject to production



Typical Electrical And Thermal Characteristics




Figure 1:Switching Test Circuit





Figure 3 Output Characteristics






Figure 2:Switching Waveforms








Figure 4 Transfer Characteristics










Vsd Source-Drain Voltage (V) Figure 8 Source-DrainDiode Forward



Vds Drain-Source Voltage (V) Figure 10 Safe Operation Area









Figure 12 Normalized Maximum Transient Thermal Impedance



SOT-23 Package Outline Dimensions








Symbol	Dimensions In Millimeters		Dimensions In Inches		
	Min	Max	Min	Max	
Α	0.900	1.150	0.035	0.045	
A1	0.000	0.100	0.000	0.004	
A2	0.900	1.050	0.035	0.041	
b	0.300	0.500	0.012	0.020	
С	0.080	0.150	0.003	0.006	
D	2.800	3.000	0.110	0.118	
Е	1.200	1.400	0.047	0.055	
E1	2.250	2.550	0.089	0.100	
e	0.950	0.950 TYP		7 TYP	
e1	1.800	2.000	0.071	0.079	
L	0.550 REF		0.022 REF		
L1	0.300	0.500	0.012	0.020	
θ	0°	8°	0°	8°	

SOT-23 Suggested Pad Layout



Note: 1.Controlling dimension:in millimeters.

2.General tolerance:± 0.05mm.
 3.The pad layout is for reference purposes only.



Attention

Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.

• HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.

• Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

• HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other

give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

• In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

• No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.

Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production.
HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.