

Silicon P-Channel Power MOSFET

Description


The MDT40P10D uses advanced technology and design to provide excellent RDS(ON) . It can be used in a wide variety of applications.

General Features

- ① V_{DSS}= -100V, I_D=-40A
- ② Low ON Resistance
- ③ Low Reverse transfer capacitances
- ④ 100% Single Pulse avalanche energy Test

Application

- ① Power switching application
- ② Adapter and charger



Electrical Characteristics @ Ta=25°C (unless otherwise specified)

Absolute Maximum Ratings:

Symbol	Parameter	Value	Units
V _{DSS}	Drain-to-Source Breakdown Voltage	-100	V
I _D	Drain Current (continuous) at T _c =25°C	-40	A
I _{DM}	Drain Current (pulsed)	-120	A
V _{GS}	Gate to Source Voltage	+/-20	V
P _{tot}	Total Dissipation at T _c =25°C	180	W
T _j	Max. Operating Junction Temperature	175	°C
E _{AS}	Single Pulse Avalanche Energy	700	mJ



迈诺斯科技

MDT40P10D

Electrical Parameters:

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
V _{DS}	Drain-source Voltage	V _{GS} = 0V, I _D = -250μA	-100			V
R _{DS(on)}	Static Drain-to-Source on-Resistance	V _{GS} = -10V, I _D = -15A		26	32	mΩ
V _{GS(th)}	Gated Threshold Voltage	V _{DS} = V _{GS} , I _D = -250μA	-1.0	-2.0	-3.0	V
I _{DSS}	Drain to Source leakage Current	V _{DS} = -110V, V _{GS} = 0V			-1.0	μA
I _{GSS(F)}	Gated Body Foward Leakage	V _{GS} = +20V			100	nA
I _{GSS(R)}	Gated Body Reverse Leakage	V _{GS} = -20V			-100	nA
C _{iss}	Input Capacitance	V _{GS} = 0V, V _{DS} = 25V, f = 1.0MHZ	2315			pF
C _{oss}	Output Capacitance		190			pF
C _{rss}	Reverse Transfer Capacitance		11			pF

Switching Characteristics

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
t _{d(on)}	Turn-on Delay Time	V _{DD} = -20V, I _D = -16A, R _G = 10Ω		28		nS
t _r	Turn-on Rise Time			21		nS
t _{d(off)}	Turn-off Delay Time			62		nS
t _f	Turn-off Fall Time			32		nS
Q _g	Total Gate Charge	V _{DS} = -20V I _D = -16A V _{GS} = -10V		40		nC
Q _{gs}	Gate-Source Charge			9.2		nC
Q _{gd}	Gate-Drain Charge			14		nC

Source-Drain Diode Characteristics

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
I _{SD}	S-D Current(Body Diode)				-40	A
I _{SDM}	Pulsed S-D Current(Body Diode)				-140	A
V _{SD}	Diode Forward Voltage	V _{GS} = 0V, I _{DS} = -35A			-1.5	V
t _{rr}	Reverse Recovery Time	T _J = 25 °C, I _F = -35A di/dt = 100A/us			555	nS
Q _{rr}	Reverse Recovery Charge				4550	μC
	*Pulse Test: Pulse Width <= 300μs, Duty Cycle <= 2%					

Symbol	Parameter	Typ	Units
R _{θJC}	Junction-to-Case	2.5	°C/W



迈诺斯科技

MDT40P10D

NOTE:

1. Exceeding the maximum ratings of the device in performance may cause damage to the device, even the permanent failure, which may affect the dependability of the machine. Please do not exceed the absolute maximum ratings of the device when circuit designing.
2. When installing the heat sink, please pay attention to the torsional moment and the smoothness of the heat sink.
3. MOSFETs is the device which is sensitive to the static electricity, it is necessary to protect the device from being damaged by the static electricity when using it.
4. Shenzhen Minos reserves the right to make changes in this specification sheet and is subject to change without prior notice.

CONTACT:

深圳市迈诺斯科技有限公司（总部）

地址：深圳市福田区华富街道田面社区深南中路4026号田面城市大厦22B-22C

邮编：518025

电话：0755-83273777