


电路图



PCB. 焊接图

主要技术规格:

1. 额定值: 50mA DC12V
2. 接触电阻: $\leq 100m\Omega$
3. 操作力: $250 \pm 30gf$
4. 行程: $0.25 \pm 0.1mm$
5. 绝缘电阻: $100M\Omega$
6. 抗电强度: 250V 50HZ 1Min.
7. 寿命: 100,000 Cycles

材料:

本体:	LCP	(白色)
按钮:	PPA	(黑色)
卡件:	黄铜	(镀银)
弹片:	不锈钢	(镀银)
盖板:	黄铜	(镀锡铈)

PAPT NO	TS1101C-X-X
Operating Force	160 : 160gf ; 260 : 260gf
Height	35 : 3.5mm

		new		2015/5/3	A	瀚源
ECN BO.		DESCRIPTION.		DATE.	REV.	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	TS1101C-X-X	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X. ± 0.25
			MODEL NAME	TS1101C-X-X		X.x ± 0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx ± 0.15
					ANGULAIR	± 3
					FILE.NO.	