SIEMENS

Data sheet

3RA2110-0CD15-1AP6



Fuseless motor starter Direct start 600VAC Size S00 0.18-0.25a 220/240VAC 50/60HZ screw connection For snapping onto 60 mm busbar systems Type of coordination 2 IQ = 150 KA Also full fills type Of coordination 1 1NO (contactor)

product brand name	SIRIUS
product brand name	non-fused motor starter 3RA2
design of the product	direct starter
manufacturer's article number	
of the supplied contactor	3RT2015-1AP61
 of the supplied contactor of the supplied circuit-breakers 	3RV2011-0CA10
 of the supplied busbar adapter 	8US1251-5DS10
 of the supplied busbar adapter of the supplied link module 	3RA1921-1DA00
General technical data	
size of the circuit-breaker	S00
size of load feeder	S00
	Yes
product extension auxiliary switch insulation voltage with degree of pollution 3 at AC rated	690 V
value	090 V
degree of pollution	3
surge voltage resistance rated value	6 kV
shock resistance according to IEC 60068-2-27	6g / 11 ms
mechanical service life (switching cycles) of contactor	30 000 000
typical	
type of assignment	2
Ambient conditions	
ambient temperature	
 during operation 	-20 +60 °C
 during storage 	-50 +80 °C
during transport	-55 +80 °C
Main circuit	
number of poles for main current circuit	3
design of the switching contact	electromechanical
adjustable current response value current of the current-dependent overload release	0.18 0.25 A
operating voltage	
 rated value 	690 V
 at AC-3 rated value maximum 	690 V
operating frequency rated value	50 60 Hz
operational current at AC-3 at 400 V rated value	0.2 A
operating power at AC-3	
 at 400 V rated value 	60 W
• at 500 V rated value	90 W
• at 690 V rated value	120 W

General Product Approval		ous locations	Conformity
General Product Approval		For use in hazard-	Declaration of
Certificates/ approvals			
touch protection on the front according to IEC 60529	finger-safe, for vertical conta	act from the front	
protection class IP on the front according to IEC 60529	1720		
according to SN 31920	- IP20		
B10 value with high demand rate according to SN 31920 proportion of dangerous failures with high demand rate	73 %		
Safety related data B10 value with high demand rate according to SN 31920	1 000 000		
finely stranded with core end processing			
connectable conductor cross-section for main contacts	0.5 2.5 mm²		
at AWG cables for main contacts	2x (20 16), only for conta	,	
for main contacts stranded	0.5 4 mm², 2x (0.75 2.8	ō mm²)	
type of connectable conductor cross-sections			
type of electrical connection for main current circuit	screw-type terminals		
Connections/ Terminals			
— at the side	9 mm		
— upwards — downwards	20 mm		
— upwards	20 mm		
— lorwards — backwards	0 mm		
 for live parts forwards 	0 mm		
— downwards	10 mm		
— at the side	9 mm		
— upwards	20 mm		
— backwards	0 mm		
— forwards	0 mm		
• for grounded parts			
required spacing			
depth	155.1 mm		
width	45 mm		
height	200 mm		
fastening method	for snapping onto 60 mm bu	usbar systems	
mounting position	vertical		
Installation/ mounting/ dimensions			
at 500 V according to IEC 60947-4-1 rated value	100 000 A		
• at 400 V according to IEC 60947-4-1 rated value	153 000 A		
• at 690 V according to IEC 60947-4-1 rated value	100 000 A		
conditional short-circuit current (lq)			
design of the short-circuit trip	magnetic		
product function short circuit protection	Yes		
Short-circuit protection			
unit			
response value current of instantaneous short-circuit trip	3.25 A		
design of the overload release	thermal (bimetallic)		
trip class	CLASS 10		
Protective and monitoring functions			
number of NC contacts for auxiliary contacts number of NO contacts for auxiliary contacts	1		
	0		
Auxiliary circuit			
inductive power factor with the holding power of the coil	0.25		
apparent holding power of magnet coil at AC	4.8 VA		
● at 60 Hz rated value	192 264 V		
• at 60 Hz rated value	240 V		
• at 50 Hz rated value	187 242 V		
• at 50 Hz rated value	220 V		
control supply voltage at AC	_		

(SP)	<u>Confirmation</u>		EHC	KEx ATEX	UK CA	
Declaration of Conformity	Test Certificates		Marine / Shipping			
CE EG-Konf.	<u>Type Test Certific-</u> ates/Test Report	Special Test Certific- ate	ABS	B U REAU VERITAS	Lloyd's Register uts	
Marine / Shipping				other	Railway	
PRS	RINA	RMRS	DNV-GL DNV-GL	<u>Confirmation</u>	Vibration and Shock	
Further information						
Information- and Downloadcenter (Catalogs, Brochures,) https://www.siemens.com/ic10						
Industry Mall (Online ordering system)						

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2110-0CD15-1AP6

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2110-0CD15-1AP6

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


https://support.industry.siemens.com/cs/ww/en/ps/3RA2110-0CD15-1AP6

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2110-0CD15-1AP6&lang=en

Characteristic: Tripping characteristics, I²t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RA2110-0CD15-1AP6/char

Further characteristics (e.g. electrical endurance, switching frequency) http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2110-0CD15-1AP6&objecttype=14&gridview=view1



last modified:

12/15/2020 🖸