SIEMENS

Data sheet

3RM1201-2AA04



Reversing starter, 3RM1, 500 V, 0 - 0.12 kW, 0.1 - 0.5 A, 24 V DC, spring-type terminals

product brand name	SIRIUS			
product category	Motor starter			
product designation	Reversing starter			
design of the product	with electronic overload protection			
product type designation	3RM1			
General technical data				
trip class	CLASS 10A			
equipment variant according to IEC 60947-4-2	3			
product function	Reversing starter			
 intrinsic device protection 	Yes			
 for power supply reverse polarity protection 	No			
suitability for operation device connector 3ZY12	Yes			
insulation voltage rated value	500 V			
overvoltage category	III			
surge voltage resistance rated value	6 kV			
maximum permissible voltage for safe isolation				
 between main and auxiliary circuit 	500 V			
 between control and auxiliary circuit 	250 V			
shock resistance	6g / 11 ms			
vibration resistance	1 6 Hz, 15 mm; 20 m/s², 500 Hz			
operating frequency maximum	1 1/s			
mechanical service life (switching cycles) typical	30 000 000			
reference code according to IEC 81346-2	Q			
Substance Prohibitance (Date)	03/01/2017			
product function				
 direct start 	No			
reverse starting	Yes			
product function short circuit protection	No			
Electromagnetic compatibility				
EMC emitted interference according to IEC 60947-1	class A			
EMC immunity according to IEC 60947-1	Class A			
conducted interference				
 due to burst according to IEC 61000-4-4 	3 kV / 5 kHz			
 due to conductor-earth surge according to IEC 61000-4-5 	2 kV			
 due to conductor-conductor surge according to IEC 61000-4-5 	1 kV			
 due to high-frequency radiation according to IEC 61000-4-6 	10 V			
field-based interference according to IEC 61000-4-3	10 V/m			


electrostatic discharge according to IEC 61000-4-2	4 kV contact discharge / 8 kV air discharge			
conducted HF interference emissions according to CISPR11	Class B for the domestic, business and commercial environments			
field-bound HF interference emission according to CISPR11	Class B for the domestic, business and commercial environments			
Safety related data				
protection class IP on the front according to IEC 60529	IP20			
touch protection on the front according to IEC 60529	- finger-safe			
Main circuit				
number of poles for main current circuit	3			
design of the switching contact	Hybrid			
design of the switching contact as NO contact for signaling function	OUT, electronic, 24 V DC, 15 mA			
adjustable current response value current of the current-dependent overload release	0.1 0.5 A			
minimum load [%]	20 %; from set rated current			
type of the motor protection	solid-state			
operating voltage rated value	48 500 V			
relative symmetrical tolerance of the operating voltage	10 %			
operating frequency 1 rated value	50 Hz			
operating frequency 2 rated value	60 Hz			
relative symmetrical tolerance of the operating frequency	10 %			
operational current				
• at AC at 400 V rated value	0.5 A			
 at AC-3 at 400 V rated value 	0.5 A			
 at AC-53a at 400 V at ambient temperature 40 °C rated value 	0.5 A			
ampacity when starting maximum	4 A			
operating power for 3-phase motors at 400 V at 50 Hz	0 0.12 kW			
Inputs/ Outputs				
input voltage at digital input				
 at DC rated value 	24 V			
 with signal <0> at DC 	0 5 V			
● for signal <1> at DC	15 30			
input current at digital input				
● for signal <1> at DC	11 mA			
• with signal <0> at DC	1 mA			
number of CO contacts for auxiliary contacts	1			
operational current of auxiliary contacts at AC-15 at 230 V maximum	3 A			
operational current of auxiliary contacts at DC-13 at 24 V maximum	1 A			
Control circuit/ Control				
type of voltage of the control supply voltage	DC			
control supply voltage at DC rated value	19.2 30 V			
relative negative tolerance of the control supply voltage at DC	20 %			
relative positive tolerance of the control supply voltage at DC	25 %			
control supply voltage 1 at DC rated value	24 V			
operating range factor control supply voltage rated				
value at DC				
• initial value	0.8			
• full-scale value	1.25			
control current at DC				
in standby mode of operation	25 mA			
when switching on	150 mA			
• during operation inrush current peak	70 mA			
IDRUSD CURRENT DOOK				
• at DC at 24 V	300 mA			


a at DC at 24 V at a vitability and af matter	140 mA
at DC at 24 V at switching on of motor	140 mA
duration of inrush current peak • at DC at 24 V	80 ms
 at DC at 24 V at DC at 24 V at switching on of motor 	80 ms
power loss [W] in auxiliary and control circuit	00 115
in switching state OFF	
— with bypass circuit	0.6 W
• in switching state ON	
— with bypass circuit	1.68 W
Response times	
ON-delay time	60 90 ms
OFF-delay time	60 90 ms
Power Electronics	
operational current	
 at 40 °C rated value 	0.5 A
• at 50 °C rated value	0.5 A
• at 55 °C rated value	0.5 A
• at 60 °C rated value	0.5 A
Installation/ mounting/ dimensions	
mounting position	vertical, horizontal, standing (observe derating)
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail
height	100 mm
width	22.5 mm
depth	141.6 mm
required spacing	
 with side-by-side mounting 	
— forwards	0 mm
— backwards	0 mm
— upwards	50 mm
— downwards — at the side	50 mm 0 mm
 at the side for grounded parts 	0 mm
 for grounded parts forwards 	0 mm
— backwards	0 mm
— upwards	50 mm
— at the side	3.5 mm
— downwards	50 mm
Ambient conditions	
installation altitude at height above sea level maximum	4 000 m; For derating see manual
ambient temperature	
during operation	-25 +60 °C
during storage	-40 +70 °C
during transport	-40 +70 °C
environmental category during operation according to IEC 60721	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
relative humidity during operation	10 95 %
air pressure according to SN 31205	900 1 060 hPa
Communication/ Protocol	
protocol is supported	
PROFINET IO protocol	No
PROFIsafe protocol	No
product function bus communication	No
protocol is supported AS-Interface protocol	No
Connections/ Terminals	
type of electrical connection	spring-loaded terminals (push-in) for main circuit, spring-loaded terminals (push-in) for control circuit
 for main current circuit 	spring-loaded terminals (push-in)
for auxiliary and control circuit	spring-loaded terminals (push-in)
wire length for motor unshielded maximum	100 m
type of connectable conductor cross-sections	

 for main conta 	cts						
— solid			1x (0).5 4 mm²)			
— finely stra	inded with core end proc	essing		1x (0.5 2.5 mm ²)			
	inded without core end p	-	1x (0.5 4 mm ²)				
	s for main contacts	-	1x (20 12)				
connectable condu contacts	ctor cross-section for	main					
 solid or strand 	ed		0.5.	0.5 4 mm²			
 finely stranded 	I with core end processir	ng	0.5.	0.5 2.5 mm ²			
 finely stranded 	I without core end proce	ssing	0.5 4 mm²				
connectable condu contacts	ctor cross-section for	auxiliary					
 solid or strand 	ed		0.5.	1.5 mm²			
 finely stranded 	I with core end processir	ng	0.5.	1 mm²			
finely stranded	without core end proce	ssing	0.5.	1.5 mm²			
type of connectable	e conductor cross-sect	tions					
 for auxiliary co 	ntacts						
— solid	— solid		1x (0.5 1.5 mm²), 2x (0.5 1.5 mm²)				
 finely stranded with core end processing 			1x (0,5 1,0 mm²), 2x (0,5 1,0 mm²)				
— finely stra	 finely stranded without core end processing 			1x (0.5 1.5 mm²), 2x (0.5 1.5 mm²)			
 at AWG cables 	 at AWG cables for auxiliary contacts 			1x (20 16), 2x (20 16)			
AWG number as co section	ded connectable cond	uctor cross					
for main contacts		20 12					
 for auxiliary co 	 for auxiliary contacts 			20 16			
UL/CSA ratings							
operating voltage a	t AC						
 according to U 	L rated value		480 V				
 according to C 	SA rated value		400	400 V			
Certificates/ approva	ls						
General Product A	pproval					EMC	
		<u>Confirmatic</u>	<u>on</u>	ŝ	rnr	A	
<u></u>	(M)			(WD	EHL	Ś	
CSA	ccc			UL		RCM	
Declaration of Conformity	Test Certificates	other		Railway			
CE EG-Konf.	<u>Type Test Certific-</u> ates/Test Report	<u>Confirmatic</u>	<u>on</u>	<u>Special Test Certific</u> <u>ate</u>	22		

Further information

Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10 Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RM1201-2AA04 Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RM1201-2AA04 Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3RM1201-2AA04 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RM1201-2AA04&lang=en





last modified:

6/21/2022 🖸