SIEMENS

Data sheet 3RW5225-1AC04



SIRIUS soft starter 200-480 V 63 A, 24 V AC/DC Screw terminals Analog output

product brand name	SIRIUS
product category	Hybrid switching devices
product designation	Soft starter
product type designation	3RW52
manufacturer's article number	
 of standard HMI module usable 	3RW5980-0HS00
 of high feature HMI module usable 	3RW5980-0HF00
 of communication module PROFINET standard usable 	3RW5980-0CS00
 of communication module PROFIBUS usable 	3RW5980-0CP00
 of communication module Modbus TCP usable 	3RW5980-0CT00
 of communication module Modbus RTU usable 	3RW5980-0CR00
 of communication module Ethernet/IP 	3RW5980-0CE00
 of circuit breaker usable at 400 V 	3VA2163-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
 of circuit breaker usable at 500 V 	3VA2163-7MN32-0AA0; Type of coordination 1, Iq = 20 kA, CLASS 10
 of circuit breaker usable at 400 V at inside-delta circuit 	3VA2110-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
 of circuit breaker usable at 500 V at inside-delta circuit 	3VA2110-7MN32-0AA0; Type of coordination 1, Iq = 20 kA, CLASS 10
 of the gG fuse usable up to 690 V 	3NA3830-6; Type of coordination 1, Iq = 65 kA
 of the gG fuse usable at inside-delta circuit up to 500 V 	3NA3830-6; Type of coordination 1, Iq = 65 kA
 of full range R fuse link for semiconductor protection usable up to 690 V 	3NE1022-0; Type of coordination 2, Iq = 65 kA
 of back-up R fuse link for semiconductor protection usable up to 690 V 	3NE8024-1; Type of coordination 2, Iq = 65 kA

General technical data	
starting voltage [%]	30 100 %
stopping voltage [%]	50 %; non-adjustable
start-up ramp time of soft starter	0 20 s
current limiting value [%] adjustable	130 700 %
certificate of suitability	
 CE marking 	Yes
UL approval	Yes
CSA approval	Yes
product component	
HMI-High Feature	No
 is supported HMI-Standard 	Yes
is supported HMI-High Feature	Yes
product feature integrated bypass contact system	Yes
number of controlled phases	3

trin class	CLASS 10A (default) / 10E / 20E; and to IEC 60047 4.2
trip class	CLASS 10A (default) / 10E / 20E; acc. to IEC 60947-4-2
buffering time in the event of power failure	100 mg
for main current circuit for control circuit	100 ms
• for control circuit	100 ms
insulation voltage rated value	600 V
degree of pollution	3, acc. to IEC 60947-4-2
impulse voltage rated value	6 kV
blocking voltage of the thyristor maximum	1 400 V
service factor	1
surge voltage resistance rated value	6 kV
maximum permissible voltage for safe isolation	C00.V
between main and auxiliary circuit	600 V
shock resistance	15 g / 11 ms, from 12 g / 11 ms with potential contact lifting
vibration resistance	15 mm to 6 Hz; 2g to 500 Hz
utilization category according to IEC 60947-4-2	AC 53a
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	02/15/2018
product function	Van
• ramp-up (soft starting)	Yes
• ramp-down (soft stop)	Yes
Soft Torque	Yes
adjustable current limitation	Yes
pump ramp down intrincip dovice greater than	Yes
• intrinsic device protection	Yes
motor overload protection	Yes; Electronic motor overload protection
evaluation of thermistor motor protection	No V
• inside-delta circuit	Yes
• auto-RESET	Yes
• manual RESET	Yes
• remote reset	Yes; By turning off the control supply voltage
communication function	Yes
operating measured value display	Yes; Only in conjunction with special accessories
error logbook via coffware parameterizable	Yes; Only in conjunction with special accessories
via software parameterizable	No You
via software configurable PROFlorery	Yes
PROFlenergy	Yes; in connection with the PROFINET Standard communication module
firmware update	Yes
 removable terminal for control circuit 	Yes
torque control	No
analog output	Yes; 4 20 mA (default) / 0 10 V (parameterizable with High Feature HMI)
Power Electronics	
operational current	
at 40 °C rated value	63 A
at 50 °C rated value	56 A
at 60 °C rated value	51 A
operational current at inside-delta circuit	
at 40 °C rated value	109 A
• at 50 °C rated value	96 A
at 60 °C rated value	87.5 A
operating voltage	
rated value	200 480 V
at inside-delta circuit rated value	200 480 V
relative negative tolerance of the operating voltage	-15 %
relative positive tolerance of the operating voltage	10 %
relative negative tolerance of the operating voltage at inside-delta circuit	-15 %
relative positive tolerance of the operating voltage at inside-delta circuit	10 %
operating power for 3-phase motors	

	40.5 120
at 230 V at 40 °C rated value at 230 V at inside delta sireuit at 40 °C rated value	18.5 kW
at 230 V at inside-delta circuit at 40 °C rated value at 400 V at 40 °C rated value	30 kW
 at 400 V at 40 °C rated value at 400 V at inside-delta circuit at 40 °C rated value 	30 kW 55 kW
Operating frequency 1 rated value	50 Hz
Operating frequency 2 rated value	60 Hz
relative negative tolerance of the operating frequency	-10 %
relative positive tolerance of the operating frequency	10 %
adjustable motor current	
at rotary coding switch on switch position 1	25.5 A
at rotary coding switch on switch position 2	28 A
 at rotary coding switch on switch position 3 	30.5 A
at rotary coding switch on switch position 4	33 A
at rotary coding switch on switch position 5	35.5 A
 at rotary coding switch on switch position 6 	38 A
 at rotary coding switch on switch position 7 	40.5 A
 at rotary coding switch on switch position 8 	43 A
 at rotary coding switch on switch position 9 	45.5 A
 at rotary coding switch on switch position 10 	48 A
 at rotary coding switch on switch position 11 	50.5 A
 at rotary coding switch on switch position 12 	53 A
at rotary coding switch on switch position 13	55.5 A
at rotary coding switch on switch position 14	58 A
at rotary coding switch on switch position 15	60.5 A
at rotary coding switch on switch position 16	63 A
minimum adjustable motor current	25.5 A
 adjustable motor current for inside-delta circuit at rotary coding switch on switch position 1 	44.2 A
 for inside-delta circuit at rotary coding switch on switch position 2 	48.5 A
 for inside-delta circuit at rotary coding switch on switch position 3 	52.8 A
 for inside-delta circuit at rotary coding switch on switch position 4 	57.2 A
 for inside-delta circuit at rotary coding switch on switch position 5 	61.5 A
 for inside-delta circuit at rotary coding switch on switch position 6 	65.8 A
 for inside-delta circuit at rotary coding switch on switch position 7 	70.1 A
for inside-delta circuit at rotary coding switch on switch position 8	74.5 A
for inside-delta circuit at rotary coding switch on switch position 9 for inside delta circuit at rotary coding switch on switch on the circuit at rotary coding switch on switch on the circuit at rotary coding switch on switch on the circuit at rotary coding switch on switch position switch on the circuit at rotary coding switch on switch on the circuit at rotary coding switch	78.8 A
for inside-delta circuit at rotary coding switch on switch position 10 for inside delta circuit at rotary coding switch on	83.1 A
for inside-delta circuit at rotary coding switch on switch position 11 for inside-delta circuit at rotary coding switch on	91.8 A
 for inside-delta circuit at rotary coding switch on switch position 12 for inside-delta circuit at rotary coding switch on 	91.8 A 96.1 A
ior inside-delta circuit at rotary coding switch on switch position 13 for inside-delta circuit at rotary coding switch on	100 A
ior inside-delta circuit at rotary coding switch on switch position 14 for inside-delta circuit at rotary coding switch on	105 A
switch position 15 • for inside-delta circuit at rotary coding switch on	109 A
switch position 16 • at inside-delta circuit minimum	44.2 A
minimum load [%]	15 %; Relative to smallest settable le
power loss [W] for rated value of the current at AC	
at 40 °C after startup	31 W
• at 50 °C after startup	29 W

at 60 °C after startup	27 W
power loss [W] at AC at current limitation 350 %	
 at 40 °C during startup 	882 W
 at 50 °C during startup 	744 W
at 60 °C during startup	659 W
Control circuit/ Control	
type of voltage of the control supply voltage	AC/DC
control supply voltage at AC	
 at 50 Hz rated value 	24 V
at 60 Hz rated value	24 V
relative negative tolerance of the control supply voltage at AC at 50 Hz	-20 %
relative positive tolerance of the control supply voltage at AC at 50 Hz	20 %
relative negative tolerance of the control supply voltage at AC at 60 Hz	-20 %
relative positive tolerance of the control supply voltage at AC at 60 Hz	20 %
control supply voltage frequency	50 60 Hz
relative negative tolerance of the control supply voltage frequency	-10 %
relative positive tolerance of the control supply voltage frequency	10 %
control supply voltage	
at DC rated value	24 V
relative negative tolerance of the control supply voltage at DC	-20 %
relative positive tolerance of the control supply voltage at DC	20 %
control supply current in standby mode rated value	160 mA
holding current in bypass operation rated value	380 mA
locked-rotor current at close of bypass contact	7.6 A
maximum inrush current peak at application of control supply voltage maximum	3.3 A
duration of inrush current peak at application of control supply voltage	12.1 ms
design of the overvoltage protection	Varistor
design of short-circuit protection for control circuit	4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply
Inputs/ Outputs	
number of digital inputs	1
number of digital outputs	3
not parameterizable	2
digital output version	2 normally-open contacts (NO) / 1 changeover contact (CO)
number of analog outputs	1
switching capacity current of the relay outputs	
at AC-15 at 250 V rated value	3 A
• at DC-13 at 24 V rated value	1 A
Installation/ mounting/ dimensions	
mounting position	+/- 10° rotation possible and can be tilted forward or backward on vertical mounting surface
fastening method	screw fixing
height	306 mm
width	185 mm
depth	203 mm
required spacing with side-by-side mounting	
• forwards	10 mm
backwards	0 mm
• upwards	100 mm
• downwards	75 mm
at the side	5 mm
- at the erae	V

weight without packaging	5.6 kg
Connections/ Terminals	
type of electrical connection	
 for main current circuit 	box terminal
 for control circuit 	screw-type terminals
width of connection bar maximum	25 mm
type of connectable conductor cross-sections	
 for main contacts for box terminal using the front clamping point solid 	1x (2.5 16 mm²)
 for main contacts for box terminal using the front clamping point finely stranded with core end processing 	1x (2.5 50 mm²)
 for main contacts for box terminal using the front clamping point stranded 	1x (10 70 mm²)
 at AWG cables for main contacts for box terminal using the front clamping point 	1x (10 2/0)
for main contacts for box terminal using the back clamping point solid	1x (2.5 16 mm²)
at AWG cables for main contacts for box terminal using the back clamping point	1x (10 2/0)
for main contacts for box terminal using both clamping points solid	2x (2.5 16 mm²)
 for main contacts for box terminal using both clamping points finely stranded with core end processing 	2x (2.5 35 mm²)
for main contacts for box terminal using both clamping points stranded	2x (6 16 mm²), 2x (10 50 mm²)
 for main contacts for box terminal using the back clamping point finely stranded with core end processing 	1x (2.5 50 mm²)
 for main contacts for box terminal using the back clamping point stranded 	1x (10 70 mm²)
type of connectable conductor cross-sections	
 for control circuit solid 	1x (0.5 4.0 mm²), 2x (0.5 2.5 mm²)
 for control circuit finely stranded with core end processing 	1x (0.5 2.5 mm²), 2x (0.5 1.5 mm²)
 at AWG cables for control circuit solid 	1x (20 12), 2x (20 14)
wire length	
 between soft starter and motor maximum 	800 m
 at the digital inputs at AC maximum 	100 m
at the digital inputs at DC maximum	1 000 m
tightening torque	
for main contacts with screw-type terminals	4.5 6 N·m
for auxiliary and control contacts with screw-type	0.8 1.2 N·m
terminals	
tightening torque [lbf·in]	
 for main contacts with screw-type terminals 	40 53 lbf·in
 for auxiliary and control contacts with screw-type terminals 	7 10.3 lbf·in
mbient conditions	
installation altitude at height above sea level maximum	5 000 m; Derating as of 1000 m, see catalog
ambient temperature	
during operation	-25 +60 °C; Please observe derating at temperatures of 40 °C or above
during storage and transport	-40 +80 °C
environmental category	
during operation according to IEC 60721	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
• during storage according to IEC 60721	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4
 during transport according to IEC 60721 	2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)
EMC emitted interference	acc. to IEC 60947-4-2: Class A
communication/ Protocol	
ommanication/ 1 Totocol	

• PROFINET standard Yes EtherNet/IP Yes Modbus RTU Yes • Modbus TCP Yes PROFIBUS Yes **UL/CSA** ratings manufacturer's article number of circuit breaker - usable for Standard Faults at 460/480 V

- usable for High Faults at 460/480 V according to UL

- usable for Standard Faults at 460/480 V at inside-delta circuit according to UL

- usable for High Faults at 460/480 V at insidedelta circuit according to UL

- usable for Standard Faults at 575/600 V according to UL

- usable for Standard Faults at 575/600 V at inside-delta circuit according to UL

according to UL

- usable for Standard Faults up to 575/600 V according to UL

- usable for High Faults up to 575/600 V according to UL

- usable for Standard Faults at inside-delta circuit up to 575/600 V according to UL

- usable for High Faults at inside-delta circuit up to 575/600 V according to UL

Siemens type: 3RV2742, max. 70 A or 3VA51, max. 125 A; Iq = 10 kA

Siemens type: 3VA51, max. 125 A; Iq max = 65 kA

Siemens type: 3VA51, max. 125 A; Iq = 10 kA

Siemens type: 3VA51, max. 125 A; Iq max = 65 kA

Siemens type: 3RV2742, max. 70 A or 3VA51, max. 125 A; Iq = 10 kA

Siemens type: 3VA51, max. 125 A; Iq = 10 kA

Type: Class RK5 / K5, max. 200 A; Iq = 10 kA

Type: Class J / L, max. 225 A; Iq = 100 kA

Type: Class RK5 / K5, max. 200 A; Iq = 10 kA

Type: Class J / L, max. 225 A; Iq = 100 kA

operating power [hp] for 3-phase motors

• at 200/208 V at 50 °C rated value • at 220/230 V at 50 °C rated value 20 hp • at 460/480 V at 50 °C rated value 30 hp

• at 200/208 V at inside-delta circuit at 50 °C rated • at 220/230 V at inside-delta circuit at 50 °C rated

value at 460/480 V at inside-delta circuit at 50 °C rated

value

15 hp

40 hp

30 hp

75 hp

contact rating of auxiliary contacts according to UL

R300-B300

Safety related data

protection class IP on the front according to IEC touch protection on the front according to IEC 60529

electromagnetic compatibility

IP00; IP20 with cover

finger-safe, for vertical contact from the front with cover in accordance with IEC 60947-4-2

Certificates/ approvals

General Product Approval

EMC



Confirmation









Declaration of Conformity

Test Certificates

Marine / Shipping





Type Test Certificates/Test Report







Marine / Shipping

other





Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5225-1AC04

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5225-1AC04

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RW5225-1AC04
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RW5225-1AC04&lang=en

Characteristic: Tripping characteristics, I²t, Let-through current https://support.industry.siemens.com/cs/ww/en/ps/3RW5225-1AC04/char

Characteristic: Installation altitude

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RW5225-1AC04&objecttype=14&gridview=view1

Simulation Tool for Soft Starters (STS)

https://support.industry.siemens.com/cs/ww/en/view/101494917

ast modified:	4/10/2022