

## Crystal Part No.: RFX-32-16.0M40IL

Issue 2; 28th November 2022

### Features

- Frequency 16.0MHz fundamental
- Calibration tolerance  $\pm 10$ ppm
- Temperature stability  $\pm 30$ ppm
- Temperature range (-40 to +85) $^{\circ}$ C
- The flexible nature of the design, means that variations to suit almost any application can be developed to meet individual customer requirements
- Drive level 100uW
- Series Resistance 80 $\Omega$
- Shunt capacitance  $C_0$  3 pF max.
- Load capacitance CL (8 - 50)pF or series
- Ageing :  $\pm 3 \times 10^{-6}$  /year

### Environmental

- Electrostatic-Sensitive Device (ESD)
- Storage Temperature Range: (-55 to +125) $^{\circ}$ C
- Mechanical shock: MIL standard 202F, method 213 condition J
- Thermal shock: MIL standard 202F, method 107, condition A
- Vibration: MIL standard 202F, method 204, condition B
- Solderability: 5 seconds maximum at 230 $^{\circ}$ C
- 3 seconds maximum at 350 $^{\circ}$ C

### Compliance

- RoHS Status (2011/65/EU) Compliant
- REACH Status - Compliant

### Packaging

- Pack Style: tape and reel: 3000 pieces

### Ordering Information

- Crystal model: RFX-32 series
- Crystal Part No.: RFX-32-16.0M40IL[xx]


Where [xx] is the required load

e.g. RFX-32-16.0M40IL30 for 30pF

RFX-32-16.0M40ILS for series



### Dimensions (mm)



### Part number examples by load

Load condition	Part number
10pF	RFX-32-16.0M40IL10
20pF	RFX-32-16.0M40IL20
30pF	RFX-32-16.0M40IL30
Series	RFX-32-16.0M40ILS