

SERIES: VGS-150W | **DESCRIPTION:** INTERNAL AC-DC POWER SUPPLY


FEATURES

- wide input range (85 ~ 305 VAC)
- available with conformal coating or terminal cover options
- UL/EN/IEC 62368 certified
- designed to meet IEC/EN 61558 and IEC/EN 60335 system requirements
- short-circuit, over-current, over-voltage protections
- input over voltage category III for fixed installations (under 2,000 m altitude)
- CISPR/EN55032 Class B radiated/conducted emissions



| MODEL | output voltage | output current | output power | ripple and noise ¹ | efficiency ² |
|-------------|----------------|----------------|--------------|-------------------------------|-------------------------|
| | (Vdc) | max (A) | max (W) | typ (mVp-p) | typ (%) |
| VGS-150W-12 | 12 | 12.5 | 150 | 150 | 86 |
| VGS-150W-15 | 15 | 10.0 | 150 | 150 | 87 |
| VGS-150W-24 | 24 | 6.5 | 156 | 200 | 88 |
| VGS-150W-36 | 36 | 4.3 | 154 | 200 | 88 |
| VGS-150W-48 | 48 | 3.3 | 158 | 200 | 89 |

Notes: 1. Ripple & noise are measured at 20 MHz BW with 47 μ F aluminum electrolytic capacitor and 0.1 μ F ceramic capacitor on the output.
 2. Measured at 230 Vac.

PART NUMBER KEY


INPUT

| parameter | conditions/description | min | typ | max | units |
|---------------------------|------------------------|-----|-----|------|-------|
| voltage | ac input | 85 | | 305 | Vac |
| | dc input | 120 | | 431 | Vdc |
| frequency | | 47 | | 63 | Hz |
| current | at 115 Vac | | | 4 | A |
| | at 230 Vac | | | 2 | A |
| inrush current | at 115 Vac | | 30 | | A |
| | at 230 Vac | | 60 | | A |
| leakage current | at 277 Vac | | | 0.75 | mA |
| no load power consumption | at 250 Vac | | | 0.5 | W |

OUTPUT

| parameter | conditions/description | min | typ | max | units |
|----------------------------|------------------------|-----|-------|--------|-------|
| capacitive load | 12 Vdc output | | | 10,000 | μF |
| | 15 Vdc output | | | 6,000 | μF |
| | 24 Vdc output | | | 2,400 | μF |
| | 36 Vdc output | | | 1,200 | μF |
| | 48 Vdc output | | | 600 | μF |
| initial set point accuracy | at full load | | ±1 | | % |
| line regulation | at rated load | | ±0.5 | | % |
| load regulation | 0% ~ 100% load | | ±0.5 | | % |
| hold-up time | at 115 Vac | 8 | | | ms |
| | at 230 Vac | 40 | | | ms |
| switching frequency | | | 65 | | kHz |
| temperature coefficient | | | ±0.03 | | %/°C |
| adjustability | built in trim pot | | ±10 | | % |

PROTECTIONS

| parameter | conditions/description | min | typ | max | units |
|-----------------------------|-----------------------------------|-----|-----|-------|-------|
| over voltage protection | 12 Vdc output, hiccup | | | 16.2 | Vdc |
| | 15 Vdc output, hiccup | | | 21.75 | Vdc |
| | 24 Vdc output, hiccup | | | 33.6 | Vdc |
| | 36 Vdc output, hiccup | | | 48.6 | Vdc |
| | 48 Vdc output, hiccup | | | 60 | Vdc |
| over current protection | auto recovery | 110 | | 150 | % |
| short circuit protection | hiccup, continuous, auto recovery | | | | |
| over-temperature protection | shut-down, auto recovery | | | | °C |

SAFETY & COMPLIANCE

| parameter | conditions/description | min | typ | max | units |
|-------------------|---|--------|-------------|-----|-------|
| isolation voltage | input to ground, 1 min. <10mA | 2,000 | | | Vac |
| | input to output, 1 min. <10mA | 4,000 | | | Vac |
| | output to ground, 1 min. <10mA | 1,250 | | | Vac |
| safety approvals | certified to | 62368: | IEC, EN, UL | | |
| | designed to meet | 60335: | IEC, EN | | |
| | designed to meet | 61558: | IEC, EN | | |
| safety class | class I | | | | |
| EMI/EMC | CISPR 32/EN 55032 Class B, IEC 61000-3-2 Class A (≤80% load) | | | | |
| ESD | IEC/EN 61000-4-2 Contact ±6KV/Air ±8KV perf. criteria A | | | | |
| radiated immunity | IEC/EN 61000-4-3 10 V/m perf. criteria A | | | | |
| EFT/burst | IEC/EN 61000-4-4 ±4KV perf. criteria A | | | | |
| surge | IEC/EN 61000-4-5 line to line ±2KV/line to ground ±4KV perf. criteria A | | | | |

SAFETY & COMPLIANCE

| | | | |
|-------------------------------|---|---------|-------|
| conducted immunity | IEC/EN 61000-4-6 10 Vr.m.s perf. criteria A | | |
| voltage dips and interruption | IEC/EN 61000-4-11 0%, 70% perf. criteria B | | |
| MTBF | as per MIL-HDBK-217F at 25°C | 300,000 | hours |
| RoHS | yes | | |

ENVIRONMENTAL

| parameter | conditions/description | min | typ | max | units |
|-----------------------|------------------------|-----|-----|-----|-------|
| operating temperature | | -30 | | 70 | °C |
| storage temperature | | -40 | | 85 | °C |
| operating humidity | non-condensing | 20 | | 90 | % |
| storage humidity | non-condensing | 10 | | 95 | % |

MECHANICAL


| parameter | conditions/description | min | typ | max | units |
|---------------|---|-----|------------|-----|-------|
| dimensions | 159.00 x 97.00 x 30.00 mm | | | | inch |
| weight | 12V, 15V models 24V, 36V, 48V models | | 430 410 | | g |
| cooling | free air convection | | | | |
| case material | metal (AL1100, SGCC) | | | | |

MECHANICAL DRAWING

units: mm
tolerance: ±1 [±0.039]

| PIN CONNECTIONS | |
|-----------------|----------|
| PIN | Function |
| 1 | AC(L) |
| 2 | AC(N) |
| 3 | ⊕ |
| 4 | -Vo |
| 5 | -Vo |
| 6 | +Vo |
| 7 | +Vo |

wire range: 22-12 AWG
connector tightening torque: M3.5, 0.8N·m




| Position | Screw spec. | L (max) | Torque (max) |
|----------|-------------|---------|--------------|
| ② - ④ | M3 | 5 mm | 0.4 N·m |
| ⑦ - ⑧ | M3 | 3 mm | 0.4 N·m |


Note: At least one hole position, ①~④ must be securely connected to Protective Earth (PE) ⊕

DERATING CURVE

TEMPERATURE DERATING CURVE




INPUT VOLTAGE DERATING CURVE (25 °C)




EFFICIENCY CURVES

EFFICIENCY VS INPUT LOAD (full load)



EFFICIENCY VS OUTPUT LOAD (at 230 Vac)



REVISION HISTORY

| rev. | description | date |
|------|--|------------|
| 1.0 | initial release | 09/02/2020 |
| 1.01 | derating and efficiency curves updated | 06/14/2021 |
| 1.02 | screw length table updated | 12/09/2021 |
| 1.03 | UKCA mark added | 06/13/2022 |
| 1.04 | derating curve updated | 09/04/2022 |
| 1.05 | features updated | 01/09/2024 |

The revision history provided is for informational purposes only and is believed to be accurate.



Headquarters
20050 SW 112th Ave.
Tualatin, OR 97062
800.275.4899

Fax 503.612.2383
cui.com
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.