# SIEMENS

Data sheet for SINAMICS G120X

#### Article No. :

#### 6SL3230-3YC36-0UF0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Rated data		
Input		
Number of phases	3 AC	
Line voltage	200 240 V +10 %	6 -20 %
Line frequency	47 63 Hz	
Rated voltage	200V IEC	240V NEC
Rated current (LO)	126.00 A	126.00 A
Rated current (HO)	98.00 A	98.00 A
Output		
Number of phases	3 AC	
Rated voltage	200V IEC	240V NEC <sup>1)</sup>
Rated power (LO)	37.00 kW	50.00 hp
Rated power (HO)	30.00 kW	40.00 hp
Rated current (LO)	130.00 A	130.00 A
Rated current (HO)	104.00 A	104.00 A
Rated current (IN)	133.00 A	
Max. output current	176.00 A	
Pulse frequency	4 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	

#### **Overload capability**

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor $\lambda$	0.90 0.95	
Offset factor $\cos \phi$	0.99	
Efficiency η	0.97	
Sound pressure level (1m)	72 dB	
Power loss 3)	1.450 kW	
Filter class (integrated)	Unfiltered	
EMC category (with accessories)	without	
Safety function "Safe Torque Off"	without	
Communication		

Communication

PROFINET, EtherNet/IP

ltem no. : Consignment no. : Project :

Switching level: 1 → 0     5       Max. inrush current     1       Fail-safe digital inputs     1       Number     1	5 11 V 5 V
Switching level: $0 \rightarrow 1$ 1Switching level: $1 \rightarrow 0$ 5Max. inrush current1Fail-safe digital inputsNumber1	- 11 V
Switching level: 1 → 0       5         Max. inrush current       1         Fail-safe digital inputs       1         Number       1	
Max. inrush current 1 Fail-safe digital inputs Number 1	5 V
Fail-safe digital inputs       Number     1	
Number 1	15 mA
Divited externate	l
Digital outputs	
Number as relay changeover contact 2	2
Output (resistive load)	DC 30 V, 5.0 A
Number as transistor 0	)
Analog / digital inputs	
Number 2	2 (Differential input)
Resolution 1	I0 bit
Switching threshold as digital input	
0 → 1 4	1 V
1 → 0 1	1.6 V
Analog outputs	
Number 1	I (Non-isolated output)
PTC/ KTY interface	
1 motor temperature sensor input, senso Thermo-Click, accuracy ±5 °C	are that can be connected DTC KTV and

Closed-loop control techniques		
V/f linear / square-law / parameterizable	Yes	
V/f with flux current control (FCC)	Yes	
V/f ECO linear / square-law	Yes	
Sensorless vector control	Yes	
Vector control, with sensor	No	
Encoderless torque control	No	
Torque control, with encoder	No	

## **SIEMENS**

#### Data sheet for SINAMICS G120X

#### Article No. :

#### 6SL3230-3YC36-0UF0

Ambie	nt conditions
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002
Cooling	Air cooling using an integrated fan
Cooling air requirement	0.153 m³/s (5.403 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
Ambient temperature	
Operation	-20 45 °C (-4 113 °F)
Transport	-40 70 °C (-40 158 °F)
Storage	-25 55 °C (-13 131 °F)
Relative humidity	
Max. operation	95 % At 40 $^\circ C$ (104 $^\circ F), condensation and icing not permissible$
Co	nnections
Signal cable	
Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 16)
Line side	
Version	M10 screw
Conductor cross-section	35.00 2 x 120.00 mm² (AWG 1 AWG 2 x 4/0)
Motor end	
Version	M10 screw
Conductor cross-section	35.00 2 x 120.00 mm <sup>2</sup> (AWG 1 AWG 2 x 4/0)
DC link (for braking resistor)	
PE connection	M10 screw
Max. motor cable length	
Shielded	300 m (984.25 ft)
Unshielded	450 m (1,476.38 ft)

	Aechanical data
Degree of protection	IP20 / UL open type
Frame size	FSF
Net weight	18.8 kg (41.45 lb)
Dimensions	
Width	305 mm (12.01 in)
Height	709 mm (27.91 in)
Depth	369 mm (14.53 in)
	Standards
Compliance with standards UL, cUL, CE, C-Tick (RCM), EAC, KC SEMI F47, REACH	
CE marking	EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC
Converter	losses to IEC61800-9-2*
Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	56.2 %
I ▲ 976.0 W (1.8 %)	1,160.0 W (2.1 %) 1,450.0 W (2.7 %
100% <b>•</b>	•
571.0 W (1.1 %)	639.0 W (1.2 %) 734.0 W (1.4 %)

The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*converted values

<sup>1)</sup>The output current and HP ratings are valid for the voltage range 220V-240V

<sup>3)</sup>Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.

## SIEMENS

### Data sheet for SINAMICS G120X

#### Article No. :

#### 6SL3230-3YC36-0UF0

	Operator panel:	Intelligent Operator Panel (IOP-2)
	Screen	
Display design	LCD color	Ambient temperature
Screen resolution	320 x 240 Pixel	Operation
	Mechanical data	Storage
Degree of protection	IP55 / UL type 12	Transport
Net weight	0.134 kg (0.30 lb)	Relative humidity at 25°C o
Dimensions		Max. operation
Width	70.00 mm (2.76 in)	
Height	106.85 mm (4.21 in)	
Depth	19.65 mm (0.77 in)	Certificate of suitability

Ambient conditions Ambient temperature		
	55 °C only with door installation kit	
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
elative humidity at 25°C durin	g	
Max. operation	95 %	
Approvals		
ertificate of suitability	CE, cULus, EAC, KCC, RCM	