




Specification:
 Volatage Rating:250V AC/DC
 Current Rating :3A AC/DC
 Withstaning Voltage:800V AC/Minute
 Temperature Range:-40~+105°(C5191)
 -40~+125°(C7025)
 Insulation Resistance:≥1000MΩ
 Contact Resistance:≤10MΩ

K 201900 T F - X X XX - X
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- 1.K:XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:T-Terminal
- 4.Welding Board Angle:F-Female Terminal
- 5.Material:P-Phosphor Bronze
H-High Conductivity Copper
- 6.Plating Code:SN:40~120u"(1~3um)Ni
80~200u"(2~5um)Tin
SN1:40~120u"(1~3um)Tin
- 7.Plating Process:S-Stamping before Plating
P-Stamping after Plating
- 8.Barrel type:H-High Feet; L-Low Feet



K201900TF-XXXX-X	Phosphor Bronze	K201900HM	X2000W
PART NO	Material	Suitable XKB Housing	Suitable XKB Wafer

K201900TF-XXXX-H	AWG#22-20 (0.35~0.5mm ²)	Ø1.6mm Max	1.80	1.70	K201900HM
K201900TF-XXXX-L	AWG#24-22 (0.22~0.35mm ²)		1.70	1.60	
PART NO	Wire Range	Insulation O.D	DIM A	DIM B	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	2.0mm automotive connector
CHKD	UNIT: mm/in	PART NO.: K201900TF-XXXX-X
APPD	SIZE: A4	DWG NO.: X-K201900TF-XXXX-X
		WEIGHT SHEET REVISION
		1/1 A0



XKB INDUSTRIAL PRECISION CO.,LIMITED

SECTION: A-A
SCALE: 1:1

SECTION: B-B
SCALE: 1:1

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

ΔX					
ΔX					
ΔX					
MARK	DESCRIPTION	DATE	REVISED	APPROVED	

REVISIONS