


■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -40°C~+125°C
- Insulation resistance: 1000MΩ Min
- Contact resistance: 10mΩ Max

K 202820 H - 2xXX - N0 X  
 ① ② ③ ④ ⑤ ⑥

1.K: XKBTEK-Car Connector  
 2.XKB Series No  
 3.Category:H-Housing  
 4.Row No.-Pin No:2xXX-2x04P~2x21P  
 5.Material : N0-PA66 UL 94V-0  
 6.Color:W-White ; B-Black;GY-Grey

Circuits	Dimensions		
	A	B	C
2x4	6.00	10.00	4.80
2x5	8.00	12.00	4.80
2x6	10.00	14.00	4.80
2x7	12.00	16.00	4.80
2x8	14.00	18.00	4.80
2x9	16.00	20.00	4.80
2x10	18.00	22.00	11.20
2x11	20.00	24.00	11.20
2x12	22.00	26.00	11.20
2x13	24.00	28.00	11.20
2x14	26.00	30.00	11.20
2x15	28.00	32.00	11.20
2x16	30.00	34.00	15.20
2x17	32.00	36.00	15.20
2x18	34.00	38.00	15.20
2x19	36.00	40.00	15.20
2x20	38.00	42.00	15.20
2x21	40.00	44.00	15.20



K202820H-2xXX-N0X	PA66	X202820T	X202820W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Wafer

DSND	SCALE: N/A	MODEL TYPE: 2.0mm Automobile connector
DWN	VIEW:	PART NO.: K202820H-2xXX-N0X
CHKD	UNIT: mm/in	DWG NO.: X-K202820H-2xXX-N0X
APPD	SIZE: A4	



					ANGULAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						