
Page 1 of 3 **AS-11.0592-S-EXT-TR**

SPECIFICATIONS

PARAMETER	VALUE
NOMINAL FREQUENCY	11.0592 MHz
MODE OF OSCILLATION	Fundamental
FREQUENCY TOLERANCE AT 25°C	±30 ppm max
FREQUENCY STABILITY OVER TEMPERATURE	±50 ppm max
OPERATING TEMPERATURE RANGE	-40°C to +85°C
STORAGE TEMPERATURE RANGE	-55°C to +125°C
AGING	±5 ppm per year max
LOAD CAPACITANCE	Series
EQUIVALENT SERIES RESISTANCE	50 Ω max
SHUNT CAPACITANCE	7 pF max
DRIVE LEVEL	100 μW typ, 1000 μW max
REFLOW CONDITIONS	260°C for 10s max
INSULATION RESIATANCE	500 MΩ min @ DC 100V



MECHANICAL SPECIFICATION




H=3.5 mm





AS-11.0592-S-EXT-TR

WAVE SOLDER PROFILE



Wave Solder profile				
Profile Feature	SnPb eutectic	Pb-Free		
Average ramp-up rate	~200°C/second	~200°C/second		
Heating Rate during preheat	typical 1-2°/second max 4°/second	typical 1-2°/second max 4°/second		
Final preheat temperature, T _S	~130°C	~130°C		
Peak temperature, T _P	235°C	260°C		
Time within +0°C / -5°C of actual temperature, t _P	10 seconds	10 seconds		
Ramp-down rate	5°C/second max.	5°C/second max.		

NOTE: This document should serve as recommendation only. Other parameters may also affect soldering, this profile does not guarantee absolute success. Soldering profile should be determined by the equipment manufacturer and customers' process engineer.

ENVIRONMENTAL

PARAMETER	VALUE
MOISTURE SENSITIVITY LEVEL	1
RoHS	Compliant
REACH SVHC	Compliant
HALOGEN-FREE	Compliant
ESD CLASSIFICATION LEVEL	N/A
TERMINATION FINISH	Sn





LOW PROFILE MICROPROCESSOR CRYSTAL

Page 3 of 3

AS-11.0592-S-EXT-TR

MARKING

R110xSyw

x-1 or 2 digits as Internal Production ID code

y - Year code

w – Week code

YEAR CODE		
Year	Code	
2015	5	
2016	6	
2017	7	
2018	8	
2019	9	
2020	0	
2021	1	
2022	2	
2023	3	
2024	4	
2025	5	

	ALPHA WEEK CODE TABLE				
Week	Code	Week	Code	Week	Code
1	a	19	s	37	K
2	b	20	t	38	L
3	c	21	u	39	M
4	d	22	v	40	N
5	e	23	w	41	0
6	f	24	x	42	P
7	g	25	У	43	Q
8	h	26	Z	44	R
9	i	27	A	45	S
10	j	28	В	46	T
11	k	29	C	47	U
12	1	30	D	48	V
13	m	31	E	49	W
14	n	32	F	50	X
15	0	33	G	51	Y
16	р	34	Н	52	Z
17	q	35	I		
18	r	36	J		

APPROVAL

DRAWN BY:	A, Initial Release, December 16, 2011
APPROVED BY:	A, Initial Release, December 16, 2011
REVISION:	B, Updated to current spec levels by
	YLi. May 7, 2020

Raltron Electronics / RAMI Technology USA, LLC, including its affiliates, employees, agents and other persons acting on its behalf (collectively Raltron/RAMI Tech), disclaim any and all liability for any errors or inaccuracies contained in this data sheet. While Raltron/RAMI Tech has made every reasonable effort ensure the accuracy of all product information, specifications and data contained herein, Raltron/RAMI Tech does not guarantee that the information is accurate, reliable or current. The product information is provided only for reference purposes only and is subject to change, correction or revision, at any time without notice. Raltron/RAMI Tech does not sasume any liability arising to a superior or use of any product described herein and disclaims any warranties expressed or implied. The user of products in such applications shall assume all risks of such use and will agree to hold Raltron/RAMI Tech, harmless against all damages.

Copyright © 2016, Raltron Electronics / RAMI Technology USA, LLC. All rights reserved. No part of this document may be reproduced in any form without the prior written permission of Raltron Electronics / RAMI Technology USA, LLC.